

# Plastic Silicon Infrared Phototransistor

## **QSE122**

#### Description

The QSE122 is a silicon phototransistor encapsulated in a wide angle, infrared transparent, black plastic sidelooker package.

#### **Features**

NPN Silicon PhototransistorPackage Type: Sidelooker

Medium Wide Reception Angle, 50°
Package Material and Color: Black Epoxy

• Matched Emitter: QEE113

Daylight FilterHigh Sensitivity

• Red Dot Marking on the Top Side

• This is a Pb-Free Device


## **ABSOLUTE MAXIMUM RATINGS** ( $T_A = 25^{\circ}C$ unless otherwise noted)


Symbol	Parameter	Value	Unit
T <sub>OPR</sub>	Operating Temperature	-40 to +100	°C
T <sub>STG</sub>	Storage Temperature	-40 to +100	°C
T <sub>SOL-I</sub>	Soldering Temperature (Iron) 240 for 5 s (Note 2), (Note 3), (Note 4)		°C
T <sub>SOL-F</sub>	Soldering Temperature (Flow) (Note 2), (Note 3)	260 for 10 s	°C
V <sub>CE</sub>	Collector Emitter Voltage	30	V
V <sub>EC</sub>	Emitter Collector Voltage	5	V
P <sub>D</sub>	Power Dissipation (Note 1)	100	mW

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. Derate power dissipation linearly 1.33 mW/°C above 25°C.
- 2. RMA flux is recommended.
- 3. Methanol or isopropyl alcohols are recommended as cleaning agents.
- 4. Soldering iron 1/16" (1.6 mm) minimum from housing.

#### **SCHEMATIC**





SIDELOOKER DETECTOR CASE 100CN

#### **ORDERING INFORMATION**

Device	Package	Shipping
QSE122	SIDELOOKER DETECTOR (Pb-Free)	500 / Bulk Bag

#### **QSE122**

## **ELECTRICAL CHARACTERISTICS** (T<sub>A</sub> = 25°C)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
$\lambda_{PS}$	Peak Sensitivity		-	880	-	nm
Θ	Reception Angle		_	±25	-	٥
I <sub>CEO</sub>	Collector Emitter Dark Current	V <sub>CE</sub> = 10 V, Ee = 0	-	-	100	nA
BV <sub>CEO</sub>	Collector-Emitter Breakdown	I <sub>C</sub> = 1 mA	30	_	-	V
BV <sub>ECO</sub>	Emitter-Collector Breakdown	I <sub>E</sub> = 100 μA	5	-	-	V
I <sub>C(ON)</sub>	On-State Collector Current (Note 5)	$Ee = 0.5 \text{ mW/cm}^2, V_{CE} = 5 \text{ V}$	3.0	-	12.0	mA
V <sub>CE(SAT)</sub>	Saturation Voltage (Note 5)	$Ee = 0.5 \text{ mW/cm}^2, I_C = 0.1 \text{ mA}$	-	_	0.4	V
t <sub>r</sub>	Rise Time	$I_C$ = 1 mA, $V_{CC}$ = 5 V, $R_L$ = 100 $\Omega$	-	8	_	μs
t <sub>f</sub>	Fall Time		-	8	-	μs

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5.  $\lambda = 880 \text{ nm}$  (AlGaAs).

#### TYPICAL PERFORMANCE CHARACTERISTICS




Figure 1. Light Current vs. Radiant Intensity




Figure 3. Dark Current vs. Collector – Emitter Voltage




Figure 5. Dark Current vs. Ambient Temperature




Figure 2. Angular Response Curve




Figure 4. Light Current vs. Collector – Emitter Voltage

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales