ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari

TND6252/D Rev. 0, FEB – 2018



LED Driver with Phase–cut Dimmable Function, 40 W

1

LED Driver with Phase-cut Dimmable Function, 40 W

The following reference design supports inclusion of FL7734MX in design of an LED Driver with Phase-cut dimmable function. It should be used in conjunction with the FL7734MX datasheet.

Application	ON Semiconductor Device	Input Voltage Range	Rated Output Power	Output Voltage (Rated Current)	Topology
LED Driver	FL7734	108-305 V _{AC}	40 W	40 V (1000 mA)	Flyback

Key Features


Performance

- < ±2.0% Total Constant Current Tolerance Over All Conditions</p>
- < ±1.8% Over Universal Line Voltage Variation</p>
- < 0.7% from 70% to 100% Load Voltage Variation</p>
- Excellent Dimmer Compatibility by Active Dimming Control
- Programmable Dimming Curve and Input Current Management
- Fast Startup utilizing Bleeding Circuit
 < 0.1 s at the Max. Dimmer Phase Angle
 < 0.5 s at the Min. Dimmer Phase Angle
- Power Factor Correction in Non-dimming Mode
- Constant LED Current Regulation in Large Phase Angle Range


System Protection

- LED Short / Open Protection
- Output Diode Short Protection, Sensing Resistor Short / Open Protection
- VDD Over-Voltage Protection (OVP)
- VDD Under-Voltage Lockout (UVLO)
- Over-Temperature Protection (OTP)
- All Protections are Auto Restart (AR)
- Cycle-by-Cycle Current Limit

1. Schematic



2. Transformer





9

11




Figure 3. Transformer Winding Structure

2.1. Winding Specification

Winding	Pins (S→F)	Wire (Diameter)	Turns	Layers	Winding Direction	Winding Method	
N _{P1} ⁽¹⁾	3→2	0.5 φ	8	1	▲ Forward	Solenoid	
Insulation: 1 ta	Insulation: 1 tape layer between coil and finish lead, 1 tape layer after winding						
Ns	9→11	0.7 φ TIW	14	1	▲ Forward	Solenoid	
Insulation: 1 ta	Insulation: 1 tape layer after winding						
Np2	2→1	0.5 φ	5	1	▲ Forward	Solenoid	
Insulation: 1 ta	Insulation: 1 tape layer between coil and finish lead, 1 tape layer after winding						
NA	4→5	0.2 φ	8	1	▲ Forward	Solenoid	
Insulation: 1 tape layer between coil and finish lead, 3 tape layers after winding							

2.2. Electrical Characteristics

	Pin	Specification	Remarks
Inductance	3→1	150 µH ± 5 %	50 kHz, 1 V _{AC}
Leakage	3→1	< 10 µH	Short all other pins

3. Bill of Material

ltem No.	Part Reference	Part Number	Description	Manufacturer
1	F1	SS-5-2A	2 A/250 V Fuse	Bussmann
2	MOV1	SVC471D-10A	Metal Oxide Varistor	Samwha
3	BD1	G3SBA60	4 A / 600 V, Bridge Diode	Vishay
4	R111	MOR 1W TC 1R5K	Metal oxide film resistor RSD type J 1.5 kOhm/1W R-forming	ABC
5	R114	MOR 2W TC 200R	Metal oxide film resistor RSD type J 200 Ohm/2W R-forming	ABC
6	R115	MOR 2W TC 200R	Metal oxide film resistor RSD type J 200 Ohm/2W R-forming	ABC
7	R116	MOR 2W TC 2R	Metal oxide film resistor RSD type J 2 Ohm/2W R-forming	ABC
8	R117	RC0805 JR-071KL	1 kOhm SMD Resistor 2012 F 1/8W	Yageo
9	R118	RC0603 JR-0736KL	36 kOhm SMD Resistor 1608 F 1/16W	Yageo
10	R119	RC0603 JR-07240KL	240 kOhm SMD Resistor 1608 F 1/16W	Yageo
11	R120	RC1206JR-07100KL	100 kOhm SMD Resistor 3216 F 1/4W	Yageo
12	R121	RC1206JR-07100KL	100 kOhm SMD Resistor 3216 F 1/4W	Yageo
13	R122	RC1206JR-07100KL	100 kOhm SMD Resistor 3216 F 1/4W	Yageo
14	R123	MOR 1W TC 2R0K	Metal oxide film resistor RSD type J 2.0 kOhm/1W R-forming	ABC
15	R125	RC1206 JR-0733RL	33 Ohm SMD Resistor 3216 F 1/4W	Yageo
16	R128	RC1206 JR-070R3RL	0.3 Ohm SMD Resistor 3216 F 1/4W	Yageo
17	R10	RC1206 JR-0730RL	30 Ohm SMD Resistor 3216 F 1/4W	Yageo
18	R11	RC1206 JR-0743RL	43 Ohm SMD Resistor 3216 F 1/4W	Yageo
19	R12	RC1206 JR-072ML	2 MOhm SMD Resistor 3216 F 1/4W	Yageo
20	R13	RC0805 JR-071KL	1 kOhm SMD Resistor 2012 F 1/8W	Yageo
21	R14	RC1206 JR-070R3RL	0.3 Ohm SMD Resistor 3216 F 1/4W	Yageo
22	R15	RC1206 JR-070R3RL	0.3 Ohm SMD Resistor 3216 F 1/4W	Yageo
23	R16	RC0805 JR-07360RL	360 Ohm SMD Resistor 2012 F 1/4W	Yageo
24	R17	RC0805 JR-0715RL	15 Ohm SMD Resistor 2012 F 1/4W	Yageo
25	R18	RC0603 JR-07560KL	560 kOhm SMD Resistor 1608 F 1/16W	Yageo
26	R19	RC0603 JR-0768KL	68 kOhm SMD Resistor 1608 F 1/16W	Yageo
27	R20	RC0603 JR-0711KL	11 kOhm SMD Resistor 1608 F 1/16W	Yageo
28	R21	RC0603 JR-07110KL	110 kOhm SMD Resistor 1608 F 1/16W	Yageo
29	R22	RC0603 JR-077R5KL	7.5 kOhm SMD Resistor 1608 F 1/16W	Yageo
30	R23	RC0603 JR-07180KL	180 kOhm SMD Resistor 1608 F 1/16W	Yageo
31	R25	RC0603 JR-070R0L	0 Ohm SMD Resistor 1608 F 1/16W	Yageo
32	R26	RC0603 JR-070R0L	0 Ohm SMD Resistor 1608 F 1/16W	Yageo
33	R27	RC0805 JR-07200KL	200 kOhm SMD Resistor 2012 F 1/4W	Yageo
34	R28	RC1206 JR-072MKL	2 MOhm SMD Resistor 3216 F 1/4W	Yageo
35	R29	RC0805 JR-07160KRL	160 kOhm SMD Resistor 2012 F 1/4W	Yageo
36	R30	RC0805 JR-07200KL	200 kOhm SMD Resistor 2012 F 1/8W	Yageo

Item Part No. Reference		Part Number	Description	Manufacturer	
37	R31	RC0805 JR-0715KL	15 kOhm SMD Resistor 2012 F 1/8W	Yageo	
38	R32	RC0805 JR-0720KL	20 kOhm SMD Resistor 2012 F 1/8W	Yageo	
39	C111	MPE 630V473	MPE 47 nF/630 V	Sungho electronics	
40	C114	TF224*2*10B	MTF 220 nF/450 V	CARLI	
40	C115	MPE 630V103	MPE 10 nF/630 V	Sungho electronics	
41	C116	TF224*2*10B	MK 0.22uF/450V	CARLI	
42	C117	TF334*2*10B	MK 0.33uF/450V	CARLI	
43	C119	C1206C101KCRACTU	100 pF / 500 V, SMD Capacitor 3216	Kemet	
44	C120	KMG 470 µF / 63 V	470 μF / 63 V, Electrolytic Capacitor	Samyoung	
45	C121	KMG 470 µF / 63 V	470 μF / 63 V, Electrolytic Capacitor	Samyoung	
46	C122	KMG 470 µF / 63 V	470 μF / 63 V, Electrolytic Capacitor	Samyoung	
47	C4	C1206C103KDRACTU	10 nF/1 kV SMD Capacitor 3216	Kemet	
49	C6	GRM1885C1E822JA01#	8.2 nF/16 V SMD Capacitor 1608 COG	Murata	
50	C8	KMG 22uF35V	KMG series 22 µF/35 V D5 X H11 105℃ Electrolytic Capacitor	Samyoung	
51	C9	GRM2192C1H682JA01#	6.8 nF/50 V SMD Capacitor 2012 CH	Murata	
52	C10	C0603C100K8GACTU	10 pF/10 V SMD Capacitor 1608 NP0	Kemet	
53	C12	KMG 2.2uF63V	KMG series 2.2 µF/63 V D5 X H11 105℃ Electrolytic Capacitor	Samyoung	
54	C13	GRM188B11A474KA61#	470 nF/10 V SMD Capacitor 1608 B	Murata	
55	C14	GRM1881X1E332JA01#	3.3 nF/10 V SMD Capacitor 1608 SL	Murata	
56	C15	GRM185D71A105KE36#	1 uF/10 V SMD Capacitor 1608 X7T	Murata	
57	C17	SCF2E471M14DW7	Y cap 470pF	SAMWHA	
58	C18	GRM1882C1H101JA01#	100 pF/50 V SMD Capacitor CH	Murata	
59	C19	GRM1881X1E202JA01#	2 nF/10 V SMD Capacitor 1608 SL	Murata	
60	LF1	B82733F	40 mH Common Inductor	EPCOS	
61	L1	R06102KT00	Radial inductor 1.0 mH size Φ10 mm X H11 mm P 8mm	BOSUNG	
62	T1	PQ3220 core	PQ Core, 12-Pin Transformer	TDK	
63	D1	1N4007	1000 V/1.0 A DO-41 package general purpose diode	ON Semiconductor	
64	D2	1N4007	1000 V/1.0 A DO-41 package general purpose diode	ON Semiconductor	
65	D4	RS1M	1000 V/1.0 A SMA package fast recovery diode	ON Semiconductor	
66	D5	EGP30K	800 V/3.0 A DO-201AD package	ON Semiconductor	
67	D6	RURP1560	600 V / 15 A, Ultrafast Rectifier	ON Semiconductor	
68	D7	1N4148WS	100V/0.3A SOD-323 package general purpose diode	ON Semiconductor	
69	TVS1	P6KE300A	TVS diode Vc=414 V	ON Semiconductor	
70	ZD2	MM3Z6V2B	6.2 V zener diode SOD-323	ON Semiconductor	
71	ZD5	MM3Z24VB	24 V zener diode SOD-323	ON Semiconductor	
72	Q1	FQB5N50C	N-ch mosfet 500 V/5.0 A D2-Pak	ON Semiconductor	
73	Q2	FCPF600N60Z	N-ch mosfet 600 V/7.4 A TO-220	ON Semiconductor	
74	Q3	FCPF600N60Z	N-ch mosfet 600 V/7.4 A TO-220	ON Semiconductor	
75	Q4	2N7002K	N-ch mosfet 60 V/0.3 A SOT-23	ON Semiconductor	
76	Q5	KST2222A	NPN General purpose transistor	ON Semiconductor	
77	U	FL7734MX	Phase cut dimmable LED driver IC	ON Semiconductor	

4. Performance





 Figure 4.
 Output Current Regulation Data plotted against Output Voltage Change

Input Voltage	l _{oυτ} Minimum (mA)	Iout Maximum (mA)	Tolerance (±%)
108 V _{AC} [60 Hz]	1036	1042	0.28
120 V _{AC} [60 Hz]	1037	1040	0.1
230 V _{AC} [60 Hz]	1021	1030	0.4
264 V _{AC} [60 Hz]	1011	1022	0.5
277 V _{AC} [60 Hz]	1004	1015	0.5
305 V _{AC} [60 Hz]	1000	1010	0.4

 Table 1. Output Current Regulation by Output Voltage Change (30-40 V)



input voltage



Input Voltage	Input Power (W)	Output Current (mA)	Output Voltage (V)	Output Power (W)	Efficiency (%)
108 V _{AC} [60 Hz]	48.4	1042	40	41.68	86.1
120 V _{AC} [60 Hz]	47.8	1040	40	41.6	86.9
230 V _{AC} [60 Hz]	46.2	1025	40	41	88.5
264 V _{AC} [60 Hz]	46.4	1020	40	40.8	87.9
277 V _{AC} [60 Hz]	46.3	1013	40	40.5	87.5
305 V _{AC} [60 Hz]	46.7	1009	40	40.3	86.4

Table 2. System Efficiency – 40 V Nominal Load




Figure 6. PF and THD data plotted against Line Variation – 40 V Nominal Load

Input Voltage	Output Current (mA)	Output Voltage (V)	Power Factor	THD (%)
108 V _{AC} [60 Hz]	1042	40	0.99	14.80
120 V _{AC} [60 Hz]	1040	40	0.99	14.80
230 V _{AC} [60 Hz]	1025	40	0.93	16.70
264 V _{AC} [60 Hz]	1020	40	0.91	19.40
277 V _{AC} [60 Hz]	1013	40	0.90	20.00
305 V _{AC} [60 Hz]	1009	40	0.88	23.90

Table 3. Power Factor and Input Current THD




Figure 7 shows a dimming curve which is obtained by rotating the dimmer switch. Regardless of input line voltage $\pm 10\%$ variation, LED current is constantly regulated from 180 to 130° dimmer phase angle .When the phase angle is below 130°, LED current decreases linearly according to internal dimming reference modulation.





Figure 8. NEMA SSL-7A Specification

FL7734 dimming control method can meet NEMA SSL-7A specification. Figure 8 indicates the maximum and minimum dimmed output range as specified by NEMA SSL-7A.



5. Electromagnetic Interference(EMI)

Figure 9. HV Live





Figure 10. HV Neutral



6. Related Resources

FL7734 Product Page

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly ori indirectly, any claim of personal injury or death

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative