

NCP6925EVK

7 Channel PMIC with 2 DC-DC Converters, 5 LDOs and a Triple Input 10 bits ADC Evaluation Kit Manual



ON Semiconductor®

<http://onsemi.com>

EVALUATION KIT MANUAL

The NCP6925EVK evaluation kit is a full assembled circuit board for evaluation and test of the NCP6925. This document provides documentation, test procedure and equipment set-up for the complete evaluation of the NCP6925. The NCP6925EVK comes with one NCP6925 evaluation board, 1 MCU board for I²C master and associated cables.

General Description

The NCP6925 integrated circuit is part of the ON Semiconductor mini power management IC family (PMIC). It is optimized to supply battery powered portable application sub-systems such as camera function, microprocessors. This device integrates 2 high efficiency 1 A step-down DC-DC converters, 5 low dropout (LDO) voltage regulators and a triple input 10 bits ADC in a WLCSP36 2.4 x 2.4 mm package.

Features

- 2 DC-DC Converters (3 MHz, 1 μ H / 10 μ F, 1 A)
 - ♦ Peak Efficiency 95%
 - ♦ Programmable Output Voltage from 0.6 V to 3.3 V by 12.5 mV Steps

- 5 Low Noise – Low Dropout Regulators (2.2 μ F, 300 mA)
 - ♦ Programmable Output Voltage from 0.8 V to 3.5 V by 25 mV Steps
- Triple Input 10 bits ADC
 - ♦ Dual Resistors Measurement Mode
 - ♦ General Purpose Mode
- Control
 - ♦ Fully Programmable Through a 400 kHz / 3.4 MHz I²C with Pins Selectable I²C Address and Interrupt Output
 - ♦ Power on Input and General Purpose I/O Pins that can be used as DC-DC Enable Pins
- Very Low Quiescent Current at No Load
- Small Footprint : 2.4 x 2.4 mm WLCSP 0.4 mm Pitch




Figure 1. Evaluation Board Picture

NCP6925EVK

Table 1. BOARD COMPONENTS DESCRIPTION

Qty	Reference	Value	PCB Footprint	MFR	Part Number
1	–	NCP6925 PMIC	–	ON Semiconductor	NCP6925
1	R13	SMD Resistor 10 K Ω	0603	Panasonic	ERJ-3GEY0R00V
10	C5, C6, C7, C8, C9, C10, C11, C12, C13, C14	Ceramic Capacitor 2.2 μ F 6.3 V X5R	0402	TDK	C1005X5R0J225K050BC
2	C15, C16	Ceramic Capacitor 1 μ F 6.3 V X5R	0402	TDK	C1005X5R0J105K05BB
2	C1, C3	Ceramic Capacitor 4.7 μ F 6.3 V X5R	0603	TDK	C1608X5R0J475K080AB
2	C2, C4	Ceramic Capacitor 10 μ F 6.3 V X5R	0603	TDK	C1608X5R0J475K080AB
2	C17, C19	Ceramic Capacitor 100 μ F 6.3 V X5R	1210	TDK	C3225X5R0J107M250AC
2	L1, L2	Inductor	2016	TOKO	DFE2016R-H-2R2N
14	J3, J5, J8, J11, J12, S102, LTR100 \rightarrow LTR107	Jumper Header Vertical Mount, 3 positions, 100mils	100 mils	Tyco Electronics / AMP	5-826629-0
13	J13 \rightarrow J21 J6, J7, J9, J10	Banana Jack		Hirschmann Test and Measurement	930160000
1	J100	Connector header 26 pos		3M	N2526-6002-RB
23	TP1 ... TP23	Test Point		Keystone Electronics	5011
4	Q3, Q4, R15, R16,	Not Mounted			
3	J4, J22, J23	Jumper Connector	400 mils	Harwin	D3082-B01
3	S4, S6, S7	Shorted			
4	Spacer nylon	H1, H2, H3, H4		Richco Plastic co	R908-4

Table 2. CONNECTOR DESCRIPTION

Input Power		
Vbat (J6–J9)	–	negative input connected to GND pin (J9)
	AVIN and PVIN	Core and DCDCs power supply (J6)
VIN_LDO (J7–J10)	–	negative input connected to GND pin (J10)
	VIN_LDO	Dedicated LDOs power supply. S4 has to be unsoldered (J10)
Regulators Outputs		
J(13 \rightarrow J21)	–	negative output connected to GND pin (J14 and J21)
	J13	DCDC1 output
	J15	DCDC2 output
	J16	LDO1 output
	J17	LDO2 output
	J18	LDO3 output
	J19	LDO4 output
	J20	LDO5 output

NCP6925EVK

Table 2. CONNECTOR DESCRIPTION

Chip Control		
MCU	SDA	I ² C data, connect to SDA pin or the 26 pins ribbon cable
	SCL	I ² C data, connect to SCL pin or the 26 pins ribbon cable
	HWEN	Master enable pin connected to the 26 pins ribbon cable thru J3
	A0	I ² C address selectable pin connected to the 26 pins ribbon cable thru J11
	A1	I ² C address selectable pin connected to the 26 pins ribbon cable thru J12
	GPIO1	GPIO pin connected to the 26 pins ribbon cable thru J5
	GPIO2	GPIO pin connected to the 26 pins ribbon cable thru J8




Figure 2. Assembly Layer

NCP6925EVK

SCHEMATIC




Figure 3. Evaluation Board Schematic

REV	DATE	DESCRIPTION	AUTHOR
DESIGNED BY		ON SEMICONDUCTOR	
PCE		152 Chemin Basso Cambo BP93612 31035 TOULOUSE Cedex 1 France	
		NCP6925 Evaluation Board	Rev
		TLS-P-001-B-0613-OM	A.0
		DWG NO	
		TLS-P-001-B-0613-OM	
Thursday, June 06, 2013	Scale	Size C	Sheet 1 of 1 (Total # of pages)

NCP6925EVK

SOFTWARE INSTALLATION

Double click on NCP6925_setup.exe file. Follow the instructions set-up.

It is recommended to copy the NCP6925_setup.exe to a local directory: If eval kit is already installed, a simple double click on NCP6925.exe will launch the GUI.

Important notice: In order to properly install drivers and software, please launch NCP6925_setup.exe file before connects the MCU board.




Figure 4.

QUICK CONFIGURATION

Power Supply

NCP6925 requires at least 1 external power supply :
Vbat (J6) : supply between 2.5 V to 5.5 V.

Jumpers Configuration

The HWEN, A0 and A1 jumpers are configured by default to work with the ONSEMI I²C interface board. GPIO1 and GPIO2 jumpers are not configured.

S4 shunt is soldered to use only one power supply for the DCDCs, LDOs and AVIN.

Load

DCDCx Converters

An electronic load or passive load can be connected between J13 and J14 for DCDC1, between J15 and J21 for DCDC2.

LDOx Regulators

An electronic load or passive load can be connected between J16 and J14 or J21 for LDO1, between J17 and J14 or J21 for LDO2, J18 and J14 or J21 for LDO3, J19 and J14 or J21 for LDO4, J20 and J14 or J21 for LDO5.

ADC

TP13, TP14, TP18 can be used as general purpose input for the ADC.

NCP6925EVK

PCB LAYOUT




Figure 5. Top Layer




Figure 6. Bottom Layer

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

The evaluation board/kit (research and development board/kit) (hereinafter the "board") is not a finished product and is as such not available for sale to consumers. The board is only intended for research, development, demonstration and evaluation purposes and should as such only be used in laboratory/development areas by persons with an engineering/technical training and familiar with the risks associated with handling electrical/mechanical components, systems and subsystems. This person assumes full responsibility/liability for proper and safe handling. Any other use, resale or redistribution for any other purpose is strictly prohibited.

The board is delivered "AS IS" and without warranty of any kind including, but not limited to, that the board is production-worthy, that the functions contained in the board will meet your requirements, or that the operation of the board will be uninterrupted or error free. ON Semiconductor expressly disclaims all warranties, express, implied or otherwise, including without limitation, warranties of fitness for a particular purpose and non-infringement of intellectual property rights.

ON Semiconductor reserves the right to make changes without further notice to any board.

You are responsible for determining whether the board will be suitable for your intended use or application or will achieve your intended results. Prior to using or distributing any systems that have been evaluated, designed or tested using the board, you agree to test and validate your design to confirm the functionality for your application. Any technical, applications or design information or advice, quality characterization, reliability data or other services provided by ON Semiconductor shall not constitute any representation or warranty by ON Semiconductor, and no additional obligations or liabilities shall arise from ON Semiconductor having provided such information or services.

The boards are not designed, intended, or authorized for use in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body. Should you purchase or use the board for any such unintended or unauthorized application, you shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the board.

This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and may not meet the technical requirements of these or other related directives.

FCC WARNING – This evaluation board/kit is intended for use for engineering development, demonstration, or evaluation purposes only and is not considered by ON Semiconductor to be a finished end product fit for general consumer use. It may generate, use, or radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment may cause interference with radio communications, in which case the user shall be responsible, at its expense, to take whatever measures may be required to correct this interference.

ON Semiconductor does not convey any license under its patent rights nor the rights of others.

LIMITATIONS OF LIABILITY: ON Semiconductor shall not be liable for any special, consequential, incidental, indirect or punitive damages, including, but not limited to the costs of requalification, delay, loss of profits or goodwill, arising out of or in connection with the board, even if ON Semiconductor is advised of the possibility of such damages. In no event shall ON Semiconductor's aggregate liability from any obligation arising out of or in connection with the board, under any theory of liability, exceed the purchase price paid for the board, if any.

For more information and documentation, please visit www.onsemi.com.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:

Voice Mail: 1 800-282-9855 Toll Free USA/Canada

Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative