

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild guestions@onsemi.com.


ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



TN6717A







NPN General Purpose Amplifier

This device is designed for general purpose medium power amplifiers and switches requiring collector currents to 1.0 A. Sourced from Process 39.

Absolute Maximum Ratings*

TA = 25°C unless otherwise noted

Symbol	Parameter	Value	Units
V_{CEO}	Collector-Emitter Voltage	80	V
V _{CBO}	Collector-Base Voltage	80	V
V _{EBO}	Emitter-Base Voltage	5.0	V
I _C	Collector Current - Continuous	1.2	A
T _J , T _{stg}	Operating and Storage Junction Temperature Range	-55 to +150	°C

^{*}These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

Thermal Characteristics TA = 25°C unless otherwise noted

Symbol	Characteristic	М	Units	
		TN6717A	*NZT6717	
P_{D}	Total Device Dissipation	1.0	1.0	W
	Derate above 25°C	8.0	8.0	mW/°C
$R_{\theta JC}$	Thermal Resistance, Junction to Case	50		°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	125	125	°C/W

^{*}Device mounted on FR-4 PCB 36 mm X 18 mm X 1.5 mm; mounting pad for the collector lead min. 6 cm².

¹⁾ These ratings are based on a maximum junction temperature of 150 degrees C.

2) These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.


NPN General Purpose Amplifier


(continued)

Symbol	Parameter	Test Conditions	Min	Max	Units
OFF CHAF	RACTERISTICS				
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage*	$I_C = 10 \text{ mA}, I_B = 0$	80		V
V _{(BR)CBO}	Collector-Base Breakdown Voltage	$I_C = 100 \mu A, I_E = 0$	80		V
V _{(BR)EBO}	Emitter-Base Breakdown Voltage	$I_E = 100 \mu A, I_C = 0$	5.0		V
I _{CBO}	Collector-Cutoff Current	$V_{CB} = 60 \text{ V}, I_{E} = 0$		0.1	μΑ
				1	_
	Emitter-Cutoff Current ACTERISTICS*	V _{EB} = 5.0 V, I _C = 0		0.1	μА
ON CHAR	ACTERISTICS* DC Current Gain	I _C = 50 mA, V _{CE} = 1.0 V I _C = 250 mA, V _{CE} = 1.0 V	80 50	250	μΑ
ON CHARA	ACTERISTICS* DC Current Gain	I _C = 50 mA, V _{CE} = 1.0 V I _C = 250 mA, V _{CE} = 1.0 V I _C = 500 mA, V _{CE} = 1.0 V		250	
ON CHARA	ACTERISTICS* DC Current Gain Collector-Emitter Saturation Voltage	I _C = 50 mA, V _{CE} = 1.0 V I _C = 250 mA, V _{CE} = 1.0 V I _C = 500 mA, V _{CE} = 1.0 V I _C = 250 mA, I _B = 10 mA	50	250 0.35	V
h _{FE}	ACTERISTICS* DC Current Gain	I _C = 50 mA, V _{CE} = 1.0 V I _C = 250 mA, V _{CE} = 1.0 V I _C = 500 mA, V _{CE} = 1.0 V	50	250	
ON CHARA hFE VCE(sat) VBE(on) SMALL SIG	ACTERISTICS* DC Current Gain Collector-Emitter Saturation Voltage	I _C = 50 mA, V _{CE} = 1.0 V I _C = 250 mA, V _{CE} = 1.0 V I _C = 500 mA, V _{CE} = 1.0 V I _C = 250 mA, I _B = 10 mA	50	250 0.35	V
ON CHARA hFE VCE(sat) VBE(on)	ACTERISTICS* DC Current Gain Collector-Emitter Saturation Voltage Base-Emitter On Voltage GNAL CHARACTERISTICS	$\begin{split} I_{C} &= 50 \text{ mA}, \ V_{CE} = 1.0 \ V \\ I_{C} &= 250 \text{ mA}, \ V_{CE} = 1.0 \ V \\ I_{C} &= 500 \text{ mA}, \ V_{CE} = 1.0 \ V \\ I_{C} &= 250 \text{ mA}, \ I_{B} = 10 \text{ mA} \\ I_{C} &= 250 \text{ mA}, \ V_{CE} = 1.0 \ V \end{split}$	50 20	250 0.35 1.2	V

^{*}Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 1.0%

Typical Characteristics







NPN General Purpose Amplifier


(continued)


Typical Characteristics (continued)






Collector-Cut off Current vs Ambient Temperature






Gain Bandwidth Product

Sollector Current









NPN General Purpose Amplifier (continued)

Typical Characteristics (continued)








TO-226AE Tape and Reel Data, continued


TO-226AE Reeling Style Configuration: Figure 2.0

Machine Option "A" (H)



Style "A" D26Z, D70Z (s/h)


Machine Option "E"(J)



Style "E" D27Z, D71Z (s/h)

TO-226AE Radial Ammo Packaging

Configuration: Figure 3.0



FIRST WIRE OFF IS EMITTER (ON PKG. 92) ADHESIVE TAPE IS ON THE TOP SIDE FLAT OF TRANSISTOR IS ON BOTTOM



FIRST WIRE OFF IS COLLECTOR ADHESIVE TAPE IS ON BOTTOM SIDE FLAT OF TRANSISTOR IS ON TOP


TO-226AE Tape and Reel Data, continued TO-226AE Tape and Reel Taping Dimension Configuration: Figure 4.0 ITEM DESCRIPTION SYMBOL DIMENSION Base of Package to Lead Bend 0.098 (max) Component Height Hb 1.078 (+/- 0.050) User Direction of Feed 0.630 (+/- 0.020) Lead Clinch Height HO Component Base Height H1 0.748 (+/- 0.020) Component Alignment (side/side) Pd 0.040 (max) 0.031 (max) Component Alignment (front/back) Hd 0.500 (+/- 0.020) Component Pitch РО Feed Hole Pitch 0.500 (+/- 0.008) Hole Center to First Lead P1 0.150 (+0.009, -0.010) Hole Center to Component Center P2 0.247 (+/- 0.007) Lead Spread F1/F2 0.104 (+/- 0 010) Lead Thickness d 0.018 (+0.002, -0.003) 0.429 (max) Cut Lead Length Taped Lead Length 0.209 (+0.051, -0.052) L1 Taped Lead Thickness 0.032 (+/- 0.006) Carrier Tape Thickness t1 0.021 (+/- 0.006) TO-226AE Reel Carrier Tape Width 0.708 (+0.020, -0.019) W Configuration: Figure 5.0 Hold - down Tape Width wo 0.236 (+/- 0.012) 0.035 (max) Hold - down Tape position W1 0.360 (+/- 0.025) W2 Feed Hole Position 0.157 (+0.008, -0.007) Sprocket Hole Diameter DO 0.004 (max) Lead Spring Out S Note: All dmensions are in inches. D4 ITEM DESCRIPTION SYMBOL MINIMUM MAXIMUM Red Diameter 13975 14025 Arbor Hole Diameter (Standard) 1.200 D2 1.160 D2 0.650 0.700 (Small Hole) Core Diameter D3 3.100 3.300 Hub Recess Inner Diameter D4 3.100 Hub Recess Depth W 1 0.370 0.570 Range to Range Inner Width W2 1.630 1.690 Hub to Hub Center Width 2.090 WЗ Note: All dimensions are inches

TO-226AE Package Dimensions



TO-226AE (FS PKG Code 95, 99)








Scale 1:1 on letter size paper

Dimensions shown below are in: inches [millimeters]

Part Weight per unit (gram): 0.300








	PIN	99	95				
	1	Е	Е				
	2	В	С				
	3	С	В				
TO-226AE (95,99)							

For leadformed option ordering, refer to Tape & Reel data information.

SOT-223 Tape and Reel Data FAIRCHILD SEMICONDUCTOR TM **SOT-223 Packaging** Configuration: Figure 1.0 Customized Label **Packaging Description:** Packaging Description: SOT-223 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate reason. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 2,500 units per 13° o 330cm diameter reel. The reels are dark blue in color and is made of polystyrene plastic (anti-static coated). Other option comes in 500 units per 7° or 177cm diameter reel. This and some other options are further described in the Packaging Information table. F63TNR Label Antistatic Cover Tape These full reles are individually barcode labeled and placed inside a standard intermediate box (illustrated in figure 1.0) made of recyclable corrugated brown paper. One box contains two reels maximum. And these boxes are placed inside a barcode labeled shipping box which comes in different sizes depending on the number of parts Static Dissipative shipped. **Embossed Carrier Tape** Packaging Option no flow code **SOT-223 Unit Orientation** TNR Packaging type TNR Qty per Reel/Tube/Bag 2,500 500 Reel Size 13" Dia 7" Dia Box Dimension (mm) 343x64x343 184x187x47 Max qty per Box 5.000 1.000 343mm x 342mm x 64mm Weight per unit (gm) 0.1246 0.1246 F63TNR Label Intermediate box for Standard Weight per Reel (kg) 0.7250 0.1532 F63TNR Label F63TNR Label sample 184mm x 184mm x 47mm QTY: 3000 Pizza Box for D84Z Option **SOT-223 Tape Leader and Trailer** SPEC REV: CPN: D/C1: D9842 D/C2: Configuration: Figure 2.0 QTY1 QTY2 (F63TNR)3 \bigcirc \bigcirc 0 0 \bigcirc \circ 0 \bigcirc 0 0 Components Trailer Tape Leader Tape 300mm minimum or 500mm minimum or 38 empty pockets 62 empty pockets



SOT-223 Embossed Carrier Tape






	Dimensions are in millimeter													
Pkg type	Α0	В0	w	D0	D1	E1	E2	F	P1	P0	K0	Т	Wc	Тс
SOT-223 (12mm)	6.83 +/-0.10	7.42 +/-0.10	12.0 +/-0.3	1.55 +/-0.05	1.50 +/-0.10	1.75 +/-0.10	10.25 min	5.50 +/-0.05	8.0 +/-0.1	4.0 +/-0.1	1.88 +/-0.10	0.292 +/- 0.0130	9.5 +/-0.025	0.06 +/-0.02

Notes: A0, B0, and K0 dimensions are determined with respect to the EIA/Jedec RS-481 rotational and lateral movement requirements (see sketches A, B, and C).



Sketch A (Side or Front Sectional View)
Component Rotation




Sketch B (Top View)
Component Rotation



Sketch C (Top View)
Component lateral movement


DETAIL AA




	Dimensions are in inches and millimeters								
Tape Size	Reel Option	Dim A	Dim B	Dim C	Dim D	Dim N	Dim W1	Dim W2	Dim W3 (LSL-USL)
12mm	7" Dia	7.00 177.8	0.059 1.5	512 +0.020/-0.008 13 +0.5/-0.2	0.795 20.2	5.906 150	0.488 +0.078/-0.000 12.4 +2/0	0.724 18.4	0.469 - 0.606 11.9 - 15.4
12mm	13" Dia	13.00 330	0.059 1.5	512 +0.020/-0.008 13 +0.5/-0.2	0.795 20.2	7.00 178	0.488 +0.078/-0.000 12.4 +2/0	0.724 18.4	0.469 - 0.606 11.9 - 15.4




SOT-223 (FS PKG Code 47)





Scale 1:1 on letter size paper

Part Weight per unit (gram): 0.1246



TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

 $ACEx^{TM}$ FASTr™ PowerTrench® SyncFET™ Bottomless™ QFET™ TinyLogic™ GlobalOptoisolator™ QSTM UHC™ CoolFET™ GTO™ **VCX**TM $CROSSVOLT^{TM}$ QT Optoelectronics™ HiSeC™

DOME™ ISOPLANAR™ Quiet Series™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative