



ON Semiconductor®

Top Tips: Leverage SiC for Energy Efficient Power Electronics



ON Semiconductor®

Top Tips: Leverage SiC for Energy Efficient Power Electronics

Introduction

As you are designing new power electronic products, your goals get tougher each passing year. High efficiency tops the list, but higher power is another feature that must be achieved in a smaller size at lower cost. SiC MOSFETs are a solution that will meet those goals. The following Top Tips are designed to help you create a switching supply based upon SiC semiconductors for application areas such as solar power systems, energy storage systems, and EV charging stations.

Why Choose SiC?

To justify your selection of SiC as the power semiconductor of choice for your switch-mode design, consider these standout characteristics. SiC devices can operate at higher voltages, higher frequencies, and higher temperatures than standard or super junction MOSFETs or even IGBTs. They can significantly eliminate most of the power losses of other devices, thereby providing better than 90% efficiency in most applications. Initially, SiC devices were more expensive than other MOSFETs or IGBTs. Today, those prices have dropped considerably, making SiC an attractive alternative.

Compare SiC vs. GaN

Both SiC and GaN devices are members of that wide band gap (WBG) category of devices that are steadily replacing standard Si MOSFETs. Because they can operate at much higher frequencies, the GaN devices are more widely used in RF power applications. The SiC devices can generally withstand more voltage, current, and power than the GaN devices. They switch faster and are more efficient, making them suited to switch-mode power supply applications. And, SiC MOSFETs do incorporate a body diode.

Consider Performance

A significant feature of SiC is that its thermal conductivity is more than three times that of Si or GaN. SiC based products operate at much higher temperatures, +175°C, while conduction loss stays relatively flat over temperature. Another performance factor is extremely low RDSon that can be in the range of 15 miliohms or less; it can achieve that specification even with high operating voltages. That greatly reduces power losses, thereby boosting efficiency.

As you are designing new power electronic products, your goals get tougher each passing year. High efficiency tops the list, but higher power is another feature that must be achieved in a smaller size at lower cost. SiC MOSFETs are a solution that will meet those goals. The following Top Tips are designed to help you create a switching supply based upon SiC semiconductors for application areas such as solar power systems, energy storage systems, and EV charging stations.

Select a Topology

In addition to the standard half-bridge and full bridge circuits, two other topologies are being widely adopted for use with SiC devices. These are bidirectional converters and Vienna rectifiers. The bidirectional configuration is essentially a DC-DC converter of the buck-boost type that can be configured to provide two different voltage buses that can exchange power as needed. This arrangement is ideal for vehicles with two battery buses as in all EV and mild-hybrid EVs. The two buses ideally can draw upon one another for charging. ICs implementing the bidirectional converter are available

Another topology being increasingly deployed is the Vienna rectifier. This is a three-phase, three-level PWM controlled bridge rectifier. Its primary application is power factor correction (PFC) in high power AC-to-DC power supplies.

Determine Voltage and Current Needs

In over 90% of current applications, a SiC device can replace an IGBT. Today, few if any new designs incorporate IGBTs. IGBTs can withstand high voltages up to about 1900 volts but are slow in switching. SiC devices can handle the high voltage and current levels but switch significantly faster. SiC transistors are available with upper voltage limits of 1800 volts so make a good IGBT replacement. They can not only boost performance and increase efficiency by being able to switch at higher frequencies but also result in a much smaller package.

Pay Attention to the Gate Drivers

SiC transistors require more gate drive voltage than other MOSFETs. The typical SiC transistor needs 15 to 20 volts on the gate to turn it on and -3 to -5 volts to turn off the device. However, most SiC vendors have addressed this need with special gate driver ICs, making it easy to design with SiC devices.

Use Modules Where Available

A module is a complete pre-wired MOSFET circuit in a package optimized for size and thermal capability. An example is a three-phase bridge module designed to drive a three-phase motor. Other configurations are connected to create DC-DC converters or three-phase rectifiers. Modules integrate both SiC MOSFETs and SiC diodes to ensure lower conduction and switching losses. This arrangement implements high efficiency and superior reliability in a power product.

Modules contain a temperature sensor like a thermistor to provide a way to monitor the heat level and provide some type of circuit protection or temperature control. Modules can significantly reduce your design time and enable smaller packaging. A desirable target for a new design is 90% modules and 10% other discrete components.

Find a Reliable Supplier

When working with sophisticated devices like SiC transistors and circuits, it is helpful to have a source that can not only supply the product but also provide design solutions, information, and assistance. ON Semiconductor is that kind of supplier since it is a full-service vendor of semiconductor devices and offers the advantage of a complete internal end-to-end supply chain.

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Email Requests to: orderlit@onsemi.com

ON Semiconductor Website: www.onsemi.com

TECHNICAL SUPPORT

North American Technical Support:
Voice Mail: 1 800-282-9855 Toll Free USA/Canada
Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative