

I3T25

Process Technology I3T25: 0.35 μm Process Technology



ON Semiconductor®

www.onsemi.com

Overview

Providing the density of a 0.35 μm digital process, analog/mixed-signal capability and high voltage, the Intelligent Interface Technology I3T25 process from ON Semiconductor is the answer to the need for increased digital content in a mixed-signal and/or high voltage environment. Featuring high voltage devices up to 18 V as well as digital and analog operation at 3.3 V and 12 V, the I3T25 process family features a wide range of capabilities in a single IC.

Features

- 3 to 5 Metal Layers
- Metal to Metal (MIM) Linear Capacitors
- Poly to Poly Capacitors
- High and Medium Resistivity Polysilicon Resistors
- Floating HV Thick/Thin ox NDMOS and PDMOS Transistors
- Floating Low-voltage Diodes
- Schottky Diode
- Medium-voltage PNP and NPN Bipolar Transistors
- Zener Zap Diode OTP
- Buried Zener Diode for Clamping
- Medium-voltage Floating Metal Capacitors
- Deep N + Doped Guard Rings

PROCESS CHARACTERISTICS

Operating Voltage	3.3, 12 V
Substrate Material	N-epitaxy on P-sub, Retrograde Wells
Drawn Transistor Length	0.35 μm
Gate Oxide Thickness	7/~30 nm
Contact/Via Size	0.4 μm
Contacted Gate Pitch	1.3 μm
Top Metal Thickness	845 nm
Metal Pitch	
Metal 1	1.0 μm
Metal 2	1.1 μm
Top Metal	1.4 μm
Metal Composition	Al/Cu
Isolation	LOCOS
ILD Planarization	PSG/PETEOS/ +CMP
IMD Planarization	PETEOS+CMP

SAMPLE PROCESS OPTIONS

	Mask Layers
3 Metal, 25 V HIPO, OTP	19
4 Metal, 25 V HIPO, OTP	21
5 Metal, 25 V HIPO, OTP	23
Thick Oxide	+3
Poly Poly Cap	+1
MIMC	+1

DEVICE CHARACTERISTICS

All Values Typical at 25°C

LOW-VOLTAGE TRANSISTORS

NMOS Transistor	Typical Value	Units
Vt (10/0.35, linear extrapolated)	0.59	V
Vmax = Vbd	3.6	V
IDS (10/0.35, Vds = Vgs = 3.3 V)	530	μA/μm
PMOS Transistor	Typical Value	Units
Vt (10/0.35, linear extrapolated)	-0.57	V
Vmax = Vbd	-3.6	V
IDS (10/0.35, Vds = Vgs = 3.3 V)	-250	μA/μm

THICK OXIDE HIGH-VOLTAGE TRANSISTORS (EXTENDED DRAIN)

Floating NDMOS (18 V)	Typical Value	Units
Vt (Vd = 0.1 V)	1.3	V
Vbd (Vgs = 0)	31	V
Vgsmax	12	V
Vdsmax, SOA* (Vgs = Vgsmax, full lifetime)	12	V
Vdsmax, (Vgs full lifetime)	18	V
Ron*Area (Vg = 18 V, Vd = 0.5 V)	27	mΩ*mm ²
Ids	260	μA/μm
Floating PDMOS (18 V)	Typical Value	Units
Vt (Vd = 0.1 V)	-1.3	V
Vbd (Vgs = 0)	-35	V
Vgsmax	-12	V
Vdsmax, SOA* (Vgs = Vgsmax, full lifetime)	-12	V
Vdsmax, (Vgs full lifetime)	-18	V
Ron*Area (Vg = 18 V, Vd = 0.5 V)	71	mΩ*mm ²
Ids	-110	μA/μm

* Symmetric Device Available

THIN OXIDE HIGH-VOLTAGE TRANSISTORS (EXTENDED DRAIN)

Floating NDMOS	Typical Value	Units
Vt (Vd = 0.1 V)	0.6	V
Vbd (Vgs = 0)	31	V
Vgsmax	3.6	V
Vdsmax, SOA* (Vgs = Vgsmax, full lifetime)	12	V
Vdsmax, (Vgs full lifetime)	18	V
Ron*Area (Vg = 3.3 V, Vd = 0.5 V)	35	mΩ*mm ²
Ids	280	μA/μm
Floating PDMOS	Typical Value	Units
Vt (Vd = 0.1 V)	-0.6	V
Vbd (Vgs = 0)	-28	V

Vgsmax	-3.6	V
Vdsmax, SOA* (Vgs = Vgsmax, full lifetime)	-12	V
Vdsmax, (Vgs full lifetime)	-18	V
Ron*Area (Vg = 3.3 V, Vd = 0.5 V)	75	mΩ*mm ²
Ids	-121.5	μA/μm

* Symmetric Device Available

THICK OXIDE HIGH-VOLTAGE TRANSISTORS (NESTED DRAIN)

Floating NDMOS (12 V)	Typical Value	Units
Vt (Vd = 0.1 V)	1.3	V
Vbd (Vgs = 0)	21	V
Vgsmax	12	V
Vdsmax, SOA* (Vgs = Vgsmax, full lifetime)	8	V
Vdsmax, (Vgs full lifetime)	12	V
Ron*Area (Vg = 18 V, Vd = 0.5 V)	15	mΩ*mm ²
Ids	260	μA/μm
Floating PDMOS (12 V)	Typical Value	Units
Vt (Vd = 0.1 V)	-1.4	V
Vbd (Vgs = 0)	-21	V
Vgsmax	-12	V
Vdsmax, SOA* (Vgs = Vgsmax, full lifetime)	-8	V
Vdsmax, (Vgs full lifetime)	-12	V
Ron*Area (Vg = 18 V, Vd = 0.5 V)	75	mΩ*mm ²
Ids	-92	μA/μm

* Symmetric Device Available

BIPOLAR TRANSISTORS

Bipolar Transistors Vertical Low-Voltage NPN (Parameter, E_area = 3.61 μm²)	Typical Value	Units
Hfe @ Ic = 10 μA	17.3	-
Bvceo @ Ic = 1 μA	20.5	V
Bvces @ Ic = 1 μA	20.9	V
Vertical Low-Voltage PNP Transistor (Parameter, E_area = 0.64 μm²)	Typical Value	Units
Hfe @ Ic = 10 μA	20.1	-
Bvceo @ Ic = 1 μA	-14.5	V
Bvces @ Ic = 1 μA	-19.5	V

DIODES

Zener Diode: PBZD (a = 2 μm)	Typical Value	Units
Vz @ 100 μA	4.6	V
Rzener	45	Ω
Ileak @ Vz = 0.5 V	200	nA

Zapping Zener Diode for OTP: UZZD		
	Typical Value	Units
Vz @ 1 μA	1.5	V
Vbd @ 10 mA	4.5	V
Ileak @ Vz = 1 V	1.4	V
Poly Diode for Gate Clamping: POLYD		
	Typical Value	Units
Vreverse @ Ia = 10 μA	6.8	V
Schottky		
Vbd @ 1 μA	15	V
ILeak @ 5.5	< 20	nA

CAPACITORS (PARAMETER @ 25°C)

Type (Maximum Voltage)	Typical Value	Units
Metal2 / Metal2.5 Plate: MIMC (3.6 V)	1.5	fF/μm ²
Poly Poly Capacitor (13.2 V)	1	fF/μm ²

RESISTORS (PARAMETER @ 25°C)

Resistor Type	Typical Value	Units
High-Resistance Poly: HIPO	975	Ω/square
Salicided P+ Poly: LOPOR	2.4	Ω/square
Unsalicided P+ Poly: PPOLR	240	Ω/square
Unsalicided P+ in Mwell	64	Ω/square
Unsalicided N+ Poly: NPOLR	292	Ω/square
Unsalicided P+ in Pwell	47.5	Ω/square
Nwell under FOX (field oxide)	958	Ω/square
Nwell in AA (active area)	800	Ω/square
Pwell in AA (active area)	1755	Ω/square

LIBRARIES

All Values Typical at 25°C

Standard Cell	
Ultra High Density Core Shell	pn sum: 2.0
	Area of 2-input nand (na21): 38.88 μm ²
	Gate density (na21 @ 100% utilization): 25.72 k gates/mm ²
	Scan Flop density (scan flops @ 100% utilization): 3.215 k ff/mm ²
	Average power (@ 3.3 V): 0.2929 μW/MHz/gate
Core Cell Level Shifters	Unidirectional: 1 cell optimized for speed, pad high to core low
Standard I/O	
Fat Pad I/O Library (for core limited designs)	172.80 μm min in-line pad pitch
	180.00 μm pad height


Tall Pad I/O Library (for pad limited designs)	86 μm min in-line pad pitch
	322.50 μm pad height

MEMORY OPTIONS

RAM	
Synchronous High Speed / High Temp Single Port SRAM	Minimum: 16 words x 2 bits
	Maximum: 128 k bits (i.e: 16 k words x 8 bits, 8 k words x 16 bits, ...)
Synchronous High Speed / High Temp Dual Port SRAM	Minimum: 16 words x 2 bits
	Maximum: 128 k bits (i.e: 16 k words x 8 bits, 8 k words x 16 bits, ...)
Low Power Synchronous SRAM	Minimum: 64 words x 4 bits
	Maximum: 128 k bits (i.e: 16 k words x 8 bits, 8 k words x 16 bits, ...)
ROM	
Synchronous High Speed / High Temp Diffusion ROM	Minimum: 256 words x 4 bits
	Maximum: 512 k bits (i.e: 64 k words x 8 bits, 32 k words x 16 bits, ...)
Low Power Synchronous Via Programmable ROM	Minimum: 256 words x 4 bits
	Maximum: 512 k bits (i.e: 64 k words x 8 bits, 32 k words x 16 bits, ...)
Non-Volatile Memory	
OTP – One Time Programmable	Fuse: Zener Diode optimized for low power zapping
	Both Serial and Parallel Output Capability
	In field programming available
	Vector: Up to 320 bits
EEPROM – No Additional Masks or Processing Steps	Differential Bit Cell (Redundancy for High Reliability)
	2 ms Write/Erase
	Array: up to 8 k bits (128 x 64), Vector: 8 to 64 bits (1 x 8 to 1 x 64)
	Internal Charge Pump provided
	Memory Failure Rate: < 10 ppm, < 1 ppm with ECC (128 x 56)
	Automotive qualification AEC-Q100

CAD TOOL COMPATIBILITY

Digital Design	Synopsys Design Compiler
	Cadence Verilog
Analog Design	Cadence DFII (4.4.6)
	Cadence Spectre
Place and Route	Synopsys Apollo
	Cadence Silicon Ensemble
Physical Verification	Mentor graphics Calibre

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com
Order Literature: <http://www.onsemi.com/orderlit>
For additional information, please contact your local
Sales Representative