# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# 1.4 A Switching Regulator with 5.0 V, 100 mA Linear Regulator with Watchdog, RESET and ENABLE

The CS5111 is a dual output power supply integrated circuit. It contains a  $5.0~V\pm2\%$ , 100~mA linear regulator, a watchdog timer, a linear output voltage monitor to provide a Power On Reset (POR) and a 1.4~A current mode PWM switching regulator.

The 5.0 V linear regulator is comprised of an error amplifier, reference, and supervisory functions. It has low internal supply current consumption and provides 1.2 V (typical) dropout voltage at maximum load current.

The watchdog timer circuitry monitors an input signal (WDI) from the microprocessor. It responds to the falling edge of this watchdog signal. If a correct watchdog signal is not received within the externally programmable time, a reset signal is issued.

The externally programmable active reset circuit operates correctly for an output voltage ( $V_{LIN}$ ) as low as 1.0 V. During power up, or if the output voltage shifts below the regulation limit,  $\overline{RESET}$  toggles low and remains low for the duration of the delay after proper output voltage regulation is restored. Additionally a reset pulse is issued if the correct watchdog is not received within the programmed time. Reset pulses continue until the correct watchdog signal is received. The reset pulse width and frequency, as well as the Power On Reset delay, are set by one external RC network.

The current mode PWM switching regulator is comprised of an error amplifier with selectable feedback inputs, a current sense amplifier, an adjustable oscillator, and a 1.4 A output power switch with anti-saturation control. The switching regulator can be configured in a variety of topologies.

The CS5111 is load dump capable and has protection circuitry which includes overvoltage shutdown, current limit on the linear and switcher outputs, and an overtemperature limiter.

#### **Features**

- Linear Regulator
  - $-5.0 \text{ V} \pm 2\%$  @ 100 mA
- Switching Regulator
  - 1.4 A Peak Internal Switch
  - 120 kHz Maximum Switching Frequency
  - 5.0 V to 26 V Operating Supply Range
- Smart Functions
  - Watchdog
  - RESET
  - ENABLE
- Protection
  - Overvoltage
  - Overtemperature
  - Current Limit
- 54 V Peak Transient Capability
- Internally Fused Leads in SO-24L Package




# ON Semiconductor™

http://onsemi.com



SO-24L DWF SUFFIX CASE 751E


# MARKING DIAGRAM



A = Assembly Location

WL, L = Wafer Lot YY, Y = Year WW, W = Work Week

#### **PIN CONNECTIONS**



#### ORDERING INFORMATION

Device	Package	Shipping
CS5111YDWF24	SO-24L	31 Units/Rail
CS5111YDWFR24	SO-24L	1000 Tape & Reel




Figure 1. Block Diagram

# **ABSOLUTE MAXIMUM RATINGS\***

	Rating	Value	Unit
Logic Inputs/Outputs (ENABLE, SELECT,	WDI, RESET)	−0.3 to V <sub>LIN</sub>	V
V <sub>LIN</sub>		-0.3 to 10	
V <sub>IN</sub> , V <sub>REG</sub> :	DC Input Voltage Peak Transient Voltage (40 V Load Dump @ 14 V $_{ m IN}$ )	-0.3 to 26 -0.3 to 54	V
V <sub>SW</sub> Peak Transient Voltage		54	V
C <sub>OSC</sub> , C <sub>Delay</sub> , COMP, V <sub>FB1</sub> , V <sub>FB2</sub>		–0.3 to V <sub>LIM</sub>	V
Power Dissipation		Internally Limited	_
V <sub>LIN</sub> Output Current		Internally Limited	_
V <sub>SW</sub> Output Current		Internally Limited	_
RESET Output Sink Current		5.0	mA
ESD Susceptibility (Human Body Model)		2.0	kV
ESD Susceptibility (Machine Model)		200	V
Storage Temperature		-65 to 150	°C
Lead Temperature Soldering:	Reflow: (SMD styles only) (Note 1.)	230 peak	°C

<sup>1. 60</sup> second maximum above 183°C.

<sup>\*</sup>The maximum package power dissipation must be observed.

# **CS5111**

**ELECTRICAL CHARACTERISTICS** (5.0 V  $\leq$  V<sub>IN</sub>  $\leq$  26 V and  $-40^{\circ}$ C  $\leq$  T<sub>J</sub>  $\leq$  150 $^{\circ}$ C, C<sub>OUT</sub> = 100  $\mu$ F (ESR  $\leq$  8.0  $\Omega$ ), C<sub>Delay</sub> = 0.1  $\mu$ F, R<sub>BIAS</sub> = 64.9 k $\Omega$ , C<sub>OSC</sub> = 390 pF, C<sub>COMP</sub> = 0.1  $\mu$ F; unless otherwise specified.)

Characteristic	Test Conditions	Min	Тур	Max	Unit
General					
I <sub>IN</sub> Off Current	6.6 V ≤ V <sub>IN</sub> ≤ 26 V, I <sub>SW</sub> = 0 A	_	-	2.0	mA
I <sub>IN</sub> On Current	6.6 V ≤ V <sub>IN</sub> ≤ 26 V, I <sub>SW</sub> = 1.4 A		30	70	mA
I <sub>REG</sub> Current	I <sub>LIN</sub> = 100 mA, 6.6 V ≤ V <sub>IN</sub> ≤ 26 V	_	-	6.0	mA
Thermal Limit	Guaranteed by Design	160	-	210	°C
5.0 V Regulator Section					•
V <sub>LIN</sub> Output Voltage	$6.6 \text{ V} \le \text{V}_{REG} \le 26 \text{ V},$ $1.0 \text{ mA} \le \text{I}_{LIN} \le 100 \text{ mA}$	4.9	5.0	5.1	V
Dropout Voltage	$(V_{REG} - V_{LIN})$ @ $I_{LIN} = 100 \text{ mA}$	-	1.2	1.5	٧
Overvoltage Shutdown	-	30	34	38	V
Line Regulation	6.6 V ≤ V <sub>REG</sub> ≤ 26 V, I <sub>LIN</sub> = 5.0 mA	-	5.0	25	mV
Load Regulation	V <sub>REG</sub> = 19 V, 1.0 mA ≤ I <sub>LIN</sub> ≤ 100 mA	_	5.0	25	mV
Current Limit	6.6 V ≤ V <sub>REG</sub> ≤ 26 V	120	-	_	mA
DC Ripple Rejection	14 V ≤ V <sub>REG</sub> ≤ 24 V	60	75	_	dB
RESET Section					
Low Threshold (V <sub>RTL</sub> )	V <sub>LIN</sub> Decreasing	4.05	4.25	4.45	V
High Threshold (V <sub>RTH</sub> )	V <sub>LIN</sub> Increasing	4.2	4.45	4.7	V
Hysteresis	V <sub>RTH</sub> – V <sub>RTL</sub>	140	190	240	mV
Active High	V <sub>LIN</sub> > V <sub>RTH</sub> , I <sub>RESET</sub> = -25 μA	V <sub>LIN</sub> – 0.5	-	_	V
Active Low	$V_{LIN} = 1.0 \text{ V}$ , $10 \text{ k}\Omega$ Pull–Up from RESET to $V_{LIN}$		_	0.4	V
Delay	V <sub>LIN</sub> = 4.0 V, I <sub>RESET</sub> = 1.0 mA Invalid WDI	6.25	8.78	11	ms
Power On Delay	V <sub>LIN</sub> Crossing V <sub>RTH</sub>	6.25	0.70	_	ms
Watchdog Input (WDI)	VLIN Clossing VRIH	0.23			1113
VIH	Peak WDI Needed to Activate RESET	_	_	2.0	V
VIL	- Cak WBI Needed to Activate NEEE!	0.8		_	V
Hysteresis	Note 2.	25	50	_	mV
Pull–Up Resistor	WDI = 0 V	20	50	100	kΩ
Low Threshold	-	6.25	8.78	11	ms
Floating Input Voltage	_	3.5	-	_	V
WDI Pulse Width	_	-	_	5.0	μѕ
Switcher Section				0.0	μο
Minimum Operating Input – Voltage		-	-	5.0	V
Switching Frequency	Refer to Figure 5	80	95	110	kHz
Switch Saturation Voltage	I <sub>SW</sub> = 1.4 A	0.7	1.1	1.6	V
Output Current Limit	-	1.4	_	2.5	А
	ching Frequency $V_{SW} = 7.5 \text{ V}$ with 50 $\Omega$ Load, Refer to Figure 5			1	1

<sup>2.</sup> Guaranteed by design, not 100% tested in productions.

# CS5111

**ELECTRICAL CHARACTERISTICS (continued)** (5.0 V  $\leq$  V<sub>IN</sub>  $\leq$  26 V and  $-40^{\circ}$ C  $\leq$  T<sub>J</sub>  $\leq$  150 $^{\circ}$ C, C<sub>OUT</sub> = 100 μF (ESR  $\leq$  8.0  $\Omega$ ), C<sub>Delay</sub> = 0.1 μF, R<sub>BIAS</sub> = 64.9 kΩ, C<sub>OSC</sub> = 390 pF, C<sub>COMP</sub> = 0.1 μF; unless otherwise specified.)

Characteristic	Test Conditions	Min	Тур	Max	Unit
Switcher Section (continued)		<u>.</u>			
V <sub>FB1</sub> Regulation Voltage	-	1.206	1.25	1.294	V
V <sub>FB2</sub> Regulation Voltage	-	1.206	1.25	1.294	V
V <sub>FB1</sub> , V <sub>FB2</sub> Input Current	V <sub>FB1</sub> = V <sub>FB2</sub> = 5.0 V	-	-	1.0	μΑ
Oscillator Charge Current	C <sub>OSC</sub> = 0 V	35	40	45	μΑ
Oscillator Discharge Current	C <sub>OSC</sub> = V40	270	320	370	μΑ
C <sub>Delay</sub> Charge Current	C <sub>Delay</sub> = 0 V	35	40	45	μΑ
Switcher Max Duty Cycle	$V_{SW}$ = 5.0 V with 50 $\Omega$ Load, $V_{FB1}$ = $V_{FB2}$ = 1.0 V	72	85	95	%
Current Sense Amp Gain	I <sub>SW</sub> = 2.3 A	-	7.0	-	V/V
Error Amp DC Gain	-	-	67	-	dB
Error Amp Transconductance	-	-	2700	-	μ <b>A</b> /V
ENABLE Input					
VIL	-	0.8	1.24	_	V
VIH	-	_	1.3	2.0	V
Hysteresis	-	-	60	_	mV
Input Impedance	-	10	20	40	kΩ
Select Input					
VIL (Selects V <sub>FB1</sub> )	$4.9 \le V_{LIN} \le 5.1$	0.8	1.25	_	V
VIH (Selects V <sub>FB2</sub> )	4.9 ≤ V <sub>LIN</sub> ≤ 5.1	_	1.25	2.0	V
SELECT Pull-Up	SELECT = 0 V	10	24	50	kΩ
Floating Input Voltage	-	3.5	4.5	_	V

# PIN FUNCTION DESCRIPTION

PACKAGE PIN #				
SO-24L	PIN SYMBOL	FUNCTION		
1	$V_{IN}$	Supply voltage.		
2, 3	NC	No connection.		
4	V <sub>SW</sub>	Collector of NPN power switch for switching regulator section.		
5, 6, 7, 8, 17, 18, 19, 20	GND	Connected to the heat removing leads.		
9	V <sub>FB1</sub>	Feedback input voltage 1 (referenced to 1.25 V).		
10	V <sub>FB2</sub>	Feedback input voltage 2 (referenced to 1.25 V).		
11	SELECT	Logic level input that selects either $V_{FB1}$ or $V_{FB2}$ . An open selects $V_{FB2}$ . Connect to GND to select $V_{FB1}$ .		
12	COMP	Output of the transconductance error amplifier.		
13	C <sub>OSC</sub>	A capacitor connected to GND sets the switching frequency. Refer to Figure 5.		
14	WDI	Watchdog input. Active on falling edge.		
15	C <sub>Delay</sub>	A capacitor connected to GND sets the Power On Reset and Watchdog time.		
16	RESET	RESET output. Active low if V <sub>LIN</sub> is below the regulation limit. If watchdog timeout is reached, a reset pulse train is issued.		

# **PIN FUNCTION DESCRIPTION (continued)**

PACKAGE PIN #		
SO-24L	PIN SYMBOL	FUNCTION
21	I <sub>BIAS</sub>	A resistor connected to GND sets internal bias currents as well as the $C_{OSC}$ and $C_{Delay}$ charge currents.
22	V <sub>LIN</sub>	Regulated 5.0 V output from the linear regulator section.
23	V <sub>REG</sub>	Input voltage to the linear regulator and the internal supply circuitry.
24	ENABLE	Logic level input to shut down the switching regulator.

# **TYPICAL PERFORMANCE CHARACTERISTICS**





Figure 2. 5.0 V Regulator Bias Current vs. Load Current

Figure 3. Supply Current vs. Switch Current








Figure 5. Oscillator Frequency (kHz) vs.  $C_{OSC}$  (pF), Assuming  $R_{BIAS}$  = 64.9 k $\Omega$ 

#### CIRCUIT DESCRIPTION




Figure 6. Block Diagram of 5.0 V Linear Regulator Portion of the CS5111

#### **5.0 V LINEAR REGULATOR**

The 5.0 V linear regulator consists of an error amplifier, bandgap voltage reference, and a composite pass transistor.

The 5.0 V linear regulator circuitry is shown in Figure 6. When an unregulated voltage greater than 6.6 V is applied to the  $V_{REG}$  input, a 5.0 V regulated DC voltage will be present at  $V_{LIN}$ . For proper operation of the 5.0 V linear regulator, the  $I_{BIAS}$  lead must have a 64.9 k $\Omega$  pull down resistor to ground. A 100  $\mu F$  or larger capacitor with an ESR  $<8.0~\Omega$  must be connected between  $V_{LIN}$  and ground. To operate the 5.0 V linear regulator as an independent regulator (i.e. separate from the switching supply), the input voltage must be tied to the  $V_{REG}$  lead.

As the voltage at the V<sub>REG</sub> input is increased, Q<sub>1</sub> is turned on. Q<sub>1</sub> provides base drive for Q<sub>2</sub> which in turn provides base current for  $Q_3$ . As  $Q_3$  is turned on, the output voltage, V<sub>LIN</sub>, begins to rise as Q<sub>3</sub>'s output current charges the output capacitor, COUT. Once VLIN rises to a certain level, the error amplifier becomes biased and provides the appropriate amount of base current to Q<sub>1</sub>. The error amplifier monitors the scaled output voltage via an internal voltage divider, R<sub>2</sub> through R5, and compares it to the bandgap voltage reference. The error amplifier output or error signal is an output current equal to the error amplifier's input differential voltage times the transconductance of the amplifier. Therefore, the error amplifier varies the base current to  $Q_1$ , which provides bias to  $Q_2$  and  $Q_3$ , based on the difference between the reference voltage and the scaled V<sub>LIN</sub> output voltage.

#### **CONTROL FUNCTIONS**

The watchdog timer circuitry monitors an input signal (WDI) from the microprocessor. It responds to the falling

edge of this watchdog signal which it expects to see within an externally programmable time (see Figure 7).

The watchdog time is given by:

$$t_{WDI} = 1.353 \times C_{Delay}R_{BIAS}$$

Using  $C_{Delay}=0.1~\mu F$  and  $R_{BIAS}=64.9~k\Omega$  gives a time ranging from 6.25 ms to 11 ms assuming ideal components. Based on this, the software must be written so that the watchdog arrives at least every 6.25 ms. In practice, the tolerance of  $C_{Delay}$  and  $R_{BIAS}$  must be taken into account when calculating the minimum watchdog time  $(t_{WDI})$ .





Figure 7. Timing Diagram for Normal Regulator Operation

If a correct watchdog signal is not received within the specified time a reset pulse train is issued until the correct watchdog signal is received. The nominal reset signal in this case is a 5 volt square wave with a 50% duty cycle as shown in Figure 8.



A: Watchdog waiting for low–going transition on WDI B:  $\overline{\text{RESET}}$  stays low for  $t_{\text{WDI}}$  time

Figure 8. Timing Diagram When WDI Fails to Appear Within the Preset Time Interval, two

The RESET signal frequency is given by:

$$f_{RESET} = \frac{1}{2(t_{WDI})}$$

The Power On Reset (POR) and low voltage  $\overline{RESET}$  use the same circuitry and issue a reset when the linear output voltage is below the regulation limit. After  $V_{LIN}$  rises above the minimum specified value,  $\overline{RESET}$  remains low for a fixed period  $t_{POR}$  as shown in Figures 9 and 10.




Figure 9. The Power On Reset Time Interval (t<sub>POR</sub>) Begins When V<sub>LIN</sub> Rises Above 4.45 V (Typical)




Figure 10. RESET Signal Is Issued Whenever V<sub>LIN</sub> Falls Below 4.25 V (Typical)

The POR delay (t<sub>POR</sub>) is given by:

$$tpor = 1.353 \times CpelayRBIAS$$

#### **CURRENT MODE PWM SWITCHING CIRCUITRY**

The current mode PWM switching voltage regulator contains an error amplifier with selectable feedback inputs, a current sense amplifier, an adjustable oscillator and a 1.4 A output power switch with antisaturation control. The switching regulator and external components, connected in a boost configuration, are shown in Figure 11.

The switching regulator begins operation when  $V_{REG}$  and  $V_{IN}$  are raised above 5 volts.  $V_{REG}$  is required since the switching supply's control circuitry is powered through  $V_{LIN}$ .  $V_{IN}$  supplies the base drive to the switcher output transistor.

The output transistor turns on when the oscillator starts to charge the capacitor on C<sub>OSC</sub>. The output current will develop a voltage drop across the internal sense resistor (R<sub>S</sub>). This voltage drop produces a proportional voltage at the output of the current sense amplifier, which is compared to the output of the error amplifier. The error amplifier generates an output voltage which is proportional to the difference between the scaled down output boost voltage (V<sub>FB1</sub> or V<sub>FB2</sub>) and the internal bandgap voltage reference. Once the current sense amplifier output exceeds the error amplifier's output voltage, the output transistor is turned off.

The energy stored in the inductor during the output transistor on time is transferred to the load when the output transistor is turned off. The output transistor is turned back on at the next rising edge of the oscillator. On a cycle by cycle basis, the current mode controller in a discontinuous mode of operation charges the inductor to the appropriate amount of energy, based on the energy demand of the load. Figure 12 shows the typical current and voltage waveforms for a boost supply operating in the discontinuous mode.

# Notes:

- 1. Refer to Figure 5 to determine oscillator frequency.
- 2. The switching regulator can be disabled by providing a logic high at the <u>ENABLE</u> input.
- 3. The boost output voltage can be controlled dynamically by the feedback select input. If select is open,  $V_{FB2}$  is selected. If select is low, then  $V_{FB1}$  is selected.




Figure 11. Block Diagram of the 1.4 A Current Mode Control Switching Regulator Portion of the CS5111 in a Boost Configuration




Figure 12. Voltage and Current Waveforms for Boost Topology in CS5111

#### PROTECTION CIRCUITRY

If the input voltage at  $V_{REG}$  is increased above the overvoltage threshold, the drive to the linear and switcher output transistors is shut off. Therefore,  $V_{LIN}$  is disabled and  $V_{SW}$  can not be pulled low.

The current out of  $V_{LIN}$  is sensed in order to limit excessive power dissipation in the linear output transistor over the output range of 0 V to regulation. Also, the current into  $V_{SW}$  is sensed in order to provide the current limit function in the switcher output transistor.

If the die temperature is increased above  $160^{\circ}\text{C}$ , either due to excessive ambient temperature or excessive power dissipation, the drive to the linear output transistor is reduced proportionally with increasing die temperature. Therefore,  $V_{LIN}$  will decrease with increasing die temperature above  $160^{\circ}\text{C}$ . Since the switcher control circuitry is powered through  $V_{LIN}$ , the switcher performance, including current limit, will be affected by the decrease in  $V_{LIN}$ .

#### **APPLICATION NOTES**

#### **DESIGN PROCEDURE FOR BOOST TOPOLOGY**

This section outlines a procedure for designing a boost switching power supply operating in the discontinuous mode.

#### Step 1

Determine the output power required by the load.

$$POUT = IOUTVOUT$$
 (1)

#### Step 2

Choose  $C_{OSC}$  based on the target oscillator frequency with an external resistor value,  $R_{BIAS} = 64.9 \text{ k}\Omega$  (See Figure 5).

#### Step 3

Next select the output voltage feedback sense resistor divider as follows (Figure 13).

For  $V_{FB1}$  active, choose a value for  $R_1$  and then solve for  $R_{EO}$  where:

$$REQ = \frac{R_1}{\frac{VOUT}{VFB1} - 1}$$
 (2)

For V<sub>FB2</sub> active, find:

$$V_{FB1} = V_{OUT} \left( \frac{R_{EQ}}{R_1 + R_{EQ}} \right)$$
 (3)

and then calculate R2 where:

$$R_2 = \frac{V_{R2}}{I_{R2}} = \frac{V_{FB1} - V_{FB2}}{V_{FB1}/R_{EQ}}$$
 (4)

Then find  $R_3$ , where:

$$R_3 = R_{EQ} - R_2 \tag{5}$$




Figure 13. Feedback Sense Resistor Divider Connected Between V<sub>OUT</sub> and Ground

### Step 4

Determine the maximum on time at the minimum oscillator frequency and  $V_{IN}$ . For discontinuous operation, all of the stored energy in the inductor is transferred to the load prior to the next cycle. Since the current through the inductor cannot change instantaneously and the inductance is constant, a volt–second balance exists between the on time and off time. The voltage across the inductor during the on cycle is  $V_{IN}$  and the voltage across the inductor during the off cycle is  $V_{OUT}-V_{IN}$ . Therefore:

$$VINTON = (VOUT - VIN)tOFF$$
 (6)

where the maximum on time is:

$$t_{ON(MAX)} \approx \left[1 - \frac{V_{IN(MIN)}}{V_{OUT(MAX)}}\right] \left[\frac{1}{f_{SW(MIN)}}\right]$$
 (7)

#### Step 5

Calculate the maximum inductance allowed for discontinuous operation:

$$L_{(MAX)} = \frac{f_{SW(MIN)}V_{IN}^{2}(MIN)t_{ON}^{2}(MAX)}{2P_{OUT}/\eta}$$
(8)

where  $\eta$  = efficiency.

Usually  $\eta = 0.75$  is a good starting point. The IC's power dissipation should be calculated after the peak current has been determined in Step 6. If the efficiency is less than originally assumed, decrease the efficiency and recalculate the maximum inductance and peak current.

#### Step 6

Determine the peak inductor current at the minimum inductance, minimum  $V_{\rm IN}$  and maximum on time to make sure the inductor current doesn't exceed 1.4 A.

$$I_{PK} = \frac{V_{IN(MIN)}t_{ON(MAX)}}{L_{(MIN)}}$$
(9)

#### Step 7

Determine the minimum output capacitance and maximum ESR based on the allowable output voltage ripple.

$$C_{OUT(MIN)} = \frac{I_{PK}}{8f\Delta V_{RIPPLE}}$$
 (10)

$$ESR(MIN) = \frac{\Delta V_{RIPPLE}}{I_{PK}}$$
 (11)

In practice, it is normally necessary to use a larger capacitance value to obtain a low ESR. By placing capacitors in parallel, the equivalent ESR can be reduced.

#### Step 8

Compensate the feedback loop to guarantee stability under all operating conditions. To do this, we calculate the modulator gain and the feedback resistor network attenuation and set the gain of the error amplifier so that the overall loop gain is 0 dB at the crossover frequency,  $f_{CO}$ . In addition, the gain slope should be -20 dB/decade at the crossover frequency.

The low frequency gain of the modulator (i.e. error amplifier output to output voltage) is:

$$\frac{\Delta V_{OUT}}{\Delta V_{EA}} = \frac{IPK(MAX)}{V_{EA}(MAX)} \sqrt{\frac{R_{LOAD}Lf}{2}}$$
 (12)

where

$$I_{PK(MAX)} = \frac{V_{EA(MAX)}/G_{CSA}}{R_S} = \frac{2.4 \text{ V/7}}{150 \text{ m}\Omega} = 2.3 \text{ A} (13)$$

The V<sub>OUT</sub>/V<sub>EA</sub> transfer function has a pole at:

$$f_{p} = 1/(\pi R_{LOAD}C_{OUT}) \tag{14}$$

and a zero due to the output capacitor's ESR at:

$$f_Z = 1/(2\pi ESR(C_{OUT})) \tag{15}$$

Since the error amplifier reference voltage is 1.25 V, the output voltage must be divided down or attenuated before being applied to the input of the error amplifier. The feedback resistor divider attenuation is:

The error amplifier in the CS5111 is an operational transconductance amplifier (OTA), with a gain given by:

$$GOTA = gmZOUT$$
 (16)

where:

$$gm = \frac{\Delta I_{OUT}}{\Delta V_{IN}}$$
 (17)

For the CS5111, gm =  $2700 \,\mu\text{A/V}$  typical.

One possible error amplifier compensation scheme is shown in Figure 14. This gives the error amplifier a gain plot as shown in Figure 15.

For the error amplifier gain shown in Figure 15, a low frequency pole is generated by the error amplifier output impedance and  $C_1$ . This is shown by the line AB with a  $-20 \, \text{dB/decade}$  slope in Figure 15. The slope changes to zero at point B due to the zero at:

$$f_Z = 1/(2\pi R_4 C_1) \tag{18}$$




Figure 14. RC Network Used to Compensate the Error Amplifier (OTA)

A pole at point C:

$$f_{p} = 1/(\pi R_{4}C_{2}) \tag{19}$$

offsets the zero set by the ESR of the output capacitors.

An alternative scheme uses a single capacitor as shown in Figure 16, to roll the gain off at a relatively low frequency.

#### Step 9

Finally the watchdog timer period and Power on Reset time is determined by:

$$t_{Delay} = 1.353 \times C_{Delay}R_{BIAS}$$
 (20)




Figure 15. Bode Plot of Error Amplifier (OTA) Gain and Modulator Gain Added to the Feedback
Resistor Divider Attenuation




Figure 16. A Typical Application Diagram with External Components Configured in a Boost Topology

# **CS5111**

# LINEAR REGULATOR OUTPUT CURRENT VS. INPUT VOLTAGE




Figure 17. The Shaded Area Shows the Safe Operating Area of the CS5111 as a Function of  $I_{LIN}$ ,  $V_{REG}$ , and  $\Theta_{JA}$ . Refer to Table 1 for Typical Loads and Voltages.


Table 1.

V <sub>REG</sub> (V)	V <sub>IN</sub> (V)	I <sub>LIN</sub> (mA)	Linear Power Dissipation (W)	Worst Case Switcher Power Available (⊖ <sub>JA</sub> = 55°C/W) (W)	Worst Case Switcher Power Available (⊖ <sub>JA</sub> = 35°C/W) (W)
20	14	25	0.44	0.74	1.42
20	14	50	0.83	0.35	1.03
20	14	75	1.22	*	0.64
20	14	100	1.60	*	0.26
25	14	25	0.60	0.58	1.26
25	14	50	1.11	0.07	0.75
25	14	75	1.62	*	0.24
25	14	100	2.14	*	*

<sup>\*</sup>Subjecting the CS5111 to these conditions will exceed the maximum total power that the part can handle, thereby forcing it into thermal limit.

# **PACKAGE DIMENSIONS**

SO-24L **DWF SUFFIX** CASE 751E-04 ISSUE E



- NOTES:
  1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
  2. CONTROLLING DIMENSION: MILLIMETER.
  3. DIMENSIONS A AND B DO NOT INCLUDE MOLD PROTRUSION.
  4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER SIDE
  - 4. MIXAMOM MIDDL PROTRUSION 0.13 (0.006)
    PER SIDE.
    5. DIMENSION D DOES NOT INCLUDE DAMBAR
    PROTRUSION. ALLOWABLE DAMBAR
    PROTRUSION SHALL BE 0.13 (0.005) TOTAL IN
    EXCESS OF D DIMENSION AT MAXIMUM
    MATERIAL CONDITION.

	MILLIN	IETERS	INC	HES
DIM	MIN	MAX	MIN	MAX
Α	15.25	15.54	0.601	0.612
В	7.40	7.60	0.292	0.299
С	2.35	2.65	0.093	0.104
D	0.35	0.49	0.014	0.019
F	0.41	0.90	0.016	0.035
G	1.27 BSC		0.050	BSC
J	0.23	0.32	0.009	0.013
K	0.13	0.29	0.005	0.011
M	0 °	8°	0°	8°
P	10.05	10.55	0.395	0.415
R	0.25	0.75	0.010	0.029

#### **PACKAGE THERMAL DATA**

Parameter	SO-24L	Unit	
$R_{\Theta JC}$	Typical	9	°C/W
$R_{\Theta JA}$	Typical	55	°C/W

# **Notes**

# **Notes**

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affliliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

# **PUBLICATION ORDERING INFORMATION**

# NORTH AMERICA Literature Fulfillment:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA

**Phone**: 303–675–2175 or 800–344–3860 Toll Free USA/Canada **Fax**: 303–675–2176 or 800–344–3867 Toll Free USA/Canada

Email: ONlit@hibbertco.com

Fax Response Line: 303-675-2167 or 800-344-3810 Toll Free USA/Canada

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

EUROPE: LDC for ON Semiconductor - European Support

German Phone: (+1) 303-308-7140 (Mon-Fri 2:30pm to 7:00pm CET)

Email: ONlit-german@hibbertco.com

French Phone: (+1) 303–308–7141 (Mon–Fri 2:00pm to 7:00pm CET)

Email: ONlit-french@hibbertco.com

English Phone: (+1) 303–308–7142 (Mon–Fri 12:00pm to 5:00pm GMT)

Email: ONlit@hibbertco.com

EUROPEAN TOLL-FREE ACCESS\*: 00-800-4422-3781

\*Available from Germany, France, Italy, UK, Ireland

#### CENTRAL/SOUTH AMERICA:

Spanish Phone: 303-308-7143 (Mon-Fri 8:00am to 5:00pm MST)

Email: ONlit-spanish@hibbertco.com

ASIA/PACIFIC: LDC for ON Semiconductor – Asia Support

Phone: 303-675-2121 (Tue-Fri 9:00am to 1:00pm, Hong Kong Time)

Toll Free from Hong Kong & Singapore:

001–800–4422–3781 Email: ONlit–asia@hibbertco.com

JAPAN: ON Semiconductor, Japan Customer Focus Center 4–32–1 Nishi–Gotanda, Shinagawa–ku, Tokyo, Japan 141–0031

Phone: 81–3–5740–2745 Email: r14525@onsemi.com

ON Semiconductor Website: http://onsemi.com

For additional information, please contact your local Sales Representative.