## **ON Semiconductor**

## Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



ON Semiconductor

## **FXLA0104**

# Low-Voltage Dual-Supply 4-Bit Voltage Translator with Configurable Voltage Supplies and Signal Levels, 3-State Outputs, and Auto Direction Sensing

#### **Features**

- Bi-Directional Interface between Two Levels: from 1.1 V to 3.6 V
- Fully Configurable: Inputs and Outputs Track V<sub>CC</sub>
- Non-Preferential Power-Up; Either V<sub>CC</sub> May Be Powered Up First
- Outputs Switch to 3-State if Either V<sub>CC</sub> is at GND
- Pow er-Off Protection
- Bus-Hold on Data Inputs Eliminates the Need for Pull-Up Resistors; Do Not Use Pull-Up Resistors on A or B Ports
- Control Input (OE) Referenced to V<sub>CCA</sub> Voltage
- Available in the 12-Lead, 1.7 mm x 2.0 mm UMLP Package
- Direction Control Not Necessary
- 100 Mbps Throughput when Translating Between
   1.8 V and 2.5 V
- ESD Protection Exceeds:
  - 6 kV HBM (per JESD22-A114 & Mil Std 883e 3015.7)
  - 2 kV CDM (per ESD STM 5.3)

## **Applications**

Cell Phone, PDA, Digital Camera, Portable GPS

## **Description**

The FXLA0104 is a configurable dual-voltage supply translator for both uni-directional and bi-directional voltage translation between two logic levels. The device allows translation between voltages as high as 3.6 V to as low as 1.1 V. The A port tracks the  $V_{\rm CCA}$  level and the B port tracks the  $V_{\rm CCB}$  level. This allows for bi-directional voltage translation over a variety of voltage levels: 1.2 V, 1.5 V, 1.8 V, 2.5 V, and 3.3 V.

The device remains in three-state as long as either  $V_{CC}$ =0V, allowing either  $V_{CC}$  to be powered up first. Internal power-down control circuits place the device in 3-state if either  $V_{CC}$  is removed.

The OE input, when LOW, disables both the A and B ports by placing them in a 3-state condition. The OE input is supplied by  $V_{\text{CCA}}$ .

The FXLA0104 supports bi-directional translation without the need for a direction control pin. The two ports of the device have auto-direction sense capability. Either port may sense an input signal and transfer it as an output signal to the other port.

### **Ordering Information**

Part Number	Operating Temperature Range	Top Mark	Package	Packing Method
FXLA0104QFX	-40 to 85°C	XU	12-Lead, 1.7 mm x 2.0 mm Ultrathin Molded Leadless Package (UMLP)	5000 Units Tape and Reel

# Pin Configuration




Figure 1. Top Through View

## **Pin Definitions**

Pin #	Name	Description
1	V <sub>CCA</sub>	A-Side Power Supply
2	A0	A-Side Inputs or 3-State Outputs
3	A1	A-Side Inputs or 3-State Outputs
4	A2	A-Side Inputs or 3-State Outputs
5	А3	A-Side Inputs or 3-State Outputs
6	GND	Ground
7	B3	B-Side Inputs or 3-State Outputs
8	B2	B-Side Inputs or 3-State Outputs
9	B1	B-Side Inputs or 3-State Outputs
10	B0	B-Side Inputs or 3-State Outputs
11	V <sub>CCB</sub>	B-Side Pow er Supply
12	OE	Output Enable Input

# **Functional Diagram**




Figure 2. Functional Diagram

# **Function Table**

Control	Outputs					
OE						
LOW Logic Level	3-State					
HIGH Logic Level	Normal Operation					

## **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Condition	Min.	Max.	Unit
Vcc	Supply Voltage	Vcca	-0.5	4.6	V
VCC	Supply Vollage	V <sub>CCB</sub>	-0.5	4.6	V
Vı	DC Input Voltage	VO Ports A and B	-0.5	4.6	V
۷į	Do iliput voltage	Control Input (OE)	-0.5	4.6	V
		Output 3-State	-0.5	4.6	
Vo	Output Voltage <sup>(2)</sup>	Output Active (A <sub>n</sub> )	-0.5	V <sub>CCA</sub> +0.5	V
		Output Active (B <sub>n</sub> )	-0.5	V <sub>CCB</sub> +0.5	
l <sub>IK</sub>	DC Input Diode Current	V <sub>IN</sub> <0V		-50	mA
Юк	DC Output Diode Current	Vo<0V		-50	mA
IOK	DC Output Diode Current	Vo>Vcc		+50	ША
I <sub>OH</sub> /I <sub>OL</sub>	DC Output Source/Sink Curr	ent	-50	+50	mA
lcc	DC V <sub>CC</sub> or Ground Current (	per Supply Pin)		±100	mA
T <sub>STG</sub>	Storage Temperature Range		-65	+150	°C
$P_D$	Pow er Dissipation			17	mW
ESD	Electrostatic Discharge	Human Body Model (per JESD22- A114 & Mil Std 883e 3015.7)		6	kV
LOD	Capability Capability	Charged Device Model (per ESD STM 5.3)		2	ΚV

#### Notes:

- 1. lo absolute maximum ratings must be observed.
- 2. All unused inputs and input/outputs must be held at V<sub>CCi</sub> or GND.

## **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. ON Semiconductor does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter	Condition	Min.	Max.	Unit
V <sub>CC</sub>	Pow er Supply	Operating V <sub>CCA</sub> or V <sub>CCB</sub>	1.1	3.6	V
V <sub>IN</sub>	Input Voltage	Ports A and B	0	3.6	V
V IN	Input Vollage	Control Input (OE)	0	V <sub>CCA</sub>	V
T <sub>A</sub>	Operating Temperature, Free Air		-40	+85	°C
dt/dV	Minimum Input Edge Rate	V <sub>CCA/B</sub> = 1.1 to 3.6 V		10	ns/V
ΘЈΑ	Thermal Resistance: Junction-to-Ambient			300	°C/W
Θιс	Thermal Resistance: Junction-to-Case			165	°C/W

## Power-Up/Power-Down Sequence

FXL translators offer an advantage in that either  $V_{CC}$  may be powered up first. This benefit derives from the chip design. When either  $V_{CC}$  is at 0V, outputs are in a high-impedance state. The control input (OE) is designed to track the  $V_{CCA}$  supply.

The recommended power-up sequence is:

- 1. Apply pow er to the first  $V_{CC}$ .
- 2. Apply power to the second  $V_{CC}$ .
- 3. Drive the OE input HIGH to enable the device.

The recommended power-down sequence is:

- 1. Drive OE input LOW to disable the device.
- 2. Remove power from either  $V_{CC}$ .
- 3. Remove power from other  $V_{CC}$ .

#### Pull-Up/Pull-Down Resistors

<u>Do not use pull-up or pull-down resistors</u>. This device has bus-hold circuits: pull-up or pull-down resistors are not recommended because they interfere with the output state. The current through these resistors may exceed the hold drive,  $I_{\text{(HOLD)}}$  and/or  $I_{\text{(OD)}}$  bus-hold currents, resulting in data transition and/or auto-direction sensing failures. The bus-hold feature eliminates the need for extra resistors.

## **DC Electrical Characteristics**

T<sub>A</sub>=-40 to 85°C

Symbol	Parameter	Condition	V <sub>CCA</sub> (V)	V <sub>CCB</sub> (V)	Min.	Тур.	Max.	Unit
			2.70 to 3.60		2.00			
			2.30 to 2.70		1.60			
$V_{IHA}$		Data Inputs An Control Pin OE	1.65 to 2.30	1.10 to 3.60	.65xV <sub>CCA</sub>			V
		CONTROL VIII OL	1.40 to 1.65		.65xV <sub>CCA</sub>			
	High-Level Input		1.10 to 1.40		.90xV <sub>CCA</sub>			
	Voltage			2.70 to 3.60	2.00			
				2.30 to 2.70	1.60			
$V_{IHB}$		Data Inputs B <sub>n</sub>	1.10 to 3.60	1.65 to 2.30	.65xV <sub>CCB</sub>			V
				1.40 to 1.65	.65xV <sub>CCB</sub>			
				1.10 to 1.40	.90xV <sub>CCB</sub>			
			2.70 to 3.60				.80	
			2.30 to 2.70				.70	
$V_{ILA}$		Data Inputs An	1.65 to 2.30	1.10 to 3.60			.35xV <sub>CCA</sub>	V
	Low -Level Input	Control Pin OE					.35xV <sub>CCA</sub>	
			1.10 to 1.40				.10xV <sub>CCA</sub>	
	Voltage			2.70 to 3.60			.80	
				2.30 to 2.70			.70	
$V_{ILB}$		Data Inputs B <sub>n</sub>		1.65 to 2.30			.35xV <sub>CCB</sub>	V
				1.40 to 1.65			.35xV <sub>CCB</sub>	
				1.10 to 1.40			.10xV <sub>CCB</sub>	
V <sub>OHA</sub>	High-Leyel Output	l <sub>OH</sub> =-4 μA	1.10 to 3.60	1.10 to 3.60	V <sub>CCA</sub> 4			
V <sub>OHB</sub>	Voltage <sup>(3)</sup>	l <sub>OH</sub> =-4 μA	1.10 to 3.60	1.10 to 3.60	V <sub>CCB</sub> 4			V
Vola	Low -Leyel Output	loL=4 μA	1.10 to 3.60	1.10 to 3.60			.4	
V <sub>OLB</sub>	Voltage <sup>(3)</sup>	l <sub>OL</sub> =4 μA	1.10 to 3.60	1.10 to 3.60			.4	V
		V <sub>IN</sub> =0.8 V	3.00	3.00	75.0			
		V <sub>IN</sub> =2.0 V	3.00	3.00	-75.0			
		V <sub>IN</sub> =0.7 V	2.30	2.30	45.0			
		V <sub>IN</sub> =1.6 V	2.30	2.30	-45.0			
	Bus-Hold Input	V <sub>IN</sub> =0.57 V	1.65	1.65	25.0			
l <sub>I(HOLD)</sub>	Minimum Drive Current	V <sub>IN</sub> =1.07 V	1.65	1.65	-25.0			μA
		V <sub>IN</sub> =0.49 V	1.40	1.40	11.0			
		V <sub>IN</sub> =0.91 V	1.40	1.40	-11.0			
		V <sub>IN</sub> =0.11 V	1.10	1.10		4.0		
		V <sub>IN</sub> =0.99 V	1.10	1.10		-4.0		

#### Note:

3. This is the output voltage for static conditions. Dynamic drive specifications are given in the Dynamic Output Electrical Characteristics table.

Continued on following page...

## DC Electrical Characteristics (Continued)

T<sub>A</sub>=-40 to 85°C.

Symbol	Parameter	Condition	V <sub>CCA</sub> (V)	V <sub>CCB</sub> (V)	Min.	Max.	Unit
			3.60	3.60	450.0		
	Bus-Hold Input		2.70	2.70	300.0		
lı(ODH)	Overdrive High	Data Inputs A <sub>n</sub> , B <sub>n</sub>	1.95	1.95	200.0		μA
	Current <sup>(4)</sup>		1.60	1.60	120.0		
			1.40	1.40	80.0		
			3.60	3.60	-450.0		
	Bus-Hold Input		2.70	2.70	-300.0		
l <sub>l(ODL)</sub>	Overdrive Low	Data Inputs A <sub>n</sub> , B <sub>n</sub>	1.95	1.95	-200.0		μA
	Current <sup>(5)</sup>		1.60	1.60	-120.0		
			1.40	1.40	-80.0		
l <sub>l</sub>	Input Leakage Current	Control Inputs OE, V <sub>I</sub> =V <sub>CCA</sub> or GND	1.10 to 3.60	3.60		±1.0	μΑ
I	Pow er-Off Leakage	A <sub>n</sub> V <sub>O</sub> =0 V to 3.6 V	0	3.60		±2.0	
loff	Current	B <sub>n</sub> V <sub>O</sub> =0 V to 3.6 V	3.60	0		±2.0	μA
		$A_n$ , $B_n$ $V_O=0$ $V$ or 3.6 $V$ , $OE=V_{IL}$	3.60	3.60		±5.0	
loz	3-State Output Leakage	A <sub>n</sub> V <sub>O</sub> =0 V or 3.6 V, OE=V <sub>CCA</sub>	3.60	0		±5.0	μΑ
		B <sub>n</sub> V <sub>O</sub> =0 V or 3.6 V, OE=3.6V	0	3.60		±5.0	
ICCA/B	Quiescent Supply Current 6' 7'	V <sub>I</sub> =V <sub>CCI</sub> or GND; l <sub>O</sub> =0, OE=V <sub>IH</sub>	1.10 to 3.60	1.10 to 3.60		10.0	μΑ
lccz	Current <sup>(6)</sup> 7 <sup>)</sup>	V <sub>I</sub> =V <sub>CCI</sub> or GND; l <sub>O</sub> =0, OE=GND	1.10 to 3.60	1.10 to 3.60		10.0	μΑ
lcca		V <sub>I</sub> =V <sub>CCB</sub> or GND; l <sub>O</sub> =0 B-to-A Direction; OE=V <sub>IH</sub>	0	1.10 to 3.60		-10.0	μA
	Quiescent Supply Current	V <sub>I</sub> =V <sub>CCA</sub> or GND; I <sub>O</sub> =0 A-to-B Direction	1.10 to 3.60	0		10.0	
Іссв		$V_{\text{I=}}V_{\text{CCA}}$ or GND; $I_{\text{O}}$ =0, A-to-B Direction, OE= $V_{\text{IH}}$	1.10 to 3.60	0		-10.0	μA
		V <sub>I</sub> =V <sub>CCB</sub> or GND; I <sub>O</sub> =0 B-to-A Direction	0	1.10 to 3.60		10.0	

#### Notes:

- 4. An external drive must source at least the specified current to switch LOW-to-HIGH.
- 5. An external drive must source at least the specified current to switch HIGH-to-LOW.
- 6. V<sub>CCI</sub> is the V<sub>CC</sub> associated with the input side.7. Reflects current per supply, V<sub>CCA</sub> or V<sub>CCB</sub>.

## **Dynamic Output Electrical Characteristic**

A Port (A<sub>n</sub>)

Output Load:  $C_L$ =15 pF,  $R_L \ge M\Omega$  ( $C_{I/O}$ =4 pF),  $T_A$ =-40 to 85°C

Symbol	Parameter	V <sub>CCA</sub> =3.0 V to 3.6 V			V <sub>CCA</sub> =2.3 V to 2.7 V		V <sub>CCA</sub> =1.65 V to 1.95 V		:1.4 V .6 V	V <sub>CCA</sub> =1.1 V to 1.3 V	Unit
		Тур.	Max.	Тур.	Max.	Тур.	Max	Тур.	Max.	Тур.	
t <sub>rise</sub>	Output Rise Time A Port <sup>(</sup> 9)		3.0		3.5		4.0		5.0	7.5	ns
t <sub>fall</sub>	Output Fall Time A Port <sup>(10)</sup>		3.0		3.5		4.0		5.0	7.5	ns
Юна	Dynamic Output Current High <sup>(</sup> 9 <sup>)</sup>	-11.4		-7.5		-4.7		-3.2		-1.7	mA
Юца	Dynamic Output Current Low <sup>(10)</sup>	+11.4		+7.5		+4.7		+3.2		+1.7	mA

## B Port (B<sub>n</sub>)

Output Load:  $C_L=15$  pF,  $R_L \ge M\Omega$  ( $C_{VO}=5$  pF),  $T_A=-40$  to  $85^{\circ}C$ 

Symbol	Parameter	V <sub>CCB</sub> =3.0 V to 3.6 V		V <sub>CCB</sub> =2.3 V to 2.7 V		V <sub>CCB</sub> =1.65 V to 1.95 V		V <sub>CCB</sub> =1.4 V to 1.6 V		V <sub>CCB</sub> =1.1 V to 1.3 V	Unit
		Тур.	Max.	Тур.	Max.	Тур.	Max	Тур.	Max.	Тур.	
t <sub>rise</sub>	Output Rise Time B Port <sup>(</sup> 9)		3.0		3.5		4.0		5.0	7.5	ns
t <sub>fall</sub>	Output Fall Time B Port <sup>(10)</sup>		3.0		3.5		4.0		5.0	7.5	ns
Юнр	Dynamic Output Current High <sup>(9)</sup>	-12.0		-7.9		-5.0		-3.4		-1.8	mA
ЮЦ	Dynamic Output Current Low <sup>(10)</sup>	+12.0		+7.9		+5.0		+3.4		+1.8	mA

#### Notes:

- 8. Dynamic output characteristics are guaranteed, but not tested.
- 9. See Figure 7.
- 10. See Figure 8.

#### **AC** Characteristics

## $V_{CCA} = 3.0 \text{ V to } 3.6 \text{ V}, T_A = -40 \text{ to } 85^{\circ}\text{C}$

Symbol	Parameter	V <sub>CCB</sub> =3.0 V to 3.6 V		V <sub>CCB</sub> =2.3 V to 2.7 V		V <sub>CCB</sub> =1.65 V to 1.95 V		V <sub>CCB</sub> =	=1.4 V .6 V	V <sub>CCB</sub> =1.1 V to 1.3 V	Unit
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
tplH,tpHL	A to B	0.2	4.0	0.3	4.2	0.5	5.4	0.6	6.8	6.9	ns
IPLH, IPHL	B to A	0.2	4.0	0.2	4.1	0.3	5.0	0.5	6.0	4.5	ns
t <sub>PZL</sub> ,t <sub>PZH</sub>	OE to A, OE to B		1.7		1.7		1.7		1.7	1.7	μs
tskew	A Port, B Port <sup>(11)</sup>		0.5		0.5		0.5		1.0	1.0	ns

## $V_{CCA} = 2.3 \text{ V to } 2.7 \text{ V}, T_A = -40 \text{ to } 85^{\circ}\text{C}$

Symbol	Parameter	V <sub>CCB</sub> =3.0 V to 3.6 V		V <sub>CCB</sub> =2.3 V to 2.7 V		V <sub>CCB</sub> =1.65 V to 1.95 V		V <sub>CCB</sub> =1.4 V to 1.6 V		V <sub>CCB</sub> =1.1 V to 1.3 V	Unit
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
tou tou	A to B	0.2	4.1	0.4	4.5	0.5	5.6	0.8	6.9	7.0	ns
t <sub>PLH</sub> ,t <sub>PHL</sub>	B to A	0.3	4.2	0.4	4.5	0.5	5.5	0.5	6.5	4.8	ns
t <sub>PZL</sub> ,t <sub>PZH</sub>	OE to A, OE to B		1.7		1.7		1.7		1.7	1.7	μs
tskew	A Port, B Port <sup>(11)</sup>		0.5		0.5		0.5		1.0	1.0	ns

## $V_{CCA} = 1.65 \text{ V to } 1.95 \text{ V}, T_A = -40 \text{ to } 85^{\circ}\text{C}$

Symbol	Parameter	V <sub>CCB</sub> =3.0 V to 3.6 V		V <sub>CCB</sub> =2.3 V to 2.7 V		V <sub>CCB</sub> =1.65 V to 1.95 V		V <sub>CCB</sub> =1.4 V to 1.6 V		V <sub>CCB</sub> =1.1 V to 1.3 V	Unit
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
t <sub>PLH</sub> ,t <sub>PHL</sub>	A to B	0.3	5.0	0.5	5.5	0.8	6.7	0.9	7.5	7.5	ns
PLH, PHL	B to A	0.5	5.4	0.5	5.6	0.8	6.7	1.0	7.0	5.4	ns
t <sub>PZL</sub> ,t <sub>PZH</sub>	OE to A, OE to B		1.7		1.7		1.7		1.7	1.7	μs
tskew	A Port, B Port <sup>(11)</sup>		0.5		0.5		0.5		1.0	1.0	ns

#### Note

11. Skew is the variation of propagation delay between output signals and applies only to output signals on the same port (An or Bn) and switching with the same polarity (LOW-to-HIGH or HIGH-to-LOW) (see Figure 10). Skew is guaranteed, but not tested.

## AC Characteristics (Continued)

## $V_{CCA} = 1.4 \text{ V to } 1.6 \text{ V}, T_A = -40 \text{ to } 85^{\circ}\text{C}$

Symbol	Parameter	V <sub>CCB</sub> =3.0 V to 3.6 V		V <sub>CCB</sub> =2.3 V to 2.7 V		V <sub>CCB</sub> =1.65 V to 1.95 V		V <sub>CCB</sub> =1.4 V to 1.6 V		V <sub>CCB</sub> =1.1 V to 1.3 V	Unit
		Min.	Max.	Min.	Max.	Min.	Max	Min.	Max.	Тур.	
t <sub>PLH</sub> ,t <sub>PHL</sub>	A to B	0.5	6.0	0.5	6.5	1.0	7.0	1.0	8.5	7.9	ns
	B to A	0.6	6.8	0.8	6.9	0.9	7.5	1.0	8.5	6.1	ns
t <sub>PZL</sub> ,t <sub>PZH</sub>	OE to A, OE to B		1.7		1.7		1.7		1.7	1.7	μs
tskew	A Port, B Port <sup>(12)</sup>		1.0		1.0		1.0		1.0	1.0	ns

## $V_{CCA} = 1.1 \text{ V to } 1.3 \text{ V}, T_A = -40 \text{ to } 85^{\circ}\text{C}$

Symbol	Parameter	V <sub>CCB</sub> =3.0 V to 3.6 V	V <sub>CCB</sub> =2.3 V to 2.7 V	V <sub>CCB</sub> =1.65 V to 1.95 V	V <sub>CCB</sub> =1.4 V to 1.6 V	V <sub>CCB</sub> =1.1 V to 1.3 V	Unit
		Тур.	Тур.	Тур.	Тур.	Тур.	
4	A to B	4.6	4.8	5.4	6.2	9.2	ns
t <sub>PLH</sub> ,t <sub>PHL</sub>	B to A	6.8	7.0	7.4	7.8	9.1	ns
$t_{PZL},t_{PZH}$	OE to A, OE to B	1.7	1.7	1.7	1.7	1.7	μs
tskew	A Port, B Port <sup>(12)</sup>	1.0	1.0	1.0	1.0	1.0	ns

#### Note:

<sup>12.</sup> Skew is the variation of propagation delay between output signals and applies only to output signals on the same port (An or Bn) and switching with the same polarity (LOW-to-HIGH or HIGH-to-LOW) (see Figure 10). Skew is guaranteed, but not tested.

# Maximum Data Rate<sup>(13, 14)</sup>

#### T<sub>A</sub>=-40 to 85°C

V <sub>CCA</sub>	V <sub>CCB</sub> =3.0 V to 3.6 V	V <sub>CCB</sub> =2.3V to 2.7V	V <sub>CCB</sub> =1.65V to 1.95V	V <sub>CCB</sub> =1.4V to 1.6V	V <sub>CCB</sub> =1.1V to 1.3V	Unit
	Min.	Min.	Min.	Min.	Тур.	
V <sub>CCA</sub> =3.00 to 3.60 V	140	120	100	80	40	Mbps
V <sub>CCA</sub> =2.30 to 2.70 V	120	120	100	80	40	Mbps
V <sub>CCA</sub> =1.65 to 1.95 V	100	100	80	60	40	Mbps
V <sub>CCA</sub> =1.40 to 1.60 V	80	80	60	60	40	Mbps
V <sub>CCA</sub> =1.10 to 1.30 V	Тур.	Тур.	Тур.	Тур.	Тур.	
V CCA=1.10 to 1.00 V	40	40	40	40	40	Mbps

- Notes:

  13. Maximum data rate is guaranteed, but not tested.
- 14. Maximum data rate is specified in megabits per second (see Figure 9). It is equivalent to two times the F-toggle frequency, specified in megahertz. For example, 100 Mbps is equivalent to 50MHz.

## Capacitance

Symbol	Parameter		Conditions	T <sub>A</sub> =+25°C Typical	Unit
C <sub>IN</sub>	Input Capacitance Control	Pin (OE)	Vcca=Vccb=GND	3	pF
C <sub>I/O</sub>	Input/Output Capacitance	An	V <sub>CCA</sub> =V <sub>CCB</sub> =3.3 V, OE=GND	4	pF
<b>3</b> //0	B <sub>n</sub>		VCCA-VCCB-0.0 V, GL-GIVD	5	۲,
C <sub>pd</sub>	Pow er Dissipation Capacita	nce	V <sub>CCA</sub> =V <sub>CCB</sub> =3.3 V, V <sub>I</sub> =0V or V <sub>CC</sub> , f=10 MHz	25	pF

#### I/O Architecture Benefit

The FXLA0104 VO architecture benefits the end user, beyond level translation, in the following three ways:

Auto Direction without an external direction pin.

**Drive Capacitive Loads**. Automatically shifts to a higher current drive mode only during "Dynamic Mode" or HL / LH transitions.

**Lower Power Consumption**. Automatically shifts to low-power mode during "Static Mode" (no transitions), lowering power consumption.

The FXLA0104 does not require a direction pin. Instead, the I/O architecture detects input transitions on both side and automatically transfers the data to the corresponding output. For example, for a given channel, if both A and B side are at a static LOW, the direction has been established as A  $\rightarrow$  B, and a LH transition occurs on the B port; the FXLA0104 internal I/O architecture automatically changes direction from A  $\rightarrow$  B to B  $\rightarrow$  A.

During HL / LH transitions, or "Dynamic Mode," a strong output driver drives the output channel in parallel with a weak output driver. After a typical delay of approximately 10 ns - 50 ns, the strong driver is turned off, leaving the weak driver enabled for holding the logic state of the channel. This weak driver is called the "bus

hold." "Static Mode" is when only the bus hold drives the channel. The bus hold can be over ridden in the event of a direction change. The strong driver allows the FXLA0104 to quickly charge and discharge capacitive transmission lines during dynamic mode. Static mode conserves power, where  $I_{CC}$  is typically  $< 5 \, \mu A$ .

#### **Bus Hold Minimum Drive Current**

Specifies the minimum amount of current the bus hold driver can source/sink. The bus hold minimum drive current ( $I_{HOLD}$ ) is  $V_{CC}$  dependent and guaranteed in the DC Electrical tables. The intent is to maintain a valid output state in a static mode, but that can be overridden when an input data transition occurs.

#### **Bus Hold Input Overdrive Drive Current**

Specifies the minimum amount of current required (by an external device) to overdrive the bus hold in the event of a direction change. The bus hold overdrive ( $II_{ODH}$ ,  $II_{ODL}$ ) is  $V_{CC}$  dependent and guaranteed in the DC Electrical tables.

#### **Dynamic Output Current**

The strength of the output driver during LH / HL transitions is referenced on page 8, Dynamic Output Electrical Characteristics, I<sub>OHD</sub>, and I<sub>OLD</sub>.

## **Test Diagrams**




Figure 3. Test Circuit

Table 1. AC Test Conditions

Test	Input Signal	Output Enable Control
t <sub>PLH</sub> , t <sub>PHL</sub>	Data Pulses	VCCA
t <sub>PZL</sub>	0V	LOW to HIGH Switch
t <sub>РZH</sub>	V <sub>CCI</sub>	LOW to HIGH Switch

#### Table 2. AC Load

V <sub>cco</sub>	C1	R1
1.2 V± 0.1 V	15 pF	1 MΩ
1.5 V± 0.1 V	15 pF	1 MΩ
1.8 V ± 0.15 V	15 pF	1 ΜΩ
2.5 V ± 0.2 V	15 pF	1 MΩ
3.3 V ± 0.3 V	15 pF	1 MΩ




Figure 4. Waveform for Inverting and Non-Inverting Functions

#### Notes:

- 15. Input  $t_R = t_F = 2.0$  ns, 10% to 90%.
- 16. Input  $t_R = t_F = 2.5$  ns, 10% to 90%, at  $V_I = 3.0$  V to 3.6 V only.




Figure 5. 3-State Output Low Enable

#### Notes:

- 17. Input  $t_R = t_F = 2.0$  ns, 10% to 90%.
- 18. Input  $t_R = t_F = 2.5$  ns, 10% to 90%, at  $V_I = 3.0$  V to 3.6 V only.




Figure 6. 3-State Output High Enable

#### Notes:


- 19. Input  $t_R = t_F = 2.0$  ns, 10% to 90%.
- 20. Input  $t_R = t_F = 2.5$  ns, 10% to 90%, at  $V_I = 3.0$  V to 3.6 V only.

Table 3. Test Measure Points

Symbol	$V_{ extsf{DD}}$
V <sub>MI</sub> <sup>(21)</sup>	V <sub>CCI</sub> /2
V <sub>MO</sub>	V <sub>CCo</sub> /2
Vx	0.9 x V <sub>CCo</sub>
V <sub>Y</sub>	0.1 x V <sub>CCo</sub>


#### Note:

21. V<sub>CCI</sub>=V<sub>CCA</sub> for control pin OE or V<sub>MI</sub>(V<sub>CCA</sub>/2).



$$I_{OHD} pprox (C_L + C_{I/O}) \times \frac{\Delta V_{OUT}}{\Delta t} = (C_L + C_{I/O}) \times \frac{(20\% - 80\%) \bullet V_{CCO}}{t_{RISE}}$$

Figure 7. Active Output Rise Time and Dynamic Output Current High



$$I_{OLD} \approx (C_L + C_{I/O}) \times \frac{\Delta V_{OUT}}{\Delta t} = (C_L + C_{I/O}) \times \frac{(80\% - 20\%) \bullet V_{CCO}}{t_{FALL}}$$

Figure 8. Active Output Fall Time and Dynamic Output Current Low




Figure 9. Maximum Data Rate






Figure 10. Output Skew Time

Note:


22.  $t_{SKEW} = (t_{pHLmax} - t_{pHLmin})$  or  $(t_{pLHmax} - t_{pLHmin})$ 

## **Physical Dimensions**







#### RECOMMENDED LAND PATTERN



### NOTES:

- A. PACKAGE DOES NOT FULLY CONFORM TO JEDEC MO-220 REGISTRATION
  - B. DIMENSIONS ARE IN MILLIMETERS.
  - C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 1994.
  - D. LAND PATTERN RECOMMENDATION IS BASED ON FSC DESIGN ONLY.
  - E. DRAWING FILENAME: MKT-UMLP12Crev2.





**BOTTOM VIEW** 

**DETAIL A** 

Figure 11. 12-Lead, Ultrathin Molded Leadless Package (UMLP)

Package drawings are provided as a service to customers considering ON Semiconductor components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a ON Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of ON Semiconductor's worldwide terms and conditions, specifically the warranty therein, which covers ON Semiconductor products.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employ

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Fmail: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada.

Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semic onductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative