# **ON Semiconductor**

# Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

# **Configurable Multifunction Gate**

The NLX1G99 MiniGate  $^{\text{M}}$  is an advanced high-speed CMOS multifunction gate with a 3-state output. With the output enable input  $(\overline{OE})$  at High, the output is disabled and is kept at high impedance. With the output enable input  $(\overline{OE})$  at Low, the device can be configured for logic functions such as MUX, AND, OR, NAND, NOR, XOR, XNOR, INVERT and BUFFER, depending on the combination of the 4-bit input. The device has Schmitt-trigger inputs, thereby enhancing noise immunity.

The NLX1G99 input and output structures provide protection when voltages up to 7.0 V are applied, regardless of the supply voltage.


#### **Features**

- High Speed:  $t_{PD} = 6.7 \text{ ns (Max)} @ V_{CC} = 3.3 \text{ V}$
- Low Power Dissipation:  $I_{CC} = 1 \mu A$  (Max) at  $T_A = 25^{\circ}C$
- Power Down Protection Provided on inputs
- Balanced Propagation Delays
- Overvoltage Tolerant (OVT) Input and Output Pins
- Ultra-Small Packages
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

#### **PIN ASSIGNMENT**

1	ŌĒ
2	А
3	В
4	GND
5	С
6	D
7	Y
8	V <sub>CC</sub>

#### **PIN ASSIGNMENTS**





# ON Semiconductor®

www.onsemi.com

#### MARKING DIAGRAMS



UDFN8 1.45 x 1.0 CASE 517BZ





UDFN8 1.6 x 1.0 CASE 517BY





UDFN8 1.95 x 1.0 CASE 517CA




AA or E = Specific Device Code
M = Date Code
Device Pb-Free Package

#### **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 12 of this data sheet.

# **FUNCTION DIAGRAM**



# **FUNCTION TABLE\***

		INPUT			OUTPUT
ŌĒ	D	С	В	Α	Υ
L	L	L	L	L	L
L	L	L	L	Н	Н
L	L	L	Н	L	L
L	L	L	Н	Н	Н
L	L	Н	L	L	L
L	L	Н	L	Н	L
L	L	Н	Н	L	Н
L	L	Н	Н	Н	Н
L	Н	L	L	L	Н
L	Н	L	L	Н	L
L	Н	L	Н	L	Н
L	Н	L	Н	Н	L
L	Н	Н	L	L	Н
L	н	Н	L	Н	Н
L	н	Н	Н	L	L
L	н	Н	Н	Н	L
Н	H or L	H or L	H or L	H or L	Z

<sup>\*</sup>To select a logic function, please refer to "Logic Configurations" section.

FUNCTION SELECTION	LOGIC CONFIGURATION PAGE
3-State Buffers	3
3-State Inverters	3
3-State MUXes	3
3-State AND / OR / NOR	4
3-State NAND / OR	5
3-State XOR/XNOR	6

# **LOGIC CONFIGURATIONS**

#### 3-State Buffer Functions Available




Figure 2.

Function	ŌĒ	Α	В	С	D
3-State Buffer	L	Input H or L L H H C H	H or L Input H L H or L L L	L H Input Input L H H or L	L L H Input Input Input

# 3-State Inverter Functions Available






Figure 3.

Function	OE	Α	В	С	D
3-State Buffer	L	Input X L H H H or L H	H or L Input H L H or L H	L H Input Input L H H or L	H H L Input Input Input

# 3-State MUX Functions Available





Function	OE	Α	В	С	D
3-State 2-to-1 3-State 2-to-1 3-State 2-to-1, Inverted Out 3-State 2-to-1, Inverted Out	L	Input 1 Input 2 Input 1 Input 2	Input 2 Input 1 Input 2 Input 1	Input 1 or Input 2 Input 2 or Input 1 Input 1 or Input 2 Input 2 or Input 1	L L H

# 3-State AND/NOR/OR Function Available




Figure 5.

	No. of Inputs	AND/NAND Function	OR/NOR Function	ŌĒ	Α	В	С	D
Ī	2 2	3-State AND 3-State AND	3-State NOR 3-State NOR	L	L L	Input 1 Input 2	Input 2 Input 1	L




Figure 6.

No. of Inputs	AND/NAND Function	OR/NOR Function	ŌĒ	Α	В	С	D
2	3-State AND	3-State NOR	L	Input 2	L	Input 1	L
2	3-State AND	3-State NOR		H	Input 1	Input 2	H





Figure 7.

No. of Inputs	AND/NAND Function	OR/NOR Function	ŌE	Α	В	С	D
2	3-State AND	3-State NOR	L	Input 1	L	Input 2	L
2	3-State AND	3-State NOR		H	Input 2	Input 1	H



No. of Inputs	AND/NAND Function	OR/NOR Function	ŌĒ	Α	В	C	D
2 2	3-State AND 3-State AND	3-State NOR 3-State NOR	L	Input 1 Input 2	ΗH	Input 2 Input 1	H H

# 3-State NAND/OR Function Available




Figure 9.

No. of Inputs	AND/NAND Function	OR/NOR Function	ŌĒ	Α	В	С	D
2	3-State NAND	3-State OR	L	L	Input 1	Input 2	H
2	3-State NAND	3-State OR		L	Input 2	Input 1	H




Figure 10.

No. of Inputs	AND/NAND Function	OR/NOR Function	ŌĒ	Α	В	С	D
2 2	3-State NAND 3-State NAND	3-State OR 3-State OR	L	Input 2 H	L Input 1	Input 1 Input 2	H L





Figure 11.

No	o. of Inputs	AND/NAND Function	OR/NOR Function	ŌĒ	Α	В	С	D
	2 2	3-State NAND 3-State NAND	3–State OR 3–State OR	L	Input 1 H	L Input 2	Input 2 Input 1	H



No. of Input	AND/NAND Function	OR/NOR Function	ŌĒ	Α	В	C	D
2	3-State AND	3-State OR	L	Input 1	H	Input 2	L
2	3-State AND	3-State OR		Input 2	H	Input 1	L

# 3-State XOR/XNOR Function Available




Figure 13.

Function	ŌĒ	Α	В	С	D
3-State XOR	L	Input 1 Input 2 H or L H or L L L	H or L H or L Input 1 Input 2 H H	L L H H Input 1 Input 2	Input 2 Input 1 Input 2 Input 1 Input 2 Input 1




Figure 14.

	unction	ŌĒ	Α	В	С	D
3-3	State XOR	L	Н	L	Input 1	Input 2




Figure 15.

Function	ŌĒ	Α	В	С	D
3-State XOR	L	Н	L	Input 1	Input 2




Figure 16.

Function	ŌĒ	Α	В	С	D
3-State XNOR	L	H	L	Input 1	Input 2
3-State XNOR		H	L	Input 2	Input 1

#### **MAXIMUM RATINGS**

Symbol	Parameter	Value	Unit
V <sub>CC</sub>	DC Supply Voltage	-0.5 to +7.0	V
V <sub>IN</sub>	DC Input Voltage	−0.5 to +7.0	V
V <sub>OUT</sub>	DC Output Voltage  Active Mode (High or Low State)  Tristate Mode (Output at Hi–Z)  Power Down Mode (V <sub>CC</sub> = 0 V)	-0.5 to V <sub>CC</sub> + 0.5 -0.5 to +7.0 -0.5 to +7.0	V
I <sub>IK</sub>	DC Input Diode Current V <sub>IN</sub> < GND	-50	mA
I <sub>OK</sub>	DC Output Diode Current V <sub>OUT</sub> < GND	-50	mA
Ιο	DC Output Source/Sink Current	±50	mA
I <sub>CC</sub>	DC Supply Current Per Supply Pin	±100	mA
I <sub>GND</sub>	DC Ground Current per Ground Pin	±100	mA
T <sub>STG</sub>	Storage Temperature Range	-65 to +150	°C
TL	Lead Temperature, 1 mm from Case for 10 Seconds	260	°C
TJ	Junction Temperature Under Bias	150	°C
MSL	Moisture Sensitivity	Level 1	
F <sub>R</sub>	Flammability Rating Oxygen Index: 28 to 34	UL 94 V-0 @ 0.125 in	
V <sub>ESD</sub>	ESD Withstand Voltage  Human Body Model (Note 2)  Machine Model (Note 3)  Charged Device Model (Note 4)	> 2000 > 200 N/A	V
I <sub>LATCHUP</sub>	Latchup Performance Above V <sub>CC</sub> and Below GND at 125°C (Note 5)	±500	mA

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Measured with minimum pad spacing on an FR4 board, using 10 mm-by-1 inch, 2 ounce copper trace no air flow.

- Tested to EIA / JESD22-A114-A.
   Tested to EIA / JESD22-A115-A.
- 4. Tested to JESD22-C101-A.
- 5. Tested to EIA / JESD78.

## **RECOMMENDED OPERATING CONDITIONS**

Symbol	Para	ameter	Min	Max	Unit
V <sub>CC</sub>	Positive DC Supply Voltage		1.65	5.5	V
V <sub>IN</sub>	Digital Input Voltage		0	5.5	V
V <sub>OUT</sub>	Output Voltage	Active Mode (High or Low State) Tristate Mode (Output at Hi–Z) Power Down Mode (V <sub>CC</sub> = 0 V)	0 0 0	V <sub>CC</sub> 5.5 5.5	V
T <sub>A</sub>	Operating Free-Air Temperature		-55	+125	°C
Δt /ΔV	Input Transition Rise or Fall Rate	$V_{CC} = 2.5 \text{ V} \pm 0.2 \text{ V} \\ V_{CC} = 3.3 \text{ V} \pm 0.3 \text{ V} \\ V_{CC} = 5.0 \text{ V} \pm 0.5 \text{ V}$	0 0 0	No Limit No Limit No Limit	nS/V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

# DC ELECTRICAL CHARACTERISTICS

				T <sub>A</sub> = 2	5°C	<b>T</b> <sub>A</sub> ≤ +	85°C	T <sub>A</sub> = -55 +125		
Symbol	Parameter	Conditions	V <sub>CC</sub> (V)	Min	Max	Min	Max	Min	Max	Unit
V <sub>T+</sub>	Positive Threshold Voltage		1.65 1.8 2.3 3.0 4.5 5.5	0.79 0.87 1.11 1.5 2.16 2.61	1.16 1.28 1.56 1.87 2.74 3.33		1.16 1.28 1.56 1.87 2.74 3.33		1.16 1.28 1.56 1.87 2.74 3.33	V
V <sub>T</sub> -	Negative Threshold Voltage		1.65 1.8 2.3 3.0 4.5 5.5	0.35 0.38 0.58 0.84 1.41 1.78	0.62 0.68 0.87 1.19 1.9 2.29	0.35 0.38 0.58 0.84 1.41 1.78		0.35 0.38 0.58 0.84 1.41 1.78		٧
V <sub>H</sub>	Hysteresis Voltage		1.65 1.8 2.3 3.0 4.5 5.5	0.30 0.33 0.40 0.53 0.71 0.8	0.62 0.68 0.8 0.87 1.04 1.2	0.30 0.33 0.40 0.53 0.71 0.8	0.62 0.68 0.8 0.87 1.04 1.2	0.30 0.33 0.40 0.53 0.71 0.8	0.62 0.68 0.8 0.87 1.04	V
V <sub>OH</sub>	Minimum High-Level Output Voltage	$V_{IN} = V_{T-MIN} \text{ or } \\ V_{T+MAX} \\ I_{OH} = -50 \ \mu\text{A} \\ I_{OH} = -100 \ \mu\text{A}$	1.65–5.5 1.65–5.5	V <sub>CC</sub> -0.1 V <sub>CC</sub> -0.1		V <sub>CC</sub> -0.1 V <sub>CC</sub> -0.1		V <sub>CC</sub> -0.1 V <sub>CC</sub> -0.1		V
		$V_{IN} = V_{T-MIN} \text{ or } \\ V_{T+MAX} \\ I_{OH} = -4 \text{ mA} \\ I_{OH} = -8 \text{ mA} \\ I_{OH} = -12 \text{ mA} \\ I_{OH} = -16 \text{ mA} \\ I_{OH} = -24 \text{ mA} \\ I_{OH} = -32 \text{ mA} \\ I_{$	1.65 2.3 2.7 3.0 3.0 4.5	1.2 1.9 2.2 2.4 2.3 3.8		1.2 1.9 2.2 2.4 2.3 3.8		1.2 1.9 2.2 2.4 2.3 3.8		V
V <sub>OL</sub>	Maximum Low-Level Output Voltage	$\begin{aligned} V_{IN} &= V_{T-MIN} \text{ or } \\ V_{T+MAX} \\ I_{OL} &= 50  \mu\text{A} \\ I_{OL} &= 100  \mu\text{A} \end{aligned}$	1.65–5.5 1.65–5.5		0.1 0.1		0.1 0.1		0.1 0.1	V
		V <sub>IN</sub> = V <sub>T-MIN</sub> or V <sub>T+MAX</sub> I <sub>OL</sub> = 4 mA I <sub>OL</sub> = 8 mA I <sub>OL</sub> = 12 mA I <sub>OL</sub> = 16 mA I <sub>OL</sub> = 24 mA I <sub>OL</sub> = 32 mA	1.65 2.3 2.7 3.0 3.0 4.5		0.45 0.3 0.4 0.4 0.55 0.55		0.45 0.3 0.4 0.4 0.55 0.55		0.45 0.3 0.4 0.4 0.55 0.55	
I <sub>IN</sub>	Input Leakage Current	0 ≤ V <sub>IN</sub> ≤ 5.5 V	0 – 5.5		± 0.1		±1.0		±1.0	μΑ
I <sub>off</sub>	Power off Leakage Current	V <sub>IN</sub> or V <sub>O</sub> = 5.5 V	0		±1.0		±10		±10	μΑ
l <sub>OZ</sub>	Tri-state Output Leakage Current	V <sub>O</sub> = V <sub>CC</sub> or GND	1.65–5.5		±1.0		±10		±10	μΑ
I <sub>CC</sub>	Quiescent Supply Current	$V_{IN} = V_{CC}$ or GND, $I_O = 0$	1.65-5.5		1.0		10		10	μΑ
Δl <sub>CC</sub>	Increase in I <sub>CC</sub> Per Input	One input at (V <sub>CC</sub> -0.6) V, other inputs at V <sub>CC</sub> or GND	2.3 – 5.5		10		100		100	μΑ


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# AC ELECTRICAL CHARACTERISTICS (Input $t_r = t_f = 3.0 \text{ ns}$ )

				T <sub>A</sub> = 25°C		T <sub>A</sub> ≤	+85°C	T <sub>A</sub> = -55°C to +125°C			
Symbol	Parameter	V <sub>CC</sub> (V)	Test Condition	Min	Тур	Max	Min	Max	Min	Max	Unit
t <sub>PLH</sub> , <sup>†</sup> PHL	Propagation Delay, Any Input to Output Y (See Test Circuit)	1.65–1.95 2.3 – 2.7 3.0 – 3.6 4.5 – 5.5	Refer to switch positions and loading conditions in Figure 17 to 21.	4.3 2.4 1.7 1.3	12.8 7.1 5.2 4.0	25.1 10.2 6.7 4.5	4.3 2.4 1.7 1.3	25.1 10.2 6.9 4.9	4.3 2.4 1.7 1.3	25.1 10.2 7.0 5.0	ns
t <sub>EN</sub>	Output Enable Time, OE to Y	1.65-1.95 2.3 - 2.7 3.0 - 3.6 4.5 - 5.5	Refer to switch positions and loading conditions in Figure 17 to 21.	3.4 2.1 1.3 1.0		24.7 11 7.5 5.7	3.4 2.1 1.3 1.0	24.7 12 8.0 6.2	3.4 2.1 1.3 1.0	24.7 12.2 8.3 6.5	ns
t <sub>DIS</sub>	Output Disable Time, OE to Y	1.65-1.95 2.3 - 2.7 3.0 - 3.6 4.5 - 5.5	Refer to switch positions and loading conditions in Figure 17 to 21.	4.0 2.7 3.5 2.0		15.5 7.5 7.0 5.5	4.0 2.7 3.5 2.0	15.5 7.5 7.0 5.5	4.0 2.7 3.5 2.0	15.5 7.5 7.0 5.5	ns
t <sub>PLH</sub> , t <sub>PHL</sub>	Propagation Delay, Any Input to Output Y (See Test Circuit)	1.65–1.95 2.3 – 2.7 3.0 – 3.6 4.5 – 5.5	Refer to switch Positions and loading conditions in Figure 22 to 26.	4.3 2.5 2.3 1.6	13.6 7.8 5.6 4.4	25.7 10.7 7.6 5.2	4.3 2.5 2.3 1.6	25.7 10.7 7.6 5.2	4.3 2.5 2.3 1.6	25.7 10.7 7.6 5.2	ns
t <sub>EN</sub>	Output Enable Time, OE to Y	1.65–1.95 2.3 – 2.7 3.0 – 3.6 4.5 – 5.5	Refer to switch Positions and loading conditions in Figure 22 to 26.	4.2 2.4 2.0 1.7		25.2 11.3 8.0 6.0	4.2 2.4 2.0 1.7	25.2 12.2 8.5 6.5	4.2 2.4 2.0 1.7	25.2 13 8.7 6.7	ns
t <sub>DIS</sub>	Output Disable Time, OE to Y	1.65–1.95 2.3 – 2.7 3.0 – 3.6 4.5 – 5.5	Refer to switch Positions and loading conditions in Figure 22 to 26.	3.7 2.0 2.1 1.0		15 6.5 5.6 4.5	3.7 2.0 2.1 1.0	15 6.7 5.8 4.7	3.7 2.0 2.1 1.0	15 6.9 5.9 4.9	ns
C <sub>IN</sub>	Input Capacitance	3.3			3.5						pF
Co	Output Capacitance	3.3			6.0						pF
C <sub>PD</sub>	Power Dissipation Capacitance (Note 6)	3.3	f = 10 MHz		22						pF

<sup>6.</sup> C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the dynamic operating current consumption without load. Average operating current can be obtained by the equation I<sub>CC(OPR)</sub> = C<sub>PD</sub> • V<sub>CC</sub> • f<sub>in</sub> + I<sub>CC</sub>. C<sub>PD</sub> is used to determine the no–load dynamic power consumption: P<sub>D</sub> = C<sub>PD</sub> • V<sub>CC</sub><sup>2</sup> • f<sub>in</sub> + I<sub>CC</sub> • V<sub>CC</sub>.


#### **TEST CIRCUIT AND VOLTAGE WAVEFORMS**



Test	S1			
t <sub>PLH</sub> /t <sub>PHL</sub>	Open			
t <sub>PLZ</sub> /t <sub>PZL</sub>	$V_{LOAD}$			
t <sub>PHZ</sub> /t <sub>PZH</sub>	GND			

Figure 17. Load Circuit

	Inputs						
V <sub>CC</sub>	VI	t <sub>r</sub> /t <sub>f</sub>	V <sub>M</sub>	$V_{LOAD}$	CL	$R_{L}$	$V_{\Delta}$
$1.8 \ V \ \pm \ 0.15 \ V$	V <sub>CC</sub>	≤ 2 ns	V <sub>CC</sub> /2	2 x V <sub>CC</sub>	15 pF	1 ΜΩ	0.15 V
$2.5 \ V \ \pm \ 0.2 \ V$	V <sub>CC</sub>	≤ 2 ns	V <sub>CC</sub> /2	2 x V <sub>CC</sub>	15 pF	1 ΜΩ	0.15 V
$3.3~V~\pm~0.3~V$	3 V	≤ 2.5 ns	1.5 V	6 V	15 pF	1 ΜΩ	0.3 V
5.5 V ± 0.5 V	V <sub>CC</sub>	≤ 2.5 ns	V <sub>CC</sub> /2	2 x V <sub>CC</sub>	15 pF	1 ΜΩ	0.3 V






Figure 18. Voltage Waveforms Pulse Duration

Output V<sub>M</sub> V<sub>M</sub> 0 V

V<sub>M</sub> 0 V

V<sub>M</sub> V<sub>OH</sub>

Figure 20. Voltage Waveforms Propagation Delay Times Inverting and Noninverting Outputs

Figure 19. Voltage Waveforms Setup and Hold Times





Figure 21. Voltage Waveforms Enable and Disable Times Low- and High-Level Enabling

- 7. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control
- 8. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_0 = 50 \Omega$ .
- 9. The outputs are measured one at a time, with one transition per measurement.
- 10. All parameters are waveforms are not applicable to all devices.


<sup>\*</sup>C<sub>L</sub> includes probes and jig capacitance.



Test	S1	
t <sub>PLH</sub> /t <sub>PHL</sub>	Open	
t <sub>PLZ</sub> /t <sub>PZL</sub>	$V_{LOAD}$	
t <sub>PHZ</sub> /t <sub>PZH</sub>	GND	

Figure 22. Load Circuit

	Inputs						
V <sub>CC</sub>	VI	t <sub>r</sub> /t <sub>f</sub>	$V_{M}$	V <sub>LOAD</sub>	$c_L$	$R_{L}$	$V_\Delta$
1.8 V ± 0.15 V	V <sub>CC</sub>	≤ 2 ns	V <sub>CC</sub> /2	2 x V <sub>CC</sub>	30 pF	1 kΩ	0.15 V
2.5 V ± 0.2 V	V <sub>CC</sub>	≤ 2 ns	V <sub>CC</sub> /2	2 x V <sub>CC</sub>	30 pF	500 Ω	0.15 V
3.3 V ± 0.3 V	3 V	≤ 2.5 ns	1.5 V	6 V	50 pF	500 Ω	0.3 V
5.5 V ± 0.5 V	V <sub>CC</sub>	≤ 2.5 ns	V <sub>CC</sub> /2	2 x V <sub>CC</sub>	50 pF	500 Ω	0.3 V






Figure 23. Voltage Waveforms Pulse Duration

Output V<sub>M</sub> V<sub>M</sub> O V

Output V<sub>M</sub> V<sub>M</sub> V<sub>OL</sub>

V<sub>M</sub> V<sub>OL</sub>

V<sub>M</sub> V<sub>OL</sub>

V<sub>M</sub> V<sub>OL</sub>

V<sub>M</sub> V<sub>OL</sub>

Figure 25. Voltage Waveforms Propagation Delay Times Inverting and Noninverting Outputs

Figure 24. Voltage Waveforms Setup and Hold Times




Figure 26. Voltage Waveforms Enable and Disable Times Low- and High-Level Enabling

- 11. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control
- 12. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_0 = 50 \Omega$ .
- 13. The outputs are measured one at a time, with one transition per measurement.
- 14. All parameters are waveforms are not applicable to all devices.

<sup>\*</sup>C1 includes probes and jig capacitance.


## **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>		
NLX1G99DMUTCG	UDFN8, 1.95 x 1.0, 0.5P (Pb-Free)	3000 / Tape & Reel		
NLX1G99DMUTWG	UDFN8, 1.95 x 1.0, 0.5P (Pb-Free)	3000 / Tape & Reel		
NLX1G99EMUTCG (In Development)	UDFN8, 1.6 x 1.0, 0.4P (Pb-Free)	3000 / Tape & Reel		
NLX1G99FMUTCG (In Development)	UDFN8, 1.45 x 1.0, 0.35P (Pb-Free)	3000 / Tape & Reel		

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### **PACKAGE DIMENSIONS**

UDFN8 1.6x1.0, 0.4P CASE 517BY ISSUE O



- NOTES:

  1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.


  2. CONTROLLING DIMENSION: MILLIMETERS.

  3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 MM FROM TERMINAL TIP.

  4. PACKAGE DIMENSIONS EXCLUSIVE OF BURRS AND MOLD FLASH.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.45	0.55	
A1	0.00	0.05	
А3	0.13 REF		
b	0.15	0.25	
D	1.60 BSC		
Е	1.00 BSC		
е	0.40 BSC		
Ĺ	0.25	0.35	
L1	0.30	0.40	


#### **RECOMMENDED SOLDERING FOOTPRINT\***



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### **PACKAGE DIMENSIONS**

#### UDFN8 1.45x1.0, 0.35P CASE 517BZ ISSUE O



- NOTES:

  1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.


  2. CONTROLLING DIMENSION: MILLIMETERS.

  3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 MM FROM TERMINAL TIP.

  4. PACKAGE DIMENSIONS EXCLUSIVE OF BURRS AND MOLD FLASH.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.45	0.55	
A1	0.00	0.05	
A3	0.13 REF		
b	0.15	0.25	
D	1.45 BSC		
E	1.00 BSC		
е	0.35 BSC		
L	0.25	0.35	
L1	0.30	0.40	


#### **RECOMMENDED SOLDERING FOOTPRINT\***



\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### PACKAGE DIMENSIONS


UDFN8 1.95x1.0, 0.5P CASE 517CA **ISSUE O** 



- NOTES:
  1. DIMENSIONING AND TOLERANCING PER
- ASME Y14.5M, 1994. CONTROLLING DIMENSION: MILLIMETERS.
- DIMENSION 6 APPLIES TO PLATED
  TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 MM FROM TERMINAL TIP. PACKAGE DIMENSIONS EXCLUSIVE OF
- BURRS AND MOLD FLASH.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.45	0.55	
A1	0.00	0.05	
А3	0.13 REF		
b	0.15	0.25	
D	1.95 BSC		
Е	1.00 BSC		
е	0.50 BSC		
L	0.25	0.35	
L1	0.30	0.40	

#### **RECOMMENDED SOLDERING FOOTPRINT\***



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MiniGate is a trademark of Semiconductor Components Industries, LLC (SCILLC).

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. Coverage may be accessed at <a href="https://www.onsemi.com/site/par/-atent\_-warking.pgr">www.onsemi.com/site/par/-atent\_-warking.pgr</a>. On Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

## LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative