

## Is Now Part of



# ON Semiconductor®

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to Fairchild <a href="guestions@onsemi.com">guestions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer





# FDMF6706C – Extra-Small, High-Performance, High-Frequency DrMOS Module

#### **Benefits**

- Ultra-Compact 6x6 mm PQFN, 72% Space-Saving Compared to Conventional Discrete Solutions
- Fully Optimized System Efficiency
- Clean Switching Waveforms with Minimal Ringing
- High-Current Handling

#### **Features**

- Over 93% Peak-Efficiency
- High-Current Handling of 43 A
- High-Performance PQFN Copper Clip Package
- 3-State 5 V PWM Input Driver
- Shorter Propagation Delays than FDMF6704
- Shorter Dead Times than FDMF6704
- Skip-Mode SMOD# (Low-Side Gate Turn Off) Input
- Thermal Warning Flag for Over-Temperature Condition
- Driver Output Disable Function (DISB# Pin)
- Internal Pull-Up and Pull-Down for SMOD# and DISB# Inputs, Respectively
- Fairchild PowerTrench® Technology MOSFETs for Clean Voltage Waveforms and Reduced Ringing
- Fairchild SyncFET™ (Integrated Schottky Diode)
   Technology in the Low-Side MOSFET
- Integrated Bootstrap Schottky Diode
- Adaptive Gate Drive Timing for Shoot-through Protection
- Under-Voltage Lockout (UVLO)
- Optimized for Switching Frequencies up to 1 MHz
- Low-Profile SMD Package
- Fairchild Green Packaging and RoHS Compliant
- Based on the Intel® 4.0 DrMOS Standard

## Description

The XS™ DrMOS family is Fairchild's next-generation, fully optimized, ultra-compact, integrated MOSFET plus driver power stage solutions for high-current, high-frequency, synchronous buck DC-DC applications. The FDMF6706C integrates a driver IC, two power MOSFETs, and a bootstrap Schottky diode into a thermally enhanced, ultra-compact 6x6 mm PQFN package.

With an integrated approach, the complete switching power stage is optimized with regards to driver and MOSFET dynamic performance, system inductance, and Power MOSFET  $R_{DS(ON)}.$  XS $^{\intercal}$  DrMOS uses Fairchild's high-performance PowerTrench® MOSFET technology, which dramatically reduces switch ringing, eliminating the need for a snubber circuit in most buck converter applications.

A new driver IC with reduced dead times and propagation delays further enhances the performance of this part. A thermal warning function has been included to warn of a potential over-temperature situation. The FDMF6706C also incorporates features, such as Skip Mode (SMOD), for improved light-load efficiency along with a 3-state 5 V PWM input for compatibility with a wide range of PWM controllers.

## **Applications**

- High-Performance Gaming Motherboards
- Compact Blade Servers, V-Core and Non-V-Core DC-DC Converters
- Desktop Computers, V-Core and Non-V-Core DC-DC Converters
- Workstations
- High-Current DC-DC Point-of-Load (POL) Converters
- Networking and Telecom Microprocessor Voltage Regulators
- Small Form-Factor Voltage Regulator Modules

# **Ordering Information**

Part Number	Current Rating	Input Voltage	Switching Frequency	Package	Top Mark
FDMF6706C	40 A	12 V	1000 kHz	40-Lead, Clipbond PQFN DrMOS, 6.0x6.0 mm Package	FDMF6706C

# **Typical Application Circuit**






Figure 1. Typical Application Circuit

# **DrMOS Block Diagram**



# **Pin Configuration**








Figure 4. Top View

## **Pin Definitions**

Pin#	Name	Description
1	SMOD#	When SMOD#=HIGH, the low-side driver is the inverse of PWM input. When SMOD#=LOW, the low-side driver is disabled. This pin has a 10 $\mu$ A internal pull-up current source. Do not add a noise filter capacitor.
2	VCIN	IC bias supply. Minimum 1 $\mu\text{F}$ ceramic capacitor is recommended from this pin to CGND.
3	VDRV	Power for gate driver. Minimum 1 $\mu F$ ceramic capacitor is recommended to be connected as close as possible from this pin to CGND.
4	воот	Bootstrap supply input. Provides voltage supply to high-side MOSFET driver. Connect bootstrap capacitor from this pin to PHASE.
5, 37, 41	CGND	IC ground. Ground return for driver IC.
6	GH	For manufacturing test only. This pin must float. Must not be connected to any pin.
7	PHASE	Switch node pin for bootstrap capacitor routing. Electrically shorted to VSWH pin.
8	NC	No connect. The pin is not electrically connected internally, but can be connected to VIN for convenience.
9 - 14, 42	VIN	Power input. Output stage supply voltage.
15, 29 - 35, 43	VSWH	Switch node input. Provides return for high-side bootstrapped driver and acts as a sense point for the adaptive shoot-through protection.
16 – 28	PGND	Power ground. Output stage ground. Source pin of low-side MOSFET.
36	GL	For manufacturing test only. This pin must float. Must not be connected to any pin.
38	THWN#	Thermal warning flag, open collector output. When temperature exceeds the trip limit, the output is pulled LOW. THWN# does not disable the module.
39	DISB#	Output disable. When LOW, this pin disables Power MOSFET switching (GH and GL are held LOW). This pin has a 10 $\mu$ A internal pull-down current source. Do not add a noise filter capacitor.
40	PWM	PWM signal input. This pin accepts a 3-state 5 V PWM signal from the controller.

# **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter				Min.	Max.	Unit
	VCIN, VDRV, DISB#, PWM, SMOD#, GL, THWN# to CGND Pins					6	
	VIN to PGND, CGND Pins					25	
	BOOT, GH to VSWH, PHASE Pins					6	V
	VSWH, PHASE to PGND, CGND Pin	S				25	V
	BOOT to PGND, CGND Pins					27	
	BOOT to VDRV					22	
I <sub>O(AV)</sub> <sup>(1)</sup>	V <sub>IN</sub> =12 V, V <sub>O</sub> =1.0 V	f <sub>SW</sub> =300 kHz				43	Α
IO(AV)		f <sub>SW</sub> =1 MHz				40	А
Ө <sub>ЈРСВ</sub>	Junction-to-PCB Thermal Resistance					3.5	°C/W
T <sub>STG</sub>	Operating and Storage Temperature Range		-55	+150	°C		
ECD	Floatractatic Discharge Protection	Human Body Model, JESD22-A114		<b>A114</b>	2000		V
ESD	Electrostatic Discharge Protection Charged Device Model, JESD22-C101		2000	\ \	\ \		

#### Note:

1. I<sub>O(AV)</sub> is rated using Fairchild's DrMOS evaluation board, at T<sub>A</sub> = 25°C, with natural convection cooling. This rating is limited by the peak DrMOS temperature, T<sub>J</sub> = 150°C, and varies depending on operating conditions and PCB layout. This rating can be changed with different application settings.

# **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter	Min.	Тур.	Max.	Unit
$V_{CIN}$	Control Circuit Supply Voltage	4.5	5.0	5.5	V
$V_{DRV}$	Gate Drive Circuit Supply Voltage	4.5	5.0	5.5	V
$V_{IN}$	Output Stage Supply Voltage <sup>(2)</sup>	3.0	12.0	15.0	٧

#### Note:

 Operating at high V<sub>IN</sub> can create excessive AC overshoots on the VSWH-to-GND and BOOT-to-GND nodes during MOSFET switching transients. For reliable DrMOS operation, VSWH-to-GND and BOOT-to-GND must remain at or below the Absolute Maximum Ratings shown in the table above. Refer to the "Application Information" and "PCB Layout Guidelines" sections of this datasheet for additional information.

# **Electrical Characteristics**

Typical values are  $V_{IN}$  = 12 V,  $V_{CIN}$  = 5 V,  $V_{DRV}$  = 5 V, and  $T_A$  = +25°C unless otherwise noted.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
Basic Oper	ation	•		•		
IQ	Quiescent Current	I <sub>Q</sub> =I <sub>VCIN</sub> +I <sub>VDRV</sub> , PWM=LOW or HIGH or Float			2	mA
UVLO	UVLO Threshold	V <sub>CIN</sub> Rising	2.9	3.1	3.3	V
UVLO_Hyst	UVLO Hysteresis			0.4		V
PWM Input					•	
R <sub>UP_PWM</sub>	Pull-Up Impedance			10		kΩ
R <sub>DN_PWM</sub>	Pull-Down Impedance			10		kΩ
$V_{\text{IH\_PWM}}$	PWM High Level Voltage		3.30	3.55	3.80	V
V <sub>TRI_HI</sub>	3-State Rising Threshold		3.20	3.45	3.70	V
$V_{TRI\_LO}$	3-State Falling Threshold		1.00	1.25	1.50	V
$V_{\text{IL\_PWM}}$	PWM Low Level Voltage		0.85	1.15	1.40	V
t <sub>D_HOLD-OFF</sub>	3-State Shutoff Time			160	200	ns
V <sub>HiZ_PWM</sub>	3-State Open Voltage		2.3	2.5	2.7	V
DISB# Inpu	t					
V <sub>IH_DISB</sub>	High-Level Input Voltage		2			V
V <sub>IL DISB</sub>	Low-Level Input Voltage				0.8	V
I <sub>PLD</sub>	Pull-Down Current			10		μA
t <sub>PD_DISBL</sub>	Propagation Delay	PWM=GND, Delay Between DISB# from HIGH to LOW to GL from HIGH to LOW		25		ns
t <sub>PD_DISBH</sub>	Propagation Delay	PWM=GND, Delay Between DISB# from LOW to HIGH to GL from LOW to HIGH		25		ns
SMOD# Inp	out					
V <sub>IH_SMOD</sub>	High-Level Input Voltage		2			V
V <sub>IL SMOD</sub>	Low-Level Input Voltage				0.8	V
I <sub>PLM</sub>	Pull-Up Current			10		μA
t <sub>PD_SLGLL</sub>	Propagation Delay	PWM=GND, Delay Between SMOD# from HIGH to LOW to GL from HIGH to LOW		10		ns
t <sub>PD_SHGLH</sub>	Propagation Delay	PWM=GND, Delay Between SMOD# from LOW to HIGH to GL from LOW to HIGH		10		ns
Thermal Wa	arning Flag				/	
T <sub>ACT</sub>	Activation Temperature			150		°C
T <sub>RST</sub>	Reset Temperature			135		°C
R <sub>THWN</sub>	Pull-Down Resistance	I <sub>PLD</sub> =5 mA		30		Ω
	out Circuit	•		•	TE	
t <sub>D_ТІМЕО</sub>	Timeout Delay	SW=0V, Delay Between GH from HIGH to LOW and GL from LOW to HIGH		250	1	ns

Continued on the following page...

# **Electrical Characteristics**

Typical values are  $V_{IN}$  = 12 V,  $V_{CIN}$  = 5 V,  $V_{DRV}$  = 5 V, and  $T_A$  = +25°C unless otherwise noted.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit	
High-Side Driver							
R <sub>SOURCE_GH</sub>	Output Impedance, Sourcing	Source Current=100 mA		1		Ω	
R <sub>SINK_GH</sub>	Output Impedance, Sinking	Sink Current=100 mA		0.8		Ω	
t <sub>R_GH</sub>	Rise Time	GH=10% to 90%, C <sub>LOAD</sub> =1.1 nF		12		ns	
t <sub>F_GH</sub>	Fall Time	GH=90% to 10%, C <sub>LOAD</sub> =1.1 nF		11		ns	
t <sub>D_DEADON</sub>	LS to HS Deadband Time	GL going LOW to GH going HIGH, 2 V GL to 10 % GH		10		ns	
t <sub>PD_PLGHL</sub>	PWM LOW Propagation Delay	PWM going LOW to GH going LOW, V <sub>IL_PWM</sub> to 90% GH		16	30	ns	
t <sub>PD_PHGHH</sub>	PWM HIGH Propagation Delay (SMOD Held LOW)	PWM going HIGH to GH going HIGH, V <sub>IH_PWM</sub> to 10% GH (SMOD=LOW)		30		ns	
t <sub>PD_TSGHH</sub>	Exiting 3-State Propagation Delay	PWM (from 3-State) going HIGH to GH going HIGH, V <sub>IH_PWM</sub> to 10% GH		30		ns	
Low-Side D	Priver						
R <sub>SOURCE_GL</sub>	Output Impedance, Sourcing	Source Current=100 mA		1		Ω	
R <sub>SINK_GL</sub>	Output Impedance, Sinking	Sink Current=100 mA		0.5		Ω	
t <sub>R_GL</sub>	Rise Time	GL=10% to 90%, C <sub>LOAD</sub> =2.7 nF		12		ns	
t <sub>F_GL</sub>	Fall Time	GL=90% to 10%, C <sub>LOAD</sub> =2.7 nF		8		ns	
t <sub>D_DEADOFF</sub>	HS to LS Deadband Time	SW going LOW to GL going HIGH, 2.2 V SW to 10% GL		12		ns	
t <sub>PD_PHGLL</sub>	PWM-HIGH Propagation Delay	PWM going HIGH to GL going LOW, V <sub>IH_PWM</sub> to 90% GL		9	25	ns	
t <sub>PD_TSGLH</sub>	Exiting 3-State Propagation Delay	PWM (from 3-State) going LOW to GL going HIGH, V <sub>IL_PWM</sub> to 10% GL		20		ns	
<b>Boot Diode</b>				•			
$V_{F}$	Forward-Voltage Drop	I <sub>F</sub> =10 mA		0.35		V	
$V_R$	Breakdown Voltage	I <sub>R</sub> =1 mA	22			V	





Figure 5. PWM Timing Diagram

# **Typical Performance Characteristics**

Test Conditions:  $V_{IN}=12 \text{ V}$ ,  $V_{OUT}=1.0 \text{ V}$ ,  $V_{CIN}=5 \text{ V}$ ,  $V_{DRV}=5 \text{ V}$ ,  $V_{OUT}=320 \text{ nH}$ ,  $T_A=25^{\circ}\text{C}$ , and natural convection cooling, unless otherwise specified.






Figure 6. Safe Operating Area




Figure 7. Module Power Loss vs. Output Current




Figure 8. Power Loss vs. Switching Frequency




Figure 10. Power Loss vs. Driver Supply Voltage

Figure 9. Power Loss vs. Input Voltage





Figure 11. Power Loss vs. Output Voltage

# **Typical Performance Characteristics** (Continued)

Test Conditions:  $V_{IN}$ =12 V,  $V_{OUT}$ =1.0 V,  $V_{CIN}$ =5 V,  $V_{DRV}$ =5 V,  $L_{OUT}$ =320 nH,  $T_A$ =25°C, and natural convection cooling, unless otherwise specified.







Figure 12. Power Loss vs. Output Inductance

Figure 13. Driver Supply Current vs. Frequency








Figure 14. Driver Supply Current vs. Driver Supply Voltage

Figure 15. Driver Supply Current vs. Output Current

VIH





VDRV = 12V

1.88

1.85

1.83


Figure 16. PWM Thresholds vs. Temperature

Figure 17. DISB# Thresholds vs. Temperature

200

# **Typical Performance Characteristics** (Continued)

Test Conditions:  $V_{IN}$ =12 V,  $V_{OUT}$ =1.0 V,  $V_{CIN}$ =5 V,  $V_{DRV}$ =5 V,  $L_{OUT}$ =320 nH,  $T_A$ =25°C, and natural convection cooling, unless otherwise specified.






Figure 18. SMOD# Thresholds vs. Temperature

Figure 19. BOOT Diode V<sub>F</sub> vs. Temperature

# **Functional Description**

The FDMF6706C is a driver-plus-FET module optimized for the synchronous buck converter topology. A single PWM input signal is all that is required to properly drive the high-side and the low-side MOSFETs. Each part is capable of driving speeds up to 1 MHz.

#### **VCIN** and Disable

The VCIN pin is monitored by an under-voltage lockout (UVLO) circuit. When  $V_{\text{CIN}}$  rises above ~3.1 V, the driver is enabled for operation. When  $V_{\text{CIN}}$  falls below ~2.7 V, the driver is disabled (GH, GL=0). The driver can also be disabled by pulling the DISB# pin LOW (DISB# <  $V_{\text{IL\_DISB}}$ ), which holds both GL and GH LOW regardless of the PWM input state. The driver can be enabled by raising the DISB# pin voltage HIGH (DISB# >  $V_{\text{IH\_DISB}}$ ).

Table 1. UVLO and Disable Logic

UVLO	DISB#	Driver State		
0	Х	Disabled (GH, GL=0)		
1	0	Disabled (GH, GL=0)		
1	1	Enabled (See Table 2)		
1	Open	Disabled (GH, GL=0)		

#### Note:

 DISB# has an internal pull-down current source of 10 μA.

## **Thermal Warning Flag**

The FDMF6706C provides a thermal warning flag (THWN) to warn of over-temperature conditions. The thermal warning flag uses an open-drain output that pulls to CGND when the activation temperature (150°C) is reached. The THWN output returns to a high-impedance state once the temperature falls to the reset temperature (135°C). For use, the THWN output requires a pull-up resistor, which can be connected to VCIN. THWN does NOT disable the DrMOS module.




Figure 20. THWN Operation

### 3-State PWM Input

The FDMF6706C incorporates a 3-state 5 V PWM input gate drive design. The 3-state gate drive has both logic HIGH level and LOW level, along with a 3-state shutdown window. When the PWM input signal enters and remains within the 3-state window for a defined hold-off time ( $t_{D\_HOLD\text{-}OFF}$ ), both GL and GH are pulled LOW. This feature enables the gate drive to shut down both high-and low-side MOSFETs to support features such as phase shedding, which is a common feature on multiphase voltage regulators.

## **Operation when Exiting 3-State Condition**

When exiting a valid 3-state condition, the FDMF6706C design follows the PWM input command. If the PWM input goes from 3-state to LOW, the low side MOSFET is turned on. If the PWM input goes from 3-state to HIGH, the high-side MOSFET is turned on. This is illustrated in Figure 21. The FDMF6706C design allows for short propagation delays when exiting the 3-state window (see Electrical Characteristics).

#### **Low-Side Driver**

The low-side driver (GL) is designed to drive a ground-referenced low  $R_{DS(ON)}$  N-channel MOSFET. The bias for GL is internally connected between VDRV and CGND. When the driver is enabled, the driver's output is 180° out of phase with the PWM input. When the driver is disabled (DISB#=0 V), GL is held LOW.


#### **High-Side Driver**

The high-side driver is designed to drive a floating Nchannel MOSFET. The bias voltage for the high-side driver is developed by a bootstrap supply circuit, consisting of the internal Schottky diode and external bootstrap capacitor (C<sub>BOOT</sub>). During startup, VSWH is held at PGND, allowing CBOOT to charge to VDRV through the internal diode. When the PWM input goes HIGH, GH begins to charge the gate of the high-side MOSFET (Q1). During this transition, the charge is removed from C<sub>BOOT</sub> and delivered to the gate of Q1. As Q1 turns on, V<sub>SWH</sub> rises to V<sub>IN</sub>, forcing the BOOT pin to V<sub>IN</sub> + V<sub>BOOT</sub>, which provides sufficient V<sub>GS</sub> enhancement for Q1. To complete the switching cycle, Q1 is turned off by pulling GH to VSWH. CBOOT is then recharged to VDRV when VSWH falls to PGND. GH output is inphase with the PWM input. The high-side gate is held LOW when the driver is disabled or the PWM signal is held within the 3-state window for longer than the 3state hold-off time,  $t_D$  HOLD-OFF.

## **Adaptive Gate Drive Circuit**

The driver IC advanced design ensures minimum MOSFET dead-time while eliminating potential shoot through (cross-conduction) currents. It senses the state of the MOSFETs and adjusts the gate drive adaptively to ensure they do not conduct simultaneously. Figure 21 provides the relevant timing waveforms. To prevent overlap during the LOW-to-HIGH switching transition (Q2 off to Q1 on), the adaptive circuitry monitors the voltage at the GL pin. When the PWM signal goes HIGH, Q2 begins to turn off after some propagation delay (tpD\_PHGLL). Once the GL pin is discharged below ~2 V, Q1 begins to turn on after adaptive delay

 $t_{\rm D\_DEADON}$ . To preclude overlap during the HIGH-to-LOW transition (Q1 off to Q2 on), the adaptive circuitry monitors the voltage at the VSWH pin. When the PWM signal goes LOW, Q1 begins to turn off after some propagation delay ( $t_{\rm PD\_PLGHL}$ ). Once the VSWH pin falls below ~2.2 V, Q2 begins to turn on after adaptive delay  $t_{\rm D\_DEADOFF}$ . Additionally,  $V_{\rm GS(Q1)}$  is monitored. When  $V_{\rm GS(Q1)}$  is discharged below ~1.2 V, a secondary adaptive delay is initiated, which results in Q2 being driven on after  $t_{\rm D\_TIMEOUT}$ , regardless of SW state. This function is implemented to ensure  $C_{\rm BOOT}$  is recharged each switching cycle in the event that the SW voltage does not fall below the 2.2 V adaptive threshold. Secondary delay  $t_{\rm D\_TIMEOUT}$  is longer than  $t_{\rm D\_DEADOFF}$ .






Figure 21. PWM and 3-StateTiming Diagram

## Skip Mode (SMOD)

The SMOD function allows for higher converter efficiency under light-load conditions. During SMOD, the low-side FET gate signal is disabled (held LOW), preventing discharging of the output capacitors as the filter inductor current attempts reverse current flow – also known as "Diode Emulation" Mode.

When the SMOD pin is pulled HIGH, the synchronous buck converter works in Synchronous Mode, gating on the low-side FET. When the SMOD pin is pulled LOW, the low-side FET is gated off. The SMOD pin is connected to the PWM controller, which enables or disables the SMOD automatically when the controller detects light-load condition from output current sensing. Normally this pin is active LOW. See Figure 22 for timing delays.

Table 2. SMOD Logic

DISB#	PWM	SMOD#	GH	GL
0	Х	Х	0	0
1	3-State	Х	0	0
1	0	0	0	0
1	1	0	1	0
1	0	1	0	1
1	1	1	1	0

#### Note:

 The SMOD feature is intended to have low propagation delay between the SMOD signal and the low-side FET VGS response time to control diode emulation on a cycle-by-cycle basis.




Figure 22. SMOD Timing Diagram

# **Application Information**

## **Supply Capacitor Selection**

For the supply input ( $V_{CIN}$ ), a local ceramic bypass capacitor is recommended to reduce noise and to supply the peak current. Use at least a 1  $\mu$ F X7R or X5R capacitor. Keep this capacitor close to the VCIN pin and connect it to the GND plane with vias.

## **Bootstrap Circuit**

The bootstrap circuit uses a charge storage capacitor ( $C_{BOOT}$ ), as shown in Figure 23. A bootstrap capacitance of 100 nF X7R or X5R capacitor is adequate. A series bootstrap resistor would be needed for specific applications to improve switching noise immunity.

#### **VCIN Filter**

The VDRV pin provides power to the gate drive of the high-side and low-side power FET. In most cases, it can be connected directly to VCIN, the pin that provides power to the logic section of the driver. For additional

noise immunity, an RC filter can be inserted between VDRV and VCIN. Recommended values would be 10  $\Omega$  and 1  $\mu F.$ 

## **Power Loss and Efficiency**

#### **Measurement and Calculation**

Refer to Figure 23 for power loss testing method. Power loss calculations are:

$$\begin{split} P_{IN} = & (V_{IN} \times I_{IN}) + (V_{5V} \times I_{5V}) \text{ (W)} \\ P_{SW} = & V_{SW} \times I_{OUT} \text{ (W)} \\ P_{OUT} = & V_{OUT} \times I_{OUT} \text{ (W)} \\ P_{LOSS\_MODULE} = & P_{IN} - P_{SW} \text{ (W)} \\ P_{LOSS\_BOARD} = & P_{IN} - P_{OUT} \text{ (W)} \\ EFF_{MODULE} = & 100 \times P_{SW}/P_{IN} \text{ (%)} \\ EFF_{BOARD} = & 100 \times P_{OUT}/P_{IN} \text{ (%)} \end{split}$$




Figure 23. Power Loss Measurement Block Diagram

## **PCB Layout Guidelines**

Figure 24 provides an example of a proper layout for the FDMF6706C and critical components. All of the high-current paths, such as  $V_{\text{IN}}$ ,  $V_{\text{SWH}}$ ,  $V_{\text{OUT}}$ , and GND copper, should be short and wide for low inductance and resistance. This technique aids in achieving a more stable and evenly distributed current flow, along with enhanced heat radiation and system performance.

The following guidelines are recommendations for the PCB designer:

- Input ceramic bypass capacitors must be placed close to the VIN and PGND pins. This helps reduce the high-current power loop inductance and the input current ripple induced by the power MOSFET switching operation.
- 2. The V<sub>SWH</sub> copper trace serves two purposes. In addition to being the high-frequency current path from the DrMOS package to the output inductor, it also serves as a heat sink for the low-side MOSFET in the DrMOS package. The trace should be short and wide enough to present a lowimpedance path for the high-frequency, highcurrent flow between the DrMOS and inductor to minimize losses and temperature rise. Note that the VSWH node is a high voltage and highfrequency switching node with high noise potential. Care should be taken to minimize coupling to adjacent traces. Since this copper trace also acts as a heat sink for the lower FET, balance using the largest area possible to improve DrMOS cooling while maintaining acceptable noise emission.
- An output inductor should be located close to the FDMF6706C to minimize the power loss due to the VSWH copper trace. Care should also be taken so the inductor dissipation does not heat the DrMOS.
- 4. PowerTrench® MOSFETs are used in the output stage. The Power MOSFETs are effective at minimizing ringing due to fast switching. In most cases, no VSWH snubber is required. If a snubber is used, it should be placed close to the VSWH and PGND pins. The resistor and capacitor need to be of proper size for the power dissipation.
- VCIN, VDRV, and BOOT capacitors should be placed as close as possible to the VCIN to CGND, VDRV to CGND, and BOOT to PHASE pins to ensure clean and stable power. Routing width and length should be considered as well.
- 6. Include a trace from PHASE to VSWH to improve noise margin. Keep the trace as short as possible.

- 7. The layout should include the option to insert a small-value series boot resistor between the boot capacitor and BOOT pin. The boot-loop size, including R<sub>BOOT</sub> and C<sub>BOOT</sub>, should be as small as possible. The boot resistor is normally not required, but is effective at controlling the high-side MOSFET turn-on slew rate. This can improve noise operating margin in synchronous buck designs that may have noise issues due to ground bounce or high positive and negative VSWH ringing. Inserting a boot resistance lowers the DrMOS efficiency. Efficiency versus noise tradeoffs must be considered.
  - The VIN and PGND pins handle large current transients with frequency components greater than 100 MHz. If possible, these pins should be connected directly to the VIN and board GND planes. The use of thermal relief traces in series with these pins is discouraged since this adds inductance to the power path. This added inductance in series with either the VIN or PGND pin degrades system noise immunity by increasing positive and negative VSWH ringing.
- CGND pad and PGND pins should be connected by plane GND copper with multiple vias for stable grounding. Poor grounding can create a noise transient offset voltage level between CGND and PGND. This could lead to faulty operation of gate driver and MOSFET.
- Ringing at the BOOT pin is most effectively controlled by close placement of the boot capacitor. Do not add an additional BOOT to the PGND capacitor. This may lead to excess current flow through the BOOT diode.
- 10. The SMOD# and DISB# pins have weak internal pull-up and pull-down current sources, respectively. These pins should not have any noise filter capacitors. Do not to float these pins unless absolutely necessary.
- 11. Use multiple vias on each copper area to interconnect top, inner, and bottom layers to help distribute current flow and heat conduction. Vias should be relatively large and of reasonably low inductance. Critical high-frequency components, such as R<sub>BOOT</sub>, C<sub>BOOT</sub>, the RC snubber, and bypass capacitors should be located as close to the respective DrMOS module pins as possible on the top layer of the PCB. If this is not feasible, they should be connected from the backside through a network of low-inductance vias.





Figure 24. PCB Layout Example



ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and h

## **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative