

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese

September 2010

Motion-SPM[™]

FAIRCHILD

SEMICONDUCTOR®

FNE41060 Smart Power Module

Features

- 600V-10A 3-phase IGBT inverter bridge including control ICs for gate driving and protection
- Easy PCB layout due to built-in bootstrap diode and V_S output
- Divided negative dc-link terminals for inverter current sensing applications
- · Single-grounded power supply due to built-in HVIC
- · Built-in thermistor for over-temperature monitoring
- Isolation rating of 2000Vrms/min.

Applications

- AC 100V ~ 253V three-phase inverter drive for small power ac motor drives
- Home appliances applications like air conditioner and washing machine

General Description

It is an advanced motion-smart power module (Motion-SPMTM) that Fairchild has newly developed and designed to provide very compact and high performance ac motor drives mainly targeting low-power inverter-driven application like air conditioner and washing machine. It combines optimized circuit protection and drive matched to low-loss IGBTs. System reliability is further enhanced by the integrated under-voltage lock-out protection, short-circuit protection, and temperature monitoring. The high speed built-in HVIC provides opto-coupler-less single-sup-ply IGBT gate driving capability that further reduce the overall size of the inverter system design. Each phase current of inverter can be monitored separately due to the divided negative dc terminals.

Additional Information

For further infomation, please see AN-9070 and FEB306-001 in http://www.fairchildsemi.com






Figure 1.




Integrated Power Functions

• 600V-10A IGBT inverter for three-phase DC/AC power conversion (Please refer to Figure 3)


Integrated Drive, Protection and System Control Functions

- For inverter high-side IGBTs: Gate drive circuit, High voltage isolated high-speed level shifting
 Control circuit under-voltage (UV) protection
- For inverter low-side IGBTs: Gate drive circuit, Short circuit protection (SC) Control supply circuit under-voltage (UV) protection
- · Fault signaling: Corresponding to UV (Low-side supply) and SC faults
- Input interface: 3.3/5V CMOS compatible, Schmitt trigger input

Pin Configuration



| Pin Number | Pin Name | Pin Description |
|------------|--------------------|---|
| 1 | N.C. | No Connection |
| 2 | N.C. | No Connection |
| 3 | Р | Positive DC-Link Input |
| 4 | U | Output for U Phase |
| 5 | V | Output for V Phase |
| 6 | W | Output for W Phase |
| 7 | NU | Negative DC–Link Input for U Phase |
| 8 | N _V | Negative DC–Link Input for V Phase |
| 9 | N _W | Negative DC–Link Input for W Phase |
| 10 | C _{SC} | Capacitor (Low-pass Filter) for Short-Current Detection Input |
| 11 | V _{FO} | Fault Output |
| 12 | IN _(WL) | Signal Input for Low-side W Phase |
| 13 | IN _(VL) | Signal Input for Low-side V Phase |
| 14 | IN _(UL) | Signal Input for Low-side U Phase |
| 15 | СОМ | Common Supply Ground |
| 16 | V _{CC(L)} | Low-Side Common Bias Voltage for IC and IGBTs Driving |
| 17 | V _{CC(H)} | High-Side Common Bias Voltage for IC and IGBTs Driving |
| 18 | IN _(WH) | Signal Input for High-side W Phase |
| 19 | IN _(VH) | Signal Input for High-side V Phase |
| 20 | IN _(UH) | Signal Input for High-side U Phase |
| 21 | V _{S(W)} | High-side Bias Voltage Ground for W Phase IGBT Driving |
| 22 | V _{B(W)} | High-side Bias Voltage for W Phase IGBT Driving |
| 23 | V _{S(V)} | High-side Bias Voltage Ground for V Phase IGBT Driving |
| 24 | V _{B(V)} | High-side Bias Voltage for V Phase IGBT Driving |
| 25 | V _{S(U)} | High-side Bias Voltage Ground for U Phase IGBT Driving |
| 26 | V _{B(U)} | High-side Bias Voltage for U Phase IGBT Driving |



Note:

1) Inverter high-side is composed of three IGBTs, freewheeling diodes and one control IC for each IGBT.

Inverter low-side is composed of three IGBTs, freewheeling diodes and one control IC for each IGBT. It has gate drive and protection functions.
 Inverter power side is composed of four inverter dc-link input terminals and three inverter output terminals.

Figure 3.

Absolute Maximum Ratings (T_J = 25°C, Unless Otherwise Specified)

Inverter Part

| Symbol | Parameter | Conditions | Rating | Units |
|------------------------|--------------------------------|--|-----------|-------|
| V _{PN} | Supply Voltage | Applied between P- N_U , N_V , N_W | 450 | V |
| V _{PN(Surge)} | Supply Voltage (Surge) | Applied between P- N_U , N_V , N_W | 500 | V |
| V _{CES} | Collector-emitter Voltage | | 600 | V |
| I _{O,25} | Output Phase Current | T_{C} = 25°C, T_{J} < 150°C (Note 1) | 10 | A |
| I _{O,100} | Output Phase Current | T_{C} = 100°C, T_{J} < 150°C (Note 1) | 5 | A |
| I _{pk} | Output Peak Phase Current | T_{C} = 25°C, $T_{J} <$ 150°C, Under 1ms Pulse Width | 15 | Α |
| P _C | Collector Dissipation | T _C = 25°C per One Chip | 32 | W |
| ТJ | Operating Junction Temperature | (Note 2) | -40 ~ 150 | °C |

Note:

1. Sinusoidal PWM at V_{PN}=300V, V_{CC}=V_{BS}=15V, T_J < 150^{\circ}\, {\rm ^{\circ}C} , F_{SW}=20kHz, MI=0.9, PF=0.8

2. The maximum junction temperature rating of the power chips integrated within the SPM is 150 $^{\circ}\text{C}.$

Control Part

| Symbol | Parameter | Conditions | Rating | Units |
|-----------------|-----------------------------------|--|---------------------------|-------|
| V _{CC} | Control Supply Voltage | Applied between V _{CC(H)} , V _{CC(L)} - COM | 20 | V |
| V _{BS} | High-side Control Bias Voltage | Applied between V_B(U) - V_S(U), V_B(V) - V_S(V), V_B(W) - V_S(W) | 20 | V |
| V _{IN} | Input Signal Voltage | $\begin{array}{c} \mbox{Applied between IN}_{(UH)},\ \mbox{IN}_{(VH)},\ \mbox{IN}_{(WH)},\ \mbox{IN}_{(UL)},\\ \mbox{IN}_{(VL)},\ \mbox{IN}_{(WL)}-\mbox{COM} \end{array}$ | -0.3~V _{CC} +0.3 | V |
| V _{FO} | Fault Output Supply Voltage | Applied between V _{FO} - COM | -0.3~V _{CC} +0.3 | V |
| I _{FO} | Fault Output Current | Sink Current at V _{FO} Pin | 1 | mA |
| V _{SC} | Current Sensing Input Voltage | Applied between C _{SC} - COM | -0.3~V _{CC} +0.3 | V |

Bootstrap Diode Part

| Symbol | Parameter | Conditions | Rating | Units |
|------------------|------------------------------------|---------------------------------------|-----------|-------|
| V _{RRM} | Maximum Repetitive Reverse Voltage | | 600 | V |
| ١ _F | Forward Current | $T_{\rm C} = 25^{\circ}{\rm C}$ | 0.5 | А |
| I _{FP} | Forward Current (Peak) | T_{C} = 25°C, Under 1ms Pulse Width | 1 | А |
| Т _Ј | Operating Junction Temperature | | -40 ~ 150 | °C |

Total System

| Symbol | Parameter | Conditions | Rating | Units |
|-----------------------|--|---|-----------|------------------|
| V _{PN(PROT)} | Self Protection Supply Voltage Limit (Short Circuit Protection Capability) | $V_{CC} = V_{BS} = 13.5 \sim 16.5 V$ T _J = 150°C, Non-repetitive, less than 2µs | 400 | V |
| T _{STG} | Storage Temperature | | -40 ~ 125 | °C |
| V _{ISO} | Isolation Voltage | 60Hz, Sinusoidal, AC 1 minute, Connection Pins to heat sink plate | 2000 | V _{rms} |

Thermal Resistance

| Symbol | Parameter | Conditions | Min. | Тур. | Max. | Units |
|-----------------------|------------|-------------------------------------|------|------|------|-------|
| un(j-c)Q | Resistance | Inverter IGBT part (per 1/6 module) | - | - | 3.8 | °C/W |
| R _{th(j-c)F} | | Inverter FWD part (per 1/6 module) | - | - | 4.8 | °C/W |

Note:

3. For the measurement point of case temperature(T_C), please refer to Figure 2.

Electrical Characteristics (T_J = 25°C, Unless Otherwise Specified)

Inverter Part

| S | ymbol | Parameter | Cond | Conditions | | Тур. | Max. | Units |
|----|---------------------|--------------------------------------|--|--|------|------|------|-------|
| V | CE(SAT) | Collector-Emitter Saturation Voltage | V _{CC} = V _{BS} = 15V V _{IN} = 5V | I _C = 5A, T _J = 25°C | - | 1.5 | 2.0 | V |
| | V _F | FWD Forward Voltage | V _{IN} = 0V | $I_{\rm F}$ = 5A, $T_{\rm J}$ = 25°C | - | 1.5 | 2.0 | V |
| HS | t _{ON} | Switching Times | V_{PN} = 300V, V_{CC} = V_{B} | _S = 15V, I _C = 5A | 0.45 | 0.75 | 1.25 | μS |
| | t _{C(ON)} | | 0 | $T_J = 25^{\circ}C$ $V_{IN} = 0V \leftrightarrow 5V$, Inductive Load | | 0.20 | 0.45 | μS |
| | t _{OFF} | | (Note 4) | | - | 0.70 | 1.20 | μS |
| | t _{C(OFF)} | | | | - | 0.15 | 0.40 | μS |
| | t _{rr} | | | | - | 0.15 | - | μS |
| LS | t _{ON} | | V _{PN} = 300V, V _{CC} = V _B | _S = 15V, I _C = 5A | 0.35 | 0.65 | 1.15 | μS |
| | t _{C(ON)} | | $T_J = 25^{\circ}C$ $V_{IN} = 0V \leftrightarrow 5V$, Induct | ive Load | - | 0.15 | 0.40 | μS |
| | t _{OFF} | | (Note 4) | | - | 0.65 | 1.15 | μS |
| | t _{C(OFF)} | | | | - | 0.15 | 0.40 | μS |
| | t _{rr} | | | | - | 0.15 | - | μS |
| | I _{CES} | Collector-Emitter Leakage Current | V _{CE} = V _{CES} | | - | - | 1 | mA |

Note:

4. t_{ON} and t_{OFF} include the propagation delay time of the internal drive IC. t_{C(ON)} and t_{C(OFF)} are the switching time of IGBT itself under the given gate driving condition internally. For the detailed information, please see Figure 4.





Figure 4. Switching Time Definition






Control Part

| Symbol | Parameter | Conditions | | Min. | Тур. | Max. | Units |
|----------------------|---|---|---|------|------|------|-------|
| I _{QCCH} | Quiescent V _{CC} Supply | $V_{CC(H)}$ = 15V, IN _(UH,VH,WH) = 0V | V _{CC(H)} - COM | - | - | 0.10 | mA |
| IQCCL | Current | $V_{CC(L)} = 15V, IN_{(UL,VL,WL)} = 0V$ | V _{CC(L)} - COM | - | - | 2.65 | mA |
| I _{PCCH} | Operating V _{CC} Supply Current | $V_{CC(H)}$ = 15V, f_{PWM} = 20kHz, duty=50%, applied to one PWM signal input for High-side | V _{CC(H)} - COM | - | - | 0.15 | mA |
| I _{PCCL} | | $V_{CC(L)}$ = 15V, f_{PWM} = 20kHz, duty=50%, applied to one PWM signal input for Low-side | V _{CC(L)} - COM | - | - | 3.65 | mA |
| I _{QBS} | Quiescent V _{BS} Supply Current | | $V_{B(U)} - V_{S(U)}, V_{B(V)} - V_{S(V)}, V_{B(W)} - V_{S(W)}$ | - | - | 0.30 | mA |
| I _{PBS} | Operating V _{BS} Supply Current | | $V_{B(U)} - V_{S(U)}, V_{B(V)} - V_{S(V)}, V_{B(W)} - V_{S(W)}$ | - | - | 2.00 | mA |
| V _{FOH} | Fault Output Voltage | V_{SC} = 0V, V_{FO} Circuit: 4.7k Ω to 5V F | Pull-up | 4.5 | - | - | V |
| V _{FOL} | | V_{SC} = 1V, V_{FO} Circuit: 4.7k Ω to 5V F | Pull-up | - | - | 0.5 | V |
| V _{SC(ref)} | Short Circuit Trip Level | V _{CC} = 15V (Note 5) | | 0.45 | 0.5 | 0.55 | V |
| UV _{CCD} | | Detection Level | | 10.5 | - | 13.0 | V |
| UV _{CCR} | Supply Circuit Under-Voltage | Reset Level | | 11.0 | - | 13.5 | V |
| UV_BSD | Protection | Detection Level | | 10.0 | - | 12.5 | V |
| UV_BSR | | Reset Level | | 10.5 | - | 13.0 | V |
| t _{FOD} | Fault-out Pulse Width | | | 30 | - | - | μS |
| V _{IN(ON)} | ON Threshold Voltage | Applied between IN _(UH) , IN _(VH) , IN | I _(WH) , IN _(UL) , IN _(VL) , | - | - | 2.6 | V |
| V _{IN(OFF)} | OFF Threshold Voltage | IN _(WL) - COM | | 0.8 | - | - | V |

5. Short-circuit current protection is functioning only at the low-sides.



Units

V

V

V

V/µs

μS

kHz

V

μS

-

_

-

-4

0.5

0.5

Max.

400

16.5

18.5

1

_

20

4

_

_

| Symbol | Baramatar | Conditions | Value | | |
|---|--------------------------|---|-------|------|--|
| Symbol | Parameter | Conditions | Min. | Тур. | |
| V _{PN} | Supply Voltage | Applied between P - N _U , N _V , N _W | - | 300 | |
| V _{CC} | Control Supply Voltage | Applied between V _{CC(H)} , V _{CC(L)} -COM | 13.5 | 15 | |
| V _{BS} | High-side Bias Voltage | Applied between $V_{B(U)}$ - $V_{S(U)}$, $V_{B(V)}$ - $V_{S(V)}$, $V_{B(W)}$ - $V_{S(W)}$ | 13.0 | 15 | |
| dV _{CC} /dt, dV _{BS} /dt | Control supply variation | | -1 | - | |
| t _{dead} | Blanking Time for | For Each Input Signal | 1.5 | - | |

 $-40^{\circ}C < T_{J} < 150^{\circ}C$

(Note 7)

(Including surge voltage)

Applied between $N_U,\,N_V,\,N_W\,$ - COM

Note:

 f_{PWM}

V_{SEN}

P_{WIN(ON)}

P_{WIN(OFF)}

7. SPM might not make response if input pulse width is less than the recommanded value.

Recommended Operating Conditions


Preventing Arm-short **PWM Input Signal**

Voltage for Current

Minimun Input Pulse

Sensing

Width



Note:


8. The allowable output current value may be different from the actual application.



Package Marking and Ordering Information

| Device Marking | Device | Package | Reel Size | Tape Width | Quantity |
|----------------|----------|-----------|-----------|------------|----------|
| FNE41060 | FNE41060 | SPM26-AAA | - | - | 12 |

| Deremeter | C | Limits | | | Unite | | |
|-----------------|----------------------|----------------------|------|-----------|-------|-------|--|
| Parameter | | onditions | Min. | Min. Typ. | | Units | |
| Device Flatness | Note Figure 8 | | 0 | - | +120 | μm | |
| Mounting Torque | Mounting Screw: - M3 | Recommended 0.7N•m | 0.6 | 0.7 | 0.8 | N•m | |
| | Note Figure 9 | Recommended 7.1kg•cm | 6.2 | 7.1 | 8.1 | kg•cm | |
| Weight | | - | - | 11 | - | g | |




Note:

9. Do not make over torque when mounting screws. Much mounting torque may cause ceramic cracks, as well as bolts and Al heat-sink destruction.

10. Avoid one side tightening stress. Fig.9 shows the recommended torque order for mounting screws. Uneven mounting can cause the SPM ceramic substrate to be damaged. The Pre-Screwing torque is set to 20~30% of maximum torque rating.






b4 : IGBT OFF in spite of control input condition, but there is no fault output signal.

b5 : Under voltage reset (UV_{BSR})


b6 : Normal operation: IGBT ON and carrying current

Figure 11. Under-Voltage Protection (High-side)



- c4 : IGBT turns OFF.
- c5 : Input "L" : IGBT OFF state.
- c6 : Input "H": IGBT ON state, but during the active period of fault output the IGBT doesn't turn ON.
- c7 : IGBT OFF state






Input/Output Interface Circuit

Note:

1) RC coupling at each input (parts shown dotted) might change depending on the PWM control scheme used in the application and the wiring impedance of the application's printed circuit board. The SPM input signal section integrates 5kΩ (typ.) pull-down resistor. Therefore, when using an external filtering resistor, please pay attention to the signal voltage drop at input terminal.

2) The logic input is compatible with standard CMOS outputs.

Figure 13. Recommended CPU I/O Interface Circuit



Note:

1) To avoid malfunction, the wiring of each input should be as short as possible. (less than 2-3cm)

2) By virtue of integrating an application specific type HVIC inside the SPM, direct coupling to CPU terminals without any opto-coupler or transformer isolation is possible.

3) V_{FO} output is open drain type. This signal line should be pulled up to the positive side of the MCU or control power supply with a resistor that makes I_{FO} up to 1mA. Please refer to Figure 14.

4) C_{SP15} of around 7 times larger than bootstrap capacitor C_{BS} is recommended.

5) Input signal is High-Active type. There is a $5k\Omega$ resistor inside the IC to pull down each input signal line to GND. RC coupling circuits is recommanded for the prevention of input signal oscillation. R_SC_{PS} time constant should be selected in the range 50~150ns. (Recommended $R_S=100 \Omega$, $C_{PS}=1nF$)

6) To prevent errors of the protection function, the wiring around R_F and C_{SC} should be as short as possible.

7) In the short-circuit protection circuit, please select the $R_F C_{SC}$ time constant in the range 1.5~2 μ s.

8) Each capacitor should be mounted as close to the pins of the SPM as possible.

9) To prevent surge destruction, the wiring between the smoothing capacitor and the P&GND pins should be as short as possible. The use of a high frequency non-inductive capacitor of around 0.1~0.22 μF between the P&GND pins is recommended.


10) Relays are used at almost every systems of electrical equipments of home appliances. In these cases, there should be sufficient distance between the CPU and the relays.

11) The zener diode should be adopted for the protection of ICs from the surge destruction between each pair of control supply terminals. (Recommanded zener diode=24V/1W)

12) Please choose the electrolytic capacitor with good temperature characteristic in C_{BS}. Also, choose 0.1~0.2µF R-category ceramic capacitors with good temperature and frequency characteristics in C_{BSC}.

13) For the detailed information, please refer to the AN-9070 and FEB306-001.

Figure 14. Typical Application Circuit



www.fairchildsemi.com



SEMICONDUCTOR

TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

| Build it Now™ | FRFET® | Programmable Active Droop™ | the |
|--------------------------------------|---------------------------------------|---|-------------------------|
| CorePLUS™ | Global Power Resource SM | QFET® | puwer |
| CorePOWER™ | Green FPS™ | QS™ | franchise |
| CROSSVOLT™ | Green FPS™ e-Series™ | Quiet Series™ | TinyBoost™ TinyBuck™ |
| CTL™ | GTO™ | RapidConfigure™ | TinyLogic [®] |
| Current Transfer Logic™ | IntelliMAX™ | \sim | TINYOPTO™ |
| EcoSPARK® | ISOPLANAR™ | M | TinyPower™ |
| EfficentMax™ | MegaBuck™ | Saving our world, 1mW /W /kW at a time™ | TinyPWM™ |
| EZSWITCH™ * | MICROCOUPLER™ | SmartMax™ | TinvWire™ |
| EZ | MicroFET™ | SMART START™ | TriFault Detect™ |
| | MicroPak™ | SPM® | μSerDes™ |
| T [®] | MillerDrive™ | STEALTH™ | |
| Fairchild® | MotionMax™ Matica ODMIN | SuperFET™ | SerDes |
| Fairchild Semiconductor [®] | Motion-SPM™ OPTOLOGIC [®] | SuperSOT™-3 | UHC® |
| FACT Quiet Series™ | OPTOLOGIC* OPTOPLANAR [®] | SuperSOT™-6 SuperSOT™-8 | Ultra FRFET™ |
| FACT® | OPTOPLANAR [®] | SupreMOS™ | UniFET™ |
| FAST® | | SyncFET™ | VCX™ |
| FastvCore™ | <u>U</u> | | VisualMax™ |
| FlashWriter [®] * | PDP SPM™ | | XS™ |
| FPS™ | Power-SPM™ | The Power Franchise [®] | |
| F-PFS™ | PowerTrench® | | |
| | PowerXS™ | | |

* EZSWITCH™ and FlashWriter[®] are trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

LIFE SUPPORT POLICY

EARCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

- Life support devices or systems are devices or systems which, (a) are 1 intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or 2. system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS Definition of Terms

| Datasheet Identification | Product Status | Definition |
|--------------------------|-----------------------|---|
| Advance Information | Formative / In Design | Datasheet contains the design specifications for product development. Specifications may change in any manner without notice. |
| Preliminary | First Production | Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design. |
| No Identification Needed | Full Production | Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design. |
| Obsolete | Not In Production | Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only. |

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC