

Is Now Part of

OR NEW DESIGN

# **DN Semiconductor®**

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note. As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="mailto:www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to <a href="mailto:Fairchild questions@onsemi.com">Fairchild questions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and safety requirements or standards, regardless of any support or application provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unauthorized sage and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconduct



# FSQ0370RNA, FSQ0370RLA Green Mode Fairchild Power Switch (FPS™)

# Features

- Internal Avalanche Rugged 700V SenseFET
- Consumes Only 0.8W at 230V<sub>AC</sub> & 0.5W Load with Burst-Mode Operation
- Precision Fixed Operating Frequency: 100kHz
- Internal Startup Circuit and Built-in Soft-Start
- Pulse-by-Pulse Current Limiting, Auto-Restart Mode
- Over-Voltage Protection (OVP), Overload Protection (OLP), Internal Thermal Shutdown Function (TSD)
- Under-Voltage Lockout (UVLO)
- Low Operating Current: 3mA
- Adjustable Peak Current Limit

# Applications

- Auxiliary Power Supply for PC and Server
- SIMPS for VCR, SVR STB, DVD, and DVCD Player
- Printe Facsimile, and Scanner
- Adapter for Camcorder

# Description

The FSQ0370 consists of an integrated Current Mode Pulse Width Modul or (P.M.) and an avalanche rugged 700V SenseFET. It is specifically designed for highperformance offline vitched Mode Power Supplies (SMPS) with minimal external components. The integrated PVM controller features include: a fixedrequired P


Compared to a discrete MOSFET and controller or RCC switching converter solution, the FSQ0370 reduces total component count. design size, and weight while increasing efficiency, productivity, and system reliability. These devices provide a basic platform that is well suited for the design of cost-effective flyback converters, such as in PC auxiliary power supplies.

# **Related Application Notes**

- <u>AN-4134</u> Design Guidelines for Off-line Forward <u>Converters Using Fairchild Power Switch (FPS™)</u>
- AN-4137 Design Guidelines for Offline Flyback Converters Using Fairchild Power Switch (FPS™)
- <u>AN-4141</u> Troubleshooting and Design Tips for <u>Fairchild Power Switch (FPS™) Flyback</u> <u>Applications</u>
- AN-4147 Design Guidelines for RCD Snubber of <u>Flyback Converters</u>

#### **Ordering Information**

Part Number	Package	Marking Code	BV <sub>DSS</sub>	f <sub>osc</sub>	R <sub>ds(on)(max)</sub>
FSQ0370RNA	8-Lead, Dual Inline Package (DIP)	Q0370RA	700V	100KHz	4.75Ω
FSQ0370RLA	8-Lead, LSOP	QUSTURA	7000	TUUKHZ	4.7552






# Table 1. Output Power Table<sup>(1)</sup>


Broduct	230V <sub>AC</sub>	±15% <sup>(2)</sup>	85-265VAC	
Product	Adapter <sup>(3)</sup>	Open Frame <sup>(4)</sup>	Adapter <sup>(3)</sup>	Open Frame <sup>(4)</sup>
FSQ0370RNA	20W	27W	13W	19W
FSQ0370RLA	2000	2700	row	1900

#### Notes:

- The maximum output power can be limited by junction temperature. 1.
- $230V_{AC}$  or  $100/115V_{AC}$  with doubler. 2.
- Typical continuous ower in a non-ventilated enclosed adapter with sufficient drain pattern as a heat sink at 3. 50°C ambient
- 4. Maximum practical continuous power in an open-frame design with sufficient drain pattern as a heat sink at 50°C ambient.



**Pin Assignments** 



#### Figure 3. Pin Configuration (Top View)

# **Pin Definitions**

		lpk 4 5 Vstr				
Pin Defin	itions	Figure 3. Pin Configuration (Top View)				
Pin#	Name	Description				
1	GND	SenseFET source terminal on the primary side and internal control group o.				
2	Vcc	Positive supply voltage input Although connected to an auxiliary transformer winding, current is supplied from pin 5 (/str) via an internal switch during startup (see Figure 2). It is not until $V_{CC}$ reaches the U/LO upper threshold (12V) that the internal startup switch opens and device power is supplied via the auxiliary transformer winding.				
3	Vfb	The feedback voltage pin is the non-inverting input to the PWIA comparator. It has a 0.9mA current source connected internally, while a capacitor and optocoupler are typically connected externally. A feedback voltage of 6V triggers overload protection (OLP). There is a delay while charging external capacitor $C_{\rm o}$ from 3V to 6V using an internal 5µA current source. This delay prevents false triggering under transient conditions, but allows the motection mechanism to operate in true overload conditions.				
4	ipk	This pin adjusts the peak current limit of the SenseFET. The 0.9mA feedback current source is diverted to the parallel combination of an internal $2.8k\Omega$ resistor and any external resistor to GND on this pin. This determines the peak current limit. If this pin is tied to Vcc or left floating, the typical peak current limit is 1.1A.				
5	Vstr	This pin is connected to the rectified AC line voltage source. At startup, the internal switch supplies internal bias and charges an external storage capacitor placed between the Vcc pin and ground. Once $V_{CC}$ reaches 12V, the internal switch is opened.				
6, 7, 8	Drain	The drain pins are designed to connect directly to the primary lead of the transformer and are capable of switching a maximum of 700V. Minimizing the length of the trace connecting these pins to the transformer decreases leakage inductance.				

# FSQ0370RNA / FSQ0370RLA — Green Mode Fairchild Power Switch (FPS™)

# **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. T<sub>A</sub>=25°C, unless otherwise specified.

Symbol	Parameter	Min.	Max.	Unit
V <sub>DRAIN</sub>	Drain Pin Voltage	700		V
V <sub>STR</sub>	Vstr Pin Voltage	700		V
I <sub>DM</sub>	Drain Current Pulsed <sup>(5)</sup>		12	А
E <sub>AS</sub>	Single Pulsed Avalanche Energy <sup>(6)</sup>		230	mJ
V <sub>CC</sub>	Supply Voltage		20	V
$V_{FB}$	Feedback Voltage Range	-0.3	V <sub>cc</sub>	V
PD	Total Power Dissipation		1.5	W
TJ	Recommended Operating Junction Temperat	ure -40	Internally Limited	°C
T <sub>A</sub>	Operating Ambient Temperature	-40	+85	°C
T <sub>STG</sub>	Storage Temperature	-55	-150	°C

# **Thermal Impedance**

• 5							
T <sub>A</sub>	Operating Ambient Temperature	-40	+85	°C			
T <sub>STG</sub>	Storage Temperature	-55	+150	°C			
6. L=51mH	etitive rating: pulse-width limited by maximum junction l, starting T <sub>J</sub> =25°C. Impedance	temperature.	FORMATI	on'			
Symbol	Parameter		Value	Unit			
θ <sub>JA</sub>	Junction-to-Ambient Thermal Resistance <sup>(7)</sup> 80						
θ <sub>JC</sub>	Junction-to-Case Thermal Resistance <sup>(8)</sup>	·	20	°C/W			
ΨJT	Junction-to-Top Thermal Resistance <sup>(9)</sup> 35						
- J	Junction-to-Top (mermai Resistance)		35				

Notes:

Free-standing with no heat sirk, without copper clad. 7.

Measured on the drain pin, close to the plastic interface. 8.

Measured on the package top surface. 9.

# **Electrical Characteristics**

 $T_A \mbox{=} 25^\circ C$  unless otherwise specified.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
SenseFET	Section <sup>(10)</sup>					
		V <sub>DS</sub> =700V, V <sub>GS</sub> =0V			50	
I <sub>DSS</sub>	Zero-Gate-Voltage Drain Current	$V_{DS}$ =560V, $V_{GS}$ =0V, $T_{C}$ =125°C			200	μA
R <sub>DS(ON)</sub>	Drain-Source On-State Resistance <sup>(10)</sup>	V <sub>GS</sub> =10V, I <sub>D</sub> =0.5A		4.00	4.75	Ω
CISS	Input Capacitance	V <sub>GS</sub> =0V, V <sub>DS</sub> =25V, f=1MHz		315		pF
C <sub>OSS</sub>	Output Capacitance	V <sub>GS</sub> =0V, V <sub>DS</sub> =25V, f=1MHz		47		pF
C <sub>RSS</sub>	Reverse Transfer Capacitance	V <sub>GS</sub> =0V, V <sub>DS</sub> =25V, f=1MHz		9		рF
t <sub>d(on)</sub>	Turn-On Delay	V <sub>DD</sub> =350V, I <sub>D</sub> =1A		11.2		ns
t <sub>r</sub>	Rise Time	V <sub>DD</sub> =350V, I <sub>D</sub> =1A		34		ns
t <sub>d(off)</sub>	Turn-Off Delay	V <sub>DD</sub> =350V, I <sub>D</sub> =1A		28.2	1	ns
t <sub>f</sub>	Fall Time	V <sub>DD</sub> =350V, I <sub>D</sub> =1A		32		ns
Control Sec	ction					
f <sub>OSC</sub>	Switching Frequency		92	100	103	кНZ
$\Delta f_{OSC}$	Switching Frequency Variation <sup>(11)</sup>	-25°C < T <sub>J</sub> < 85°C		±5	±10	%
D <sub>MAX</sub>	Maximum Duty Cycle	Measure at 0.1 x V <sub>DS</sub>	55	60	650	%
D <sub>MIN</sub>	Minimum Duty Cycle	E ANTI	0	0	0	%
V <sub>START</sub>			10	12	13	
V <sub>STOP</sub>	UVLO Threshold Voltage	V <sub>FB</sub> =GND	7	8	9	V
I <sub>FB</sub>	Feedback Source Current	V <sub>FB</sub> =GND	0.7	0.9	1.1	mA
t <sub>S/S</sub>	Internal Soft-Start Time(11)	V <sub>FD</sub> =4V		10		ms
Burst-Mode	Section	N. K.				
VBURH			0.5	0.6	07	V
VBURL	Burst-Mode Voltage	⊤,=25°C	0.3	0.4	0.5	V
VBUR(HYS)	L' BASA		100	200	300	mV
Protection	Section					
I <sub>LIM</sub>	Peak Current Limit	di/dt=240mA/µs	0.97	1.10	1.23	Α
icld	Current Limit Delay(11)			500		ns
ST <sub>SD</sub>	Thermal Shu'down Temperature <sup>(11)</sup>		125	140		°C
V <sub>SD</sub>	Shutdown Feedback Voltage		5.5	6.0	6.5	V
V <sub>OVP</sub>	Over-Voltage Protection		18	19		V
I <sub>DELAY</sub>	Shutdown Delay Current	V <sub>FB</sub> =4V	3.5	5.0	6.5	μA
$t_{\text{LEB}}$	Leading-Edge Blanking Time <sup>(11)</sup>		200			ns
Total Devic						
I <sub>OP</sub>	Operating Supply Current (Control Part Only)	V <sub>CC</sub> =14V	1	3	5	mA
I <sub>CH</sub>	Startup Charging Current	V <sub>CC</sub> =0V	0.70	0.85	1.00	mA
V <sub>STR</sub>	V <sub>STR</sub> Supply Voltage	V <sub>cc</sub> =0V		24	1	V


Notes:


10. Pulse test: Pulse width  $\leq$  300µs, duty  $\leq$  2%.

11. These parameters, although guaranteed, are not 100% tested in production.

FSQ0370RNA / FSQ0370RLA/— Green Mode Fairchild Power Switch (FPS™)

5





### **Functional Description**

**1. Startup**: In previous generations of Fairchild Power Switches (FPS<sup>TM</sup>), the Vstr pin required an external resistor to the DC input voltage line. In this generation, the startup resistor is replaced by an internal high-voltage current source and a switch that shuts off 10ms after the V<sub>CC</sub> supply voltage goes above 12V. The source turns back on if V<sub>CC</sub> drops below 8V.




Figure 13. Startup Circuit

**2. Feedback Control**: The 700V FPS series employs Current Mode control, as shown in Figure 14. An optocoupler (such as the H11A817A) and shunt regulator (such as the KA431) are typically use to implement the feedback network. Comparing feedback voltage with the voltage across the R<sub>sense</sub> resistor of SenseFET, plus an other voltage, makes it possible to control the solutioning div cycle. When the regulator reference pin voltage exceeds the internal reference voltage of 2.5 the colocoupler LED current increases, feedback voltage V<sub>10</sub> is pulled down, and the duty cycle is reduced. This typically occurs when the input voltage increases of the output load decreases.





Figure 14. Pulse Width Modulation (PWM) Circuit

**3. Leading-Edge Blanking (LEB):** When the internal SenseFET is turned on; the primary-side capacitance and secondary-side rectifier diode reverse recovery typically cause a high current spike through the SenseFET. Excessive voltage across the R<sub>sense</sub> resistor leads to incorrect feedback operation in the Current Mode PWM control. To counter this effect, the FPS employs a Leading-Edge Blanking (LEB) circuit to inhibit the PWM comparator for a short time (t<sub>LEB</sub>) after the SenseFET is turned on.

4. Protection Circuits: The FPS protective functions include Overload Protection (OLP), Over-Voltage Protection (OVP), Under-Voltage Lockout (UVLO), and Thermal Shutdown (TSD). Because these protection circuits are fully integrated inside the IC without external components, reliability is improved without increasing cost. Once a fault condition occurs, switching is terminated and the SenseFET remains off. This causes  $V_{CC}$  to fall. When  $V_{CC}$  reaches the UVLO stop voltage, V<sub>STOP</sub> (typically 8V); the protection is reset and the internal high-voltage current source charges the V<sub>CC</sub> capacitor via the Vstr pin. When Vcc reaches the UVLO start voltage, V<sub>START</sub> (typically 12V); the FPS resumes normal operation. In this manner, the auto-restart can alternately enable and disable the switching of the power SenseFET until the fault condition is eliminated.

4.1 Overload Protection (OLP): Overload is defined as the load current exceeding a pre-set level due to an unexpected event. In this situation, the protection circuit should be activated to protect the SMPS. However, even when the SMPS is operating normally, the Overload Protection (OLP) circuit can be activated during the load transition. To avoid this undesired operation, the OLP circuit is designed to be activated after a specified time to determine whether it is a transient situation or a true overload situation. In conjunction with the lpk current limit pin (if used), the Current Mcde feedback bath would limit the current in the SenseFET when the maximum PWM duty cycle is attained. If the output consumes more than this maximum power, the output voltage  $(V_0)$  decreases below its nominal voltage. This reduces the current through the optocoupler LED, which also reduces the optocoupler transistor current, thus increasing the feeaback voltage (V<sub>FB</sub>). If V<sub>FB</sub> exceeds 3V, the feedback input diode is blocked and the 5µA current source  $(I_{\text{DELAY}})$  starts to slowly charge  $C_{\text{fb}}$  up to  $V_{\text{CC}}.$  In this condition, V<sub>FB</sub> increases until it reaches 6V, when the switching operation is terminated (as shown in Figure 15). The shutdown delay s the time required to charge C<sub>fb</sub> from 3V to 6V with 5µA current source.




© 2011 Fairchild Semiconductor Corporation FSQ0370RNA / FSQ0370RLA • Rev. 2

FSQ0370RNA / FSQ0370RLA — Green Mode Fairchild Power Switch (FPS<sup>™</sup>)


**4.2 Thermal Shutdown (TSD):** The SenseFET and the control IC are integrated, making it easier for the control IC to detect the temperature of the SenseFET. If the temperature exceeds approximately 140°C, thermal shutdown is activated.

4.3 Over-Voltage Protection (OVP): In the event of a malfunction in the secondary-side feedback circuit or an open feedback loop caused by a soldering defect, the current through the optocoupler transistor becomes almost zero (refer to Figure 14). Then, V<sub>FB</sub> climbs up in a similar manner to the overload situation, forcing the preset maximum current to be supplied to the SMPS until the overload protection is activated. Because excess energy is provided to the output, the output voltage may exceed the rated voltage before the overload protection is activated, resulting in the breakdown of the devices in the secondary side. To prevent this situation, an Over-Voltage Protection (OVP) circuit is employed. In general, V<sub>CC</sub> is proportional to the output voltage and the FPS uses  $V_{CC}$  instead of directly monitoring the output voltage. If  $V_{CC}$  exceeds 19V, the OVP circuit is activated, terminating switching. To avoid undesired activation of OVP during normal operation, V<sub>CC</sub> should be designed to be below 19V.


**5. Soft-Start**: The FPS internal soft-start circuit slowly increases the SenseFET current after startup, as shown in Figure 16. The typical soft-start time is 10ms, where progressive increments of the SenseFET current are allowed during the startup phase. The pulse width to be power switching device is progressively increased to establish the correct working conditions for transformers, inductors, and capacitors. The voltage on the output capacitors is progressively increased to smoothly establish the required output voltage. This helps to prevent transformer saturation and reduces the stress on the secondary diode during startup.




**6. Burst Operation:** To minimize power dissipation in Standby Mode, the FPS enters Burst Mode. Feedback voltage decreases as the load decreases and, as shown in Figure 17, the device automatically enters Burst Mode when the feedback voltage drops below  $V_{BURH}$  (typically 600mV). Switching continues until the feedback voltage drops below  $V_{BURL}$  (typically 400mV). At this point, switching stops and the output voltage starts to drop at a rate dependent on the standby current load. This causes the feedback voltage to rise. Once it passes  $V_{BURH}$ , switching resumes. The feedback voltage then falls and the process is repeated. Burst Mode alternately enables and disables switching of the SenseFET and reduces switching loss in Standby Mode.



7. Adjusting Peak Current Limit. As shown in Figure 18 a combined  $2.5k\Omega$  internal resistance is connected to the non-inverting lead on the PWM comparator. An external resistance of  $R_x$  on the current limit pin forms a parallel resistance with the  $2.8k\Omega$  when the internal diodes are biased by the main current source of 900µA.





For example, FSQ0370 has a typical SenseFET peak current limit (I<sub>LIM</sub>) of 1.1A. I<sub>LIM</sub> can be adjusted to 0.6A by inserting R<sub>x</sub> between the Ipk pin and the ground. The value of the R<sub>x</sub> can be estimated by:

$$X = R_x \parallel 2.8 k\Omega.$$
 (2)

where X represents the resistance of the parallel network.

# **Application Information**

### **Reducing Audible Noise**

Switching mode power converters have electronic and magnetic components that generate audible noises when the operating frequency is in the range of 20~20,000Hz. Even though they operate above 20KHz, they can crease noise, depending on the load condition. Three methods of reducing noise are discussed below:

#### **Glue or Varnish**

The most common method of reducing audible noise includes using glue or varnish to tighten magnetic components. The motion of core, bobbin, and coil as well as the chattering or magnetostriction of core can cause the transformer to produce audible noise. The use of rigid glue and varnish reduces the transformer noise. Glue or varnish can also crack the core because sudden changes in the ambient temperature cause the core and the glue to expand or shrink in a different ratio according to the temperature.


#### **Ceramic Capacitor**


Using a film capacitor instead of a ceramic capacitor as a snubber capacitor is another noise reduction solution. Some dielectric materials show a piezoelectric effect, depending on the electric field intensity A snubber capacitor can become one of the most significant sources of audible noise. Another possibility is in use a Zener clamp circuit instead of an RCD snubber for higher efficiency as well as lower audible noise.


#### Adjusting Sound Frequency

Moving the fundamental frequency of noise out of 2~4KHz range is a third method. Generally, humans are more sensitive to noise in the range of 2~4KHz. When the fundamental frequency of noise is located in this range, the noise sounds louder though the noise intensity level is identical. Refer to Figure 19.

If Bus Mode is suspected as a source of noise, this method may be helpful. If the frequency of Burst Mode operation lies in the range of 2-4KHz, adjusting the feedback loop can shift the burst operation frequency. To reduce burst operation frequency, increase a feedback gain capacitor ( $C_F$ ), optocoupler supply resistor ( $R_D$ ), and feedback capacitor ( $C_B$ ) and decrease a feedback gain resistor ( $R_F$ ) as shown in Figure 20.







# **Reference Materials**

AN-4134 — Design Guidelines for Offline Forward Converters Using Fairchild Power Switch (FPS™)

<u>AN-4137 — Design Guidelines for Offline Flyback</u> Converters Using Fairchild Power Switch (FPS™)

<u>AN-4140 — Transformer Design Consideration for</u> <u>Offline Flyback Converters Using Fairchild Power Switch</u> (FPS™)

<u>AN-4141 — Troubleshooting and Design Tips for</u> <u>Fairchild Power Switch (FPS™) Flyback Applications</u>

<u>AN-4147 — Design Guidelines for RCD Snubber of</u> <u>Flyback Converters</u>

<u>AN-4148 — Audible Noise Reduction Techniques for</u> <u>FPS Applications</u>

# **Typical Application Circuit**

Application	Output Power	Input Voltage	Output Voltage (Maximum Current)
PC Auxiliary Power Supply (Using FSQ0270RNA)	15W	Universal Input (85-264V <sub>AC</sub> )	5V (3A)

#### Features


- High efficiency (>78% at 115V<sub>AC</sub> and 230V<sub>AC</sub> input)
- Low Standby Mode power consumption (<0.8W at 230V<sub>AC</sub> input and 0.5W load)
- Enhanced system reliability through various protection functions
- Low EMI through frequency modulation
- Internal soft-start: 10ms
- Line UVLO function can be achieved using external components


# Key Design Notes

- The delay for overload protection is designed to be about 30ms with C8 of 47nF. If faster/slower triggering of OLP is required. C8 can be changed to a smaller or larger value (eg. 100nF or 60ms).
- ZP1, DL1, RL1, RL2, RL3, RL4, RL5, RL7, OL1, QL2, and CL9 build a line Under-Voltage Loci out block (UVLO). The Zener voltage of ZP1 determines the input voltage that turns the FPS on. RL5 and D-1 provide a reference voltage from  $V_{CC}$ . If the input voltage divided by P1 1, RL2, and RL4 is lower than the Zener voltage of DL1; QL1, and QL2 turn on and pull  $V_{fb}$  down to ground
- An evaluation board and corresponding test report can be provided. Contact a Fairchild representative.

SDEVICEIE

SENTATIVE FOR INFO





No. Pi	in (s→f)	Wire		
		VAILE	Turns	Winding Method
N <sub>p</sub> /2	$3 \rightarrow 2$	0.3 <sup>°</sup> x 1	72	Solenoid Winding
Insulation: Polyester	Tape t = 0.025mm, 1	I-Layer	X	1AI
N <sub>a</sub>	<b>4</b> → 5	0.25° x 2	22	Solenoid Winding
Insulation: Polyester	Tape t = 0.0250mm,	2-Layer	50.	
N <sub>5V</sub> 6,	7 → 9, 10	0.65 <sup>¢</sup> x 2	8	Solenoid Winding
Insulation: Polyester	Tape t = 0.025mm, 2	2-Laver		
N <sub>p</sub> /2	2→6	0.3 <sup>¢</sup> x 1	72	Solenoid Winding
Insulation: Polyester	Tape t = 0.025mm, 2	2-Layer		

# Table 3. Electrical Characteristics

SV	Pin	Specification	Remarks
Inductance	1 - 3	1.20mH ± 5%	100kHz, 1V
Leakage	1 - 3	<30µH Maximum	Short All Other Pins

# **Core & Bobbin**


- Core: EER2229 (PL-7, 37.2mm<sup>2</sup>)
- Bobbin: BE2229


13


Part Number	Value	Quantity	Description (Manufacturer)
C6, C8	47nF	2	Ceramic Capacitor
C1	2.2nF (1KV)	1	AC Ceramic Capacitor(X1 & Y1)
C10	1nF (200V)	1	Mylar Capacitor
CS1	1.5nF (50V)	1	SMD Ceramic Capacitor
C2, C3	22µF (400V)	2	Low Impedance Electrolytic Capacitor KMX series (Samyoung Electronics)
C4, C9	1000µF (16V)	2	Low ESR Electrolytic Capacitor NXC series (Samyoung Electronics)
C5	470µF (10V)	1	Low ESR Electrolytic Capacitor NXC series (Samyoung Electronics)
C7	47µF (25V)	1	General Electrolytic Capacitor
CL9	10µF (50V)	1	General Electrolytic Capacitor
L1	330µH	1	Inductor
L2	1µH	1	Inductor
R6	2.4 (1W)	1	Fusible Resistor
J1, J2, J4, L3	0	4	Jumper
R2	4.7kΩ	1	Resistor
R3	560Ω	1	Resistor
R4	100Ω	1	Pesisto.
R5	1.25kΩ	1	Resistor
R11	1.2kΩ	1	Resistor
R9	10kΩ	1	Resistor
R10	20		Resistor
R14	30Ω	1	Resistor
RL3	1kΩ	1	Resistor
RL1, RL2	1ΜΩ	2	Resistor
RL4	120k?	,1 Û	Resistor
RL5	30kΩ	C I	Resistor
RL7	40kΩ	1	Resistor
RS1	90	CV	Resistor
ZR1	80Ω	1	SMD Resistor
Ul	FOD817A	1	IC (Fairchild Semiconductor)
<b>O</b> U2	TL431	1	IC (Fairchild Semiconductor)
U3	FSQ0270RNA	1	IC (Fairchild Semiconductor)
QL1	2N2907	1	IC (Fairchild Semiconductor)
QL2	2N2222	1	IC (Fairchild Semiconductor)
D2, D3, D4, D5, D6, DS1	1N4007	6	Diode (Fairchild Semiconductor)
D1	SB540	1	Schottky Diode (Fairchild Semiconductor)
ZD1	1N4745	1	Zener Diode (Fairchild Semiconductor)
DL1	1N5233	1	Zener Diode (Fairchild Semiconductor)
ZP1	82V (1W)	1	Zener Diode (Fairchild Semiconductor)
ZDS1	P6KE180A	1	TVS (Fairchild Semiconductor)

#### Table 4. Demonstration Board Part List

FSQ0370RNA / FSQ0370RLA → Green Mode Fairchild Power Switch (FPS™)







ON Semiconductor and ware trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="https://www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

OT RECONNERVOUR OR MENDE SENTATIVE FOR INFORMATION SENTATIVE FOR INFORMATION

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

NEW DESIGN