ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,



LCD and Camera EMI Filter Array with ESD Protection


CM1620


Features

- Six or eight channels of EMI filtering with integrated ESD protection
- Pi-style EMI filters in a capacitor-resistorcapacitor (C-R-C) network
- ±15kV ESD protection on each channel (IEC 61000-4-2 Level 4, contact discharge)
- ±30kV ESD protection on each channel (HBM)
- Greater than -25dB attenuation (typical) at 1GHz
- NuDFN package with 0.40mm lead pitch:
 - 12-lead: 2.5mm x 1.20mm x 0.50mm
 - 16-lead: 3.5mm x 1.20mm x 0.50mm
- Lead-free finishing

Applications

- Applications
- LCD and camera data lines in mobile handsets
- I/O port protection for mobile handsets, notebook computers, PDAs, etc.
- EMI filtering for data ports in cell phones, PDAs or notebook computers
- Wireless handsets
- Handheld PCs/PDAs





16-PIN DESCRIPTIONS										
DEVICE PIN(s)					DEVICE PIN(s)					
-06	-08	NAME	DESCRIPTION		-06 -08		NAME	DESCRIPTION		
1	1	FILTER1	Filter + ESD Channel 1		12	16	FILTER1	Filter + ESD Channel 1		
2	2	FILTER2	Filter + ESD Channel 2		11	15	FILTER2	Filter + ESD Channel 2		
3	3	FILTER3	Filter + ESD Channel 3		10	14	FILTER3	Filter + ESD Channel 3		
4	4	FILTER4	Filter + ESD Channel 4		9	13	FILTER4	Filter + ESD Channel 4		
5	5	FILTER5	Filter + ESD Channel 5		8	12	FILTER5	Filter + ESD Channel 5		
6	6	FILTER6	Filter + ESD Channel 6		7	11	FILTER6	Filter + ESD Channel 6		
_	7	FILTER7	Filter + ESD Channel 7		-	10	FILTER7	Filter + ESD Channel 7		
-	8	FILTER8	Filter + ESD Channel 8		-	9	FILTER8	Filter + ESD Channel 8		
_	GND PAD	GND	Device Ground		,					

Ordering Information

PART NUMBERING INFORMATION								
		Lead-free Finish						
Pins	Package	Ordering Part Number ¹	Part Marking					
12	NuDFN-12	CM1620 -06DE	P20					
16	NuDFN-16	CM1620 -08DE	P208					

b

Note 1: Parts are shipped in Tape & Reel form unless otherwise specified.

Specifications

ABSOLUTE MAXIMUM RATINGS							
PARAMETER	RATING	UNITS					
Storage Temperature Range	-65 to +150	°C					
DC Power per Resistor	100	mW					
DC Package Power Rating	500	mW					

STANDARD OPERATING CONDITIONS								
PARAMETER	RATING	UNITS						
Operating Temperature Range	-40 to +85	°C						

	ELECTRICAL OPERATING CHARACTERISTICS (NOTE1)									
SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS				
R	Resistance		80	100	120	Ω				
C _{TOTAL}	Total Channel Capacitance	At 2.5VDC Reverse Bias, 1MHz, 30mVAC	14	17	22	pF				
С	Capacitance C	At 2.5VDC Reverse Bias, 1MHz, 30mVAC		8.5		pF				
$V_{\text{\tiny DIODE}}$	Standoff Voltage	$I_{\text{DIODE}} = 10 \mu A$		6.0		V				
I _{LEAK}	Diode Leakage Current (reverse bias)	V _{DIODE} = +3.3V		0.1	1.0	μА				
V _{SIG}	Signal Clamp Voltage	I _{LOAD} = 10mA	5.6	6.8	9.0	V				
V _{ESD}	In-system ESD Withstand Voltage a) Human Body Model, MIL-STD-883, Method 3015 b) Contact Discharge per IEC 61000-4- 2 Level 4	See Note 2	±30 ±15			kV kV				
R _{DYN}	Dynamic Resistance Positive Negative			2.3 0.9		Ω				
f _c	Cut-off Frequency $Z_{\text{SOURCE}} = 50\Omega$, $Z_{\text{LOAD}} = 50\Omega$	Channel R = 100Ω , Channel C = $17pF$		200		MHz				
A _{1GHz}	Absolute Attenuation @ 1GHz from 0dB Level	$\begin{split} &Z_{\text{SOURCE}} = 50\Omega, Z_{\text{LOAD}} = 50\Omega, \\ &\text{DC Bias} = \text{0V; See Notes 1 and 3} \end{split}$		-30		dB				
A _{800MHz - 6GHz}	Absolute Attenuation @ 800MHz to 6GHz from 0dB Level	$\begin{split} &Z_{\text{SOURCE}} = 50\Omega, Z_{\text{LOAD}} = 50\Omega, \\ &\text{DC Bias} = \text{0V; See Notes 1 and 3} \end{split}$		-25		dB				

Note 1: T_A =25°C unless otherwise specified. Note 2: ESD applied to input and output pins with respect to GND, one at a time.

Note 3: Attenuation / RF curves characterized by a network analyzer using microprobes.

Performance Information

Typical Filter Performance (T_A=25°C, DC Bias=0V, 50 Ohm Environment)




Figure 1. Insertion Loss vs. Frequency (FILTER1 Input to GND, CM1620-06DE)




Figure 2. Insertion Loss vs. Frequency (FILTER2 Input to GND, CM1620-06DE)




Figure 3. Insertion Loss vs. Frequency (FILTER3 Input to GND, CM1620-06DE)




Figure 4. Insertion Loss vs. Frequency (FILTER4 Input to GND, CM1620-06DE)




Figure 5. Insertion Loss vs. Frequency (FILTER5 Input to GND, CM1620-06DE)




Figure 6. Insertion Loss vs. Frequency (FILTER6 Input to GND, CM1620-06DE)




Figure 7. Insertion Loss vs. Frequency (FILTER1 Input to GND, CM1620-08DE)




Figure 8. Insertion Loss vs. Frequency (FILTER2 Input to GND, CM1620-08DE)




Figure 9. Insertion Loss vs. Frequency (FILTER3 Input to GND, CM1620-08DE)




Figure 10. Insertion Loss vs. Frequency (FILTER4 Input to GND, CM1620-08DE)




Figure 11. Insertion Loss vs. Frequency (FILTER5 Input to GND, CM1620-08DE)




Figure 12. Insertion Loss vs. Frequency (FILTER6 Input to GND, CM1620-08DE)




Figure 13. Insertion Loss vs. Frequency (FILTER7 Input to GND, CM1620-08DE)




Figure 14. Insertion Loss vs. Frequency (FILTER8 Input to GND, CM1620-08DE)

Typical Diode Capacitance vs. Input Voltage




Figure 15. Filter Capacitance vs. Input Voltage (Normalized to Capacitance at 2.5VDC and 25°C)


Mechanical Details

NuDFN-12 Mechanical Specifications

Dimensions for the 12-lead, 0.4mm pitch NuDFN package are presented below.

	PAC	KAGE	DIME	NSIO	NS			
Package	NuDFN							
JEDEC No.	MO-229C*							
Leads			-	12				
Dim.	Millimeters			Inches				
Diiii.	Min	Nom	Max	Min	Nom	Max		
Α	0.45	0.50	0.55	0.018	0.020	0.022		
A 1	0.00	0.02	0.05	0.000	0.001	0.002		
А3	0.127 REF			C).005 REF			
b	0.15	0.20	0.25	0.006	0.008	0.010		
D	2.40	2.50	2.60	0.094	0.098	0.102		
D2	1.70	1.80	1.90	0.067	0.071	0.075		
E	1.10	1.20	1.30	0.043	0.047	0.051		
E2	0.20	0.30	0.40	0.008	0.012	0.016		
е	0.40 BSC 0.016 BSC					С		
К	0.20			0.008				
L	0.20	0.25	0.30	0.008	0.010	0.012		
# per tape and reel	tape and							
	Contro	Controlling dimension: millimeters						

^{*}This package is compliant with JEDEC standard MO-229C with the exception of the D, D2, E, E2, K and L dimensions as called out in the table above.



Dimensions for 12-Lead, 0.4mm pitch NuDFN package


Mechanical Details

NuDFN-16 Mechanical Specifications, 0.4mm

Dimensions for the 16-lead, 0.4mm pitch NuDFN package are presented below.

PACKAGE DIMENSIONS									
Package	ckage NuDFN								
JEDEC No.	MO-229C*								
Leads			1	16					
Dim.	Millimeters			Inches					
Dilli.	Min	Nom	Max	Min	Nom	Max			
Α	0.45	0.50	0.55	0.018	0.020	0.022			
A 1	0.00	0.02	0.05	0.000	0.001	0.002			
А3	0	0.127 REF 0.005			0.005 RE	REF			
b	0.15	0.20	0.25	0.006	0.008	0.010			
b1		.20 BSC	SC 0.008 BSC			С			
D	3.40	3.40 3.50 3.60 0.134 0.13		0.138	0.142				
D2	2.70	2.80	2.90	0.106	0.110	0.114			
E	1.10	1.20	1.30	0.043	0.047	0.051			
E2	0.20	0.30	0.40	0.008	0.012	0.016			
е	0.400 BSC 0.016 BSC					С			
L	0.20 0.25 0.30		0.008	0.010	0.012				
L2	0.15 REF 0.006 REF					F			
# per tape and reel	3000 pieces								
Controlling dimension: millimeters									

^{*}This package is compliant with JEDEC standard MO-229C with the exception of the D, D2, E, E2, and L dimensions as called out in the table above.



Dimensions for 16-Lead, 0.4mm pitch NuDFN package

CM1620

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5773-3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative