

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese

FAIRCHILD

SEMICONDUCTOR

FSAM75SM60A Motion SPM[®] 2 Series

Features

- UL Certified No. E209204 (UL1557)
- 600 V 75 A 3-Phase IGBT Inverter with Integral Gate Drivers and Protection
- Low-Loss, Short-Circuit Rated IGBTs
- Very Low Thermal Resistance Using AIN DBC Substrate
- Separate Open-Emitter Pins from Low Side IGBTs for Three-Phase Current Sensing
- Single-Grounded Power Supply
- Optimized for 5 kHz Switching Frequency
- Built-in NTC Thermistor for Temperature Monitoring
- Inverter Power Rating of 6.0 kW / 100~253 VAC
- Adjustable Current Protection Level via Selection of Sense-IGBT Emitter's External Rs
- Isolation Rating: 2500 V_{rms} / min.

Applications

Motion Control - Home Appliance / Industrial Motor

Resource

• AN-9043 - Motion SPM® 2 Series User's Guide

January 2014

General Description

FSAM75SM60A is a Motion SPM® 2 module providing a fully-featured, high-performance inverter stage for AC Induction, BLDC, and PMSM motors. These modules integrate optimized gate drive of the built-in IGBTs to minimize EMI and losses, while also providing multiple on-module protection features including under-voltage lockouts, overcurrent shutdown, thermal monitoring, and fault reporting. The built-in, high-speed HVIC requires only a single supply voltage and translates the incoming logic-level gate inputs to the high-voltage, high-current drive signals required to properly drive the module's internal IGBTs. Separate negative IGBT terminals are available for each phase to support the widest variety of control algorithms.




Figure 1. Package Overview

Package Marking and Ordering Information

Device	Device Marking	Package	Packing Type	Quantity
FSAM75SM60A	FSAM75SM60A	S32DA-032	Rail	8


©2006 Fairchild Semiconductor Corporation FSAM75SM60A Rev. C4

www.fairchildsemi.com



©2006 Fairchild Semiconductor Corporation FSAM75SM60A Rev. C4 www.fairchildsemi.com

Pin Number	Pin Name	Pin Description
1	V _{CC(L)}	Low-Side Common Bias Voltage for IC and IGBTs Driving
2	COM _(L)	Low-Side Common Supply Ground
3	IN _(UL)	Signal Input Terminal for Low-Side U-Phase
4	IN _(VL)	Signal Input Terminal for Low-Side V-Phase
5	IN _(WL)	Signal Input Terminal for Low-Side W-Phase
6	COM _(L)	Low-Side Common Supply Ground
7	V _{FO}	Fault Output
8	C _{FOD}	Capacitor for Fault Output Duration Selection
9	C _{SC}	Capacitor (Low-Pass Filter) for Short-Circuit Current Detection Input
10	R _{SC}	Resistor for Short-Circuit Current Detection
11	IN _(UH)	Signal Input for High-Side U-Phase
12	V _{CC(UH)}	High-Side Bias Voltage for U-Phase IC
13	V _{B(U)}	High-Side Bias Voltage for U-Phase IGBT Driving
14	V _{S(U)}	High-SideBias Voltage Ground for U-Phase IGBT Driving
15	IN _(VH)	Signal Input for High-Side V-Phase
16	COM(H)	High-Side Common Supply Ground
17	V _{CC(VH)}	High-Side Bias Voltage for V-Phase IC
18	V _{B(V)}	High-Side Bias Voltage for V-Phase IGBT Driving
19	V _{S(V)}	High-Side Bias Voltage Ground for V-Phase IGBT Driving
20	IN _(WH)	Signal Input for High-side W-Phase
21	V _{CC(WH)}	High-Side Bias Voltage for W-Phase IC
22	V _{B(W)}	High-Side Bias Voltage for W-Phase IGBT Driving
23	V _{S(W)}	High-Side Bias Voltage Ground for W-Phase IGBT Driving
24	V _{TH}	Thermistor Bias Voltage
25	R _{TH}	Series Resistor for the Use of Thermistor (Temperature Detection)
26	NU	Negative DC-Link Input Terminal for U-Phase
27	N _V	Negative DC-Link Input Terminal for V-Phase
28	N _W	Negative DC-Link Input Terminal for W-Phase
29	U	Output for U-Phase
30	V	Output for V-Phase
31	W	Output for W-Phase
32	Р	Positive DC-Link Input



www.fairchildsemi.com

FSAM75SM60A Motion SPM® 2 Series

©2006 Fairchild Semiconductor Corporation FSAM75SM60A Rev. C4

Absolute Maximum Ratings ($T_J = 25^{\circ}C$, unless otherwise specified.) **Inverter Part**

Item	Symbol	Condition	Rating	Unit
Supply Voltage	V _{DC}	Applied to DC-Link	450	V
Supply Voltage (Surge)	V _{PN(Surge)}	Applied between P and N	500	V
Collector - Emitter Voltage	V _{CES}		600	V
Each IGBT Collector Current	± I _C	$T_{\rm C} = 25^{\circ}{\rm C}$	75	Α
Each IGBT Collector Current	± I _C	T _C = 100°C	37	Α
Each IGBT Collector Current (Peak)	± I _{CP}	T _C = 25°C , Under 1ms Pulse Width	110	Α
Collector Dissipation	P _C	T _C = 25°C per Chip	189	W
Operating Junction Temperature	TJ	(2nd Note 1)	-20 ~ 125	°C

2nd Notes: 1. It would be recommended that the average junction temperature should be limited to $T_J \le 125^{\circ}C$ (at $T_C \le 100^{\circ}C$) in order to guarantee safe operation.

Control Part

ltem	Symbol	Condition	Rating	Unit
Control Supply Voltage	V _{CC}	Applied between $V_{CC(UH)}$, $V_{CC(VH)}$, $V_{CC(WH)}$ - $COM_{(H)}$, $V_{CC(L)}$ - $COM_{(L)}$	20	V
High-Side Control Bias Voltage	V_{BS}	Applied between V _{B(U)} - V _{S(U)} , V _{B(V)} - V _{S(V)} , V _{B(W)} - V _{S(W)}	20	V
Input Signal Voltage	V _{IN}	$ \begin{array}{l} \mbox{Applied between IN}_{(UH)}, \mbox{IN}_{(VH)}, \mbox{IN}_{(WH)} \mbox{-} \mbox{COM}_{(H)} \\ \mbox{IN}_{(UL)}, \mbox{IN}_{(VL)}, \mbox{IN}_{(WL)} \mbox{-} \mbox{COM}_{(L)} \end{array} $	-0.3 ~ V _{CC} +0.3	V
Fault Output Supply Voltage	V _{FO}	Applied between V _{FO} - COM _(L)	-0.3 ~ V _{CC} +0.3	V
Fault Output Current	I _{FO}	Sink Current at V _{FO} Pin	5	mA
Current-Sensing Input Voltage	V _{SC}	Applied between C _{SC} - COM _(L)	-0.3 ~ V _{CC} +0.3	V

Total System

Item	Symbol	Condition	Rating	Unit
Self-Protection Supply Voltage Limit (Short-Circuit Protection Capability)	V _{PN(PROT)}	Applied to DC-Link, V _{CC} = V _{BS} = 13.5 ~ 16.5 V T _J = 125°C, Non-Repetitive, < 5 μs	400	V
Module Case Operation Temperature	T _C	See Figure 2	-20 ~ 100	°C
Storage Temperature	T _{STG}		-20 ~ 125	°C
Isolation Voltage	V _{ISO}	60Hz, Sinusoidal, AC 1 Minute, Connect Pins to Heat Sink Plate	2500	V _{rms}

Thermal Resistance

Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Junction to Case Thermal	R _{th(j-c)Q}	Inverter IGBT Part (per 1/6 module)	-	-	0.56	°C/W
Resistance	R _{th(j-c)F}	Inverter FWDi Part (per 1/6 module)	-	-	0.98	°C/W
Contact Thermal	R _{th(c-f)}	DBC Substrate (per 1 Module)	-	-	0.06	°C/W
Resistance	~ /	Thermal Grease Applied (2nd Note 3)				

2nd Notes:


2. For the measurement point of case temperature(T_c), please refer to Figure 2. 3. The thickness of thermal grease should not be more than 100 μ m.


Electrical Characteristics

Inverter Part (T_J = 25°C, unless otherwise specified.)

Item	Symbol	Conditio	on	Min.	Тур.	Max.	Unit
Collector - emitter Saturation Voltage	V _{CE(SAT)}	$V_{CC} = V_{BS} = 15 V$ $V_{IN} = 0 V$	$I_{C} = 50 \text{ A}, \text{ T}_{J} = 25^{\circ}\text{C}$	-	-	2.4	V
FWDi Forward Voltage	V _{FM}	V _{IN} = 5 V	$I_{\rm C} = 50 \text{ A}, \text{ T}_{\rm J} = 25^{\circ} \text{C}$	-	-	2.1	V
Switching Times	t _{ON}	$V_{PN} = 300 \text{ V}, V_{CC} = V_{BS} = 18$	5 V	-	0.76	-	μS
	t _{C(ON)}	$I_{C} = 75 \text{ A}, T_{J} = 25^{\circ}\text{C}$		-	0.44	-	μS
	t _{OFF}	$V_{IN} = 5 V \leftrightarrow 0 V$, Inductive L (High- And Low-Side)	oad	-	1.42	-	μS
	t _{C(OFF)}	(High-And Low-Side)		-	0.46	-	μS
	t _{rr}	(2nd Note 4)		-	0.10	-	μS
Collector-Emitter Leakage Current	I _{CES}	$V_{CE} = V_{CES}, T_J = 25^{\circ}C$		-	-	250	μΑ

2nd Notes:
 4. t_{ON} and t_{OFF} include the propagation delay time of the internal drive IC. t_{C(ON)} and t_{C(OFF)} are the switching time of IGBT itself under the given gate driving condition internally. For the detailed information, please see Figure 4.







©2006 Fairchild Semiconductor Corporation FSAM75SM60A Rev. C4

Item	Symbol		Condition	Min.	Тур.	Max.	Unit
Quiescent V _{CC} Supply Current	I _{QCCL}	V _{CC} = 15 V IN _(UL, VL, WL) = 5V	V _{CC(L)} - COM _(L)	-	-	26	mA
	I _{QCCH}	V _{CC} = 15 V IN _(UH, VH, WH) = 5V	V _{CC(UH)} , V _{CC(VH)} , V _{CC(WH)} - COM _(H)	-	-	130	μA
Quiescent $\rm V_{BS}$ Supply Current	I _{QBS}	V _{BS} = 15 V IN _(UH, VH, WH) = 5V	$V_{B(U)} - V_{S(U)}, V_{B(V)} - V_{S(V)}, V_{B(W)} - V_{S(W)}$	-	-	420	μA
Fault Output Voltage	V _{FOH}	V _{SC} = 0 V, V _{FO} Circuit	:: 4.7 k Ω to 5 V Pull-up	4.5	-	-	V
	V _{FOL}	V _{SC} = 1 V, V _{FO} Circuit	:: 4.7 k Ω to 5 V Pull-up	-	-	1.1	V
Short-Circuit Trip Level	V _{SC(ref)}	V _{CC} = 15 V (2nd Note	5)	0.45	0.51	0.56	V
Sensing Voltage of IGBT Current	V _{SEN}	$R_{SC} = 26 \Omega, R_{SU} = R$ (See a Figure 6)	$_{\rm SV}$ = R $_{\rm SW}$ = 0 Ω and I $_{\rm C}$ = 100 A	0.45	0.51	0.56	V
Supply Circuit Under-	UV _{CCD}	Detection Level		11.5	12.0	12.5	V
Voltage Protection	UV _{CCR}	Reset Level		12.0	12.5	13.0	V
	UV _{BSD}	Detection Level		7.3	9.0	10.8	V
	UV _{BSR}	Reset Level		8.6	10.3	12.0	V
Fault Output Pulse Width	t _{FOD}	C _{FOD} = 33 nF (2nd No	ote 6)	1.4	1.8	2.0	ms
ON Threshold Voltage	V _{IN(ON)}	High-Side	Applied between IN(UH),	-	-	0.8	V
OFF Threshold Voltage	V _{IN(OFF)}		IN _(VH) , IN _(WH) - COM _(H)	3.0	-	-	V
ON Threshold Voltage	V _{IN(ON)}	Low-Side	Applied between IN _(UL) ,	-	-	0.8	V
OFF Threshold Voltage	V _{IN(OFF)}		IN _(VL) , IN _(WL) - COM _(L)	3.0	-	-	V
Resistance of Thermistor	R _{TH}	@ T _{TH} = 25°C (2nd N	ote 7, Figure 5)	-	50	-	kΩ
		@ T _{TH} = 100°C (2nd I	Note 7, Figure 5)	-	3.0	-	kΩ

Electrical Characteristics ($T_J = 25^{\circ}C$, unless otherwise specified.)

2nd Notes:
5. Short-circuit protection is functioning only at the low-sides. It would be recommended that the value of the external sensing resistor (R_{SC}) should be selected around 26 Ω in order to make the SC trip-level of about 100A at the shurt resistors (R_{SU}, R_{SV}, R_{SW}) of 0Ω. For the detailed information about the relationship between the external sensing resistor (R_{SC}) and the shurt resistors (R_{SU}), R_{SV}, R_{SW}), please see Figure 6.
6. The fault-out pulse width t_{FOD} depends on the capacitance value of C_{FOD} according to the following approximate equation: C_{FOD} = 18.3 x 10⁻⁶ x t_{FOD} [F]
7. T_{TH} is the temperature of thermistor itself. To know case temperature (T_C), please make the experiment considering your application.




Figure 5. R-T Curve of The Built-in Thermistor

©2006 Fairchild Semiconductor Corporation FSAM75SM60A Rev. C4

www.fairchildsemi.com

FSAM75SM60A Motion SPM® 2 Series




Figure 6. R_{SC} Variation by Change of Shunt Resistors (R_{SU}, R_{SV}, R_{SW}) for Short-Circuit Protection (1) @ Current Trip Level ≒ 75 A (2) @ Current Trip Level ≒ 100 A

Recommended Operating Conditions


Item	Symbol	Condition	Min.	Тур.	Max.	Unit
Supply Voltage	V _{PN}	Applied between P - N _U , N _V , N _W	-	300	400	V
Control Supply Voltage	V _{CC}	Applied between $V_{CC(UH)}$, $V_{CC(VH)}$, $V_{CC(WH)}$ - COM _(H) , $V_{CC(L)}$ - COM _(L)	13.5	15.0	16.5	V
High-side Bias Voltage	V _{BS}	Applied between $V_{B(U)}$ - $V_{S(U)}$, $V_{B(V)}$ - $V_{S(V)}$, $V_{B(W)}$ - $V_{S(W)}$	13.0	15.0	18.5	V
Blanking Time for Preventing Arm-short	t _{dead}	For Each Input Signal	3.5	-	-	μS
PWM Input Signal	f _{PWM}	$T_C \le 100^{\circ}C, T_J \le 125^{\circ}C$	-	5	-	kHz
Minimum Input Pulse Width	PW _{IN(OFF)}	$\begin{array}{l} 200 \leq V_{PN} \leq 400 \text{V}, 13.5 \leq V_{CC} \leq 16.5 \text{V}, \\ 13.0 \leq V_{BS} \leq 18.5 \text{V}, 0 \leq I_C \leq 110 \text{A}, \\ -20 \leq T_J \leq 125 ^\circ \text{C} \\ \text{V}_{IN} = 5 \text{V} \leftrightarrow 0 \text{V}, \text{Inductive Load} (\text{2nd Note 8}) \end{array}$	3	-	-	μs
Input ON Threshold Voltage	V _{IN(ON)}	Applied between IN _(UH) , IN _(VH) , IN _(WH) - COM _(H) , IN _(UL) , IN _(VL) , IN _(WL) - COM _(L)		0 ~ 0.65	5	V
Input OFF Threshold Voltage	V _{IN(OFF)}	$\begin{array}{l} \mbox{Applied between IN}_{(UH)}, \mbox{IN}_{(VH)}, \mbox{IN}_{(WH)} - \\ \mbox{COM}_{(H)}, \mbox{IN}_{(UL)}, \mbox{IN}_{(VL)}, \mbox{IN}_{(WL)} - \mbox{COM}_{(L)} \end{array}$		4 ~ 5.5		V

2nd Notes:


Motion SPM[®] 2 product might not make response if the PW_{IN(OFF)} is less than the recommended minimum value.

FSAM75SM60A Motion SPM® 2 Series

Item		Condition	Min.	Тур.	Max.	Units
Nounting Torque	Mounting Screw: M4	Recommended 10 kg•cm	8	10	12	kg•cm
0	(2nd Note 9 and 10)	Recommended 0.98 N•m	0.78	0.98	1.17	N•m
BC Flatness		See Figure 7	0	-	+120	μm
Veight			-	32	-	g
d Notes:		easurement Position of The				
.Avoid one side tightening DBC substrate to be dam	aged.	anting Screws Torque Order	2	can cause th	e Motion SP	M [∞] 2 package



FSAM75SM60A Motion SPM® 2 Series



©2006 Fairchild Semiconductor Corporation FSAM75SM60A Rev. C4




Figure 13. Recommended Bootstrap Operation Circuit and Parameters

3rd Notes:

- 4. It would be recommended that the bootstrap diode, $\mathsf{D}_{\mathsf{BS}},$ has soft and fast recovery characteristics.
- 5. The bootstrap resistor(R_{BS}) should be three times greater than R_{E(H)}. The recommended value of R_{E(H)} is 5.6Ω, but it can be increased up to 20 Ω for a slower dv/ dt of high-side.

6. The ceramic capacitor placed between V_{CC} - COM should be over 1 μ F and mounted as close to the pins of the Motion SPM[®] 2 product as possible.






Figure 14. Application Circuit


4th Notes:

- 1. RpLCPL/RPHCPH /RPFCPF coupling at each Motion SPM[®] 2 product input is recommended in order to prevent input signals' oscillation and it should be as close as possible to each Motion SPM 2 product input pin.
- 2. By virtue of integrating an application specific type HVIC inside the Motion SPM 2 product, direct coupling to MCU terminals without any optocoupler or transformer isolation is possible.
- 3. V_{FO} output is open-collector type. This signal line should be pulled up to the positive side of the 5 V power supply with approximately 4.7 kΩ resistance. Please refer to Figure 12.
- 4. Sprig of around seven times larger than bootstrap capacitor C_{BS} is recommended. 5. V_{FO} output pulse width should be determined by connecting an external capacitor(C_{FOD}) between C_{FOD} (pin 8) and $COM_{(L)}$ (pin 2). (Example : if C_{FOD} = 33 nF, then
- 5. V_{FO} output pulse width should be determined by connecting an external capacitor(C_{FOD}) between C_{FOD}(pin e) and COM(L)(pin 2). (Example : II C_{FOD} = 35 nr, then t_{FO} = 1.8 ms (typ.)) Please refer to the 2nd note 6 for calculation method.
 6. Each input signal line should be pulled up to the 5 V power supply with approximately 4.7 kΩ (at high side input) or 2 kΩ (at low side input) resistance (other RC coupling circuits at each input may be needed depending on the PWM control scheme used and on the wiring impedance of the system's printed circuit board). Approximately a 0.22 ~ 2 nF by-pass capacitor should be used across each power supply connection terminals.

- Approximately a 0.22 ~ 2 in by pass capacitor should be used across each power supply connection terminals. 7. To prevent errors of the protection function, the wiring around R_{SC} , R_F and C_{SC} should be as short as possible. 8. In the short-circuit protection circuit, please select the $R_F C_{SC}$ time constant in the range 3 ~ 4 µs. 9. Each capacitor should be mounted as close to the pins of the Motion SPM 2 product as possible. 10. To prevent surge destruction, the wiring between the smoothing capacitor and the P & N pins should be as short as possible. The use of a high frequency non-independent sectors are also be as the product of the product of the PCM is product as possible. inductive capacitor of around 0.1 – 0.22 µF between the P&N pins is recommended. 11. Relays are used at almost every systems of electrical equipments of home appliances. In these cases, there is hould be sufficient distance between the MCU and
- the relays. It is recommended that the distance be 5 cm at least.










NOTES: UNLESS OTHERWISE SPECIFIED A) THIS PACKAGE DOES NOT COMPLY TO ANY CURRENT PACKAGING STANDARD B) ALL DIMENSIONS ARE IN MILLIMETERS C) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS D) () IS REFERENCE E) DRAWING FILENAME: MOD32BAREV3









LAND PATTERN RECOMMENDATIONS

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC