

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese



April 2015

FPF1039 Low On-Resistance, Slew-Rate-Controlled Load Switch

Features

- 1.2 V to 5.5 V Input Voltage Operating Range
- Typical R_{ON}:
 - $~20~m\Omega$ at V_{IN}=5.5 V $\,$
 - 21 m Ω at V_{IN}=4.5 V
 - 37 m Ω at V_{IN}=1.8 V
 - 75 mΩ at V_{IN}=1.2 V
- Slew Rate / Inrush Control with t_R: 2.7 ms (Typical)
- 3.5 A Maximum Continuous Current Capability
- Output Capacitor Discharge Function
- Low <1 µA Shutdown Current</p>
- ESD Protected: Above 8 kV HBM, 1.5 kV CDM
- GPIO / CMOS-Compatible Enable Circuitry

Applications

- HDD, Storage, and Solid-State Memory Devices
- Portable Media Devices, UMPC, Tablets, MIDs
- Wireless LAN Cards and Modules
- SLR Digital Cameras
- Portable Medical Devices
- GPS and Navigation Equipment
- Industrial Handheld and Enterprise Equipment

Description


The FPF1039 advanced load-management switch target applications requiring a highly integrated solution for disconnecting loads powered from DC power rail (<6 V) with stringent shutdown current targets and high load capacitances (up to 200 μ F). The FPF1039 consists of slew-rate controlled low-impedance MOSFET switch (21 m Ω typical) and other integrated analog features. The slew-rate controlled turn-on characteristic prevents inrush current and the resulting excessive voltage droop on power rails.


This device has exceptionally low shutdown current drain (<1 μ A maximum) that facilitates compliance in low standby power applications. The input voltage range operates from 1.2 V to 5.5 V DC to support a wide range of applications in consumer, optical, medical, storage, portable, and industrial device power management.

Switch control is managed by a logic input (active HIGH) capable of interfacing directly with low-voltage control signal / GPIO with no external pull-up required. The device is packaged in advanced fully "green" 1mm x1.5 mm Wafer-Level Chip-Scale Packaging (WLCSP); providing excellent thermal conductivity, small footprint, and low electrical resistance for wider application usage.

Part Number	Top Mark	Switch R _{oN} (Typical) at 4.5 V _{IN}	Input Buffer	Output Discharge	ON Pin Activity	t _R	Package
FPF1039UCX	QF	21 mΩ	CMOS	65Ω	Active HIGH	2.7 ms	6-Bump, WLCSP, 1.0 mm x 1.5 mm, 0.5 mm Pitch
FPF1039BUCX	QF	21 mΩ	CMOS	65Ω	Active HIGH	2.7 ms	6-Bump, WLCSP with Backside Laminate, 1.0 mm x 1.5 mm, 0.5 mm Pitch

Ordering Information





Pin Definitions

Pin #	Name	Description
A1, B1	Vout	Switch Output
A2, B2	V _{IN}	Supply Input: Input to the Power Switch
C1	GND	Ground
C2	ON	ON/OFF Control, Active High - GPIO Compatible

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Par	Min.	Max.	Unit		
V _{IN}	V_{IN} , V_{OUT} , V_{ON} to GND		-0.3	6.0	V	
I _{SW}	Maximum Continuous Switch Curren	t		3.5	А	
PD	Power Dissipation at $T_A=25^{\circ}C$			1.2	W	
T _{STG}	Storage Junction Temperature		-65	+150	°C	
T _A	Operating Temperature Range		-40	+85	°C	
	Thermal Desistance, Junction to Am	hight		85 ⁽¹⁾	°C/W	
Θ_{JA}	Thermal Resistance, Junction-to-Ambient			110 ⁽²⁾	0/00	
ESD	Electrostatic Discharge Conshility	Human Body Model, JESD22-A114	8.0		kV	
ESD	Electrostatic Discharge Capability	Charged Device Model, JESD22-C101	1.5			

Notes:

1. Measured using 2S2P JEDEC std. PCB.

2. Measured using 2S2P JEDEC PCB COLD PLATE method.

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameters	Min.	Max.	Unit
V _{IN}	Input Voltage	1.2	5.5	V
TA	Ambient Operating Temperature	-40	+85	°C

FPF1039 — IntelliMAXTM Advanced Slew Rate Controlled Load Switch

Electrical Characteristics

Unless otherwise noted, V_{IN} =1.2 to 5.5V and T_A =-40 to +85°C; typical values are at V_{IN} =4.5V and T_A =25°C.

Symbol	Parameters	Conditions	Min.	Тур.	Max.	Units	
Basic Oper	ration				1		
VIN	Input Voltage		1.2		5.5	V	
I _{Q(OFF)}	Off Supply Current	V _{ON} =GND, V _{OUT} =Open			1.0	μA	
I _{SD}	Shutdown Current	V _{ON} =GND, V _{OUT} =GND		0.2	1.0	μA	
lq	Quiescent Current	I _{OUT} =0 mA		5.5	8.0	μA	
		V _{IN} =5.5 V, I _{OUT} =1 A ⁽³⁾		20	24	1	
		V _{IN} =4.5 V, I _{OUT} =1 A, T _A =25°C 21		21	25		
P	On Resistance	V _{IN} =3.3 V, I _{OUT} =500 mA ⁽³⁾	24 29				
R _{ON}		V _{IN} =2.5 V, I _{OUT} =500 mA ⁽³⁾	1	28	35	mΩ	
		V _{IN} =1.8 V, I _{OUT} =250 mA ⁽³⁾		37	45		
		V _{IN} =1.2 V, I _{OUT} =250 mA, T _A =25°C		75	100		
R _{PD}	Output Discharge RPULL DOWN	V_{IN} =4.5 V, V_{ON} =0 V, I_{FORCE} =20 mA, T_A =25°C		65	85	Ω	
V _{IH}	On Input Logic HIGH Voltage		1.0			V	
VIL	On Input Logic LOW Voltage				0.4	V	
I _{ON}	On Input Leakage				1.5	μA	
Dynamic C	haracteristics						
t _{DON}	Turn-On Delay ⁽⁴⁾			1.7		ms	
t _R	V _{OUT} Rise Time ⁽⁴⁾	V _{IN} =4.5 V, R _L =5 Ω, C _L =100 μF, T _A =25°C		2.7		ms	
t _{ON}	Turn-On Time ⁽⁶⁾			4.4		ms	
t _{DOFF}	Turn-Off Delay ^(4,5)			0.5		ms	
t _F	V _{OUT} Fall Time ^(4,5)	V _{IN} =4.5 V, R _L =150 Ω, C _L =100 μF, T _A =25°C ⁽⁵⁾		10.0		ms	
toff	Turn-Off ^(5,7)	-20 0		10.5		ms	

Notes:


3. This parameter is guaranteed by design and characterization; not production tested.


4. $t_{DON}/t_{DOFF}/t_R/t_F$ are defined in Figure 32.

5. Output discharge enabled during off-state.


6. t_{ON}=t_R + t_{DON}


7. t_{OFF}=t_F + t_{DOFF}






FPF1039 — IntelliMAXTM Advanced Slew Rate Controlled Load Switch







FPF1039 — IntelliMAXTM Advanced Slew Rate Controlled Load Switch

Application Information

Input Capacitor

This IntelliMAXTM switch doesn't require an input capacitor. To reduce device inrush current, a 0.1 μ F ceramic capacitor, C_{IN}, is recommended close to the VIN pin. A higher value of C_{IN} can be used to reduce the voltage drop experienced as the switch is turned on into a large capacitive load.

Output Capacitor

While this switch works without an output capacitor: if parasitic board inductance forces V_{OUT} below GND when switching off; a 0.1 μ F capacitor, C_{OUT} , should be placed between V_{OUT} and GND.

Fall Time

Device output fall time can be calculated based on RC constant of the external components as follows:

$$t_{\rm F} = R_{\rm L} \times C_{\rm L} \times 2.2 \tag{1}$$

where t_F is 90% to 10% fall time, R_L is output load, and C_L is output capacitor.

The same equation works for a device with a pull-down output resistor. R_L is replaced by a parallel connected pull-down and an external output resistor combination as:


$$t_{F} = \frac{R_{L} \times R_{PD}}{R_{L} + R_{PD}} \times C_{L} \times 2.2$$
(2)

where t_F is 90% to 10% fall time, R_L is output load, R_{PD} =65 Ω is output pull-down resistor, and C_L is the output capacitor.

Resistive Output Load

If resistive output load is missing, the IntelliMAX switch without a pull-down output resistor does not discharge the output voltage. Output voltage drop depends, in that case, mainly on external device leaks.

Application Specifics



At maximum operational voltage (V_{IN} =5.5 V), device inrush current might be higher than expected. Spike current should be taken into account if V_{IN} >5 V and the output capacitor is much larger than the input capacitor. Input current can be calculated as:

$$I_{IN}(t) \approx \frac{V_{OUT}(t)}{R_{LOAD}} + (C_{LOAD} - C_{IN}) \frac{dV_{OUT}(t)}{dt}$$
(3)

where switch and wire resistances are neglected and capacitors are assumed ideal.

Estimating $V_{OUT}(t)=V_{IN}/10$ and using experimental formula for slew rate $(dV_{OUT}(t)/dt)$, spike current can be written as:

$$\max(I_{\rm IN}) = \frac{V_{\rm IN}}{10R_{\rm LOAD}} + (C_{\rm LOAD} - C_{\rm IN}) \left(0.05 V_{\rm IN} - 0.255 \right)$$
(4)

where supply voltage V_{IN} is in volts, capacitances are in micro farads, and resistance is in ohms.

Example: If V_{IN} =5.5V, C_{LOAD} =100 µF, C_{IN} =10 µF, and R_{LOAD} =50 Ω ; calculate the spike current by:

$$\max(I_{\rm IN}) = \frac{5.5}{10^{*}50} + (100 - 10)(0.05^{*}5.5 - 0.255)A = 1.8A$$
 (5)

Maximum spike current is 1.8 A, while average rampup current is:

$$I_{IN}(t) \approx \frac{V_{OUT}(t)}{R_{LOAD}} + (C_{LOAD} - C_{IN}) \frac{dV_{IN}(t)}{dt}$$

$$\approx 2.75 / 50 + 100 * 0.0022 = 0.275 \text{ A}$$
(6)

Output Discharge

FPF1039 contains a 65 Ω on-chip pull-down resistor for quick output discharge. The resistor is activated when the switch is turned off.

Recommended Layout

For best thermal performance and minimal inductance and parasitic effects, it is recommended to keep input and output traces short and capacitors as close to the device as possible. Figure 34 is a recommended layout for this device to achieve optimum performance.





Figure 34. Recommended Land Pattern, Layout



FPF1039 — Advance Load Management Switch Management Switch Advance Load Management Switch

Nominal Values

Bump	Overall Package	Silicon	Solder Bump	Solder Bump	
Pitch	Height	Thickness	Height	Diameter	
0.5 mm	0.582 mm	0.332 mm	0.250 mm		

Product-Specific Dimensions

Product	D	E	Х	Y
FPF1039UCX	1.46 mm ±0.03	0.96 mm ±0.03	0.230 mm	0.230 mm
FPF1039BUCX	1.46 mm ±0.03	0.96 mm ±0.03	0.230 mm	0.230 mm



FPF1039 —

No Identification Needed

Obsolete

Full Production

Not In Production

Rev. 174

changes at any time without notice to improve the design.

Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make

Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor has against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death ass

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC