

#### Is Now Part of



# ON Semiconductor®

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to Fairchild <a href="guestions@onsemi.com">guestions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



FSBF15CH60CT

November 2009

# Motion - SPM™

#### **Features**

UL Certified No.E209204(SPM27-JA package)

**Smart Power Module** 

- 600V-15A 3-phase IGBT inverter bridge including control ICs for gate driving and protection
- Easy PCB layout due to built in bootstrap diode
- Divided negative dc-link terminals for inverter current sensing applications
- Single-grounded power supply due to built-in HVIC
- Isolation rating of 2500Vrms/min.

#### **Applications**

- AC 100V  $\sim$  253V three-phase inverter drive for small power ac motor drives
- Home appliances applications like air conditioner and washing mashine

#### **General Description**

It is an advanced motion-smart power module (Motion-SPM™) that Fairchild has newly developed and designed to provide very compact and high performance ac motor drives mainly targeting low-power inverter-driven application like air conditioner and washing machine. It combines optimized circuit protection and drive matched to low-loss IGBTs. System reliability is further enhanced by the integrated under-voltage lock-out and short-circuit protection. The high speed built-in HVIC provides opto-coupler-less single-supply IGBT gate driving capability that further reduce the overall size of the inverter system design. Each phase current of inverter can be monitored separately due to the divided negative dc terminals.

# **Top View Bottom View**

Figure 1.

### **Integrated Power Functions**

• 600V-50A IGBT inverter for three-phase DC/AC power conversion (Please refer to Figure 3)

#### Integrated Drive, Protection and System Control Functions

- For inverter high-side IGBTs: Gate drive circuit, High voltage isolated high-speed level shifting
   Control circuit under-voltage (UV) protection
   Note) Available bootstrap circuit example is given in Figures 12 and 13.
- For inverter low-side IGBTs: Gate drive circuit, Short circuit protection (SC)
   Control supply circuit under-voltage (UV) protection
- · Fault signaling: Corresponding to UV (Low-side supply) and SC faults
- Input interface: 3.3/5V CMOS/LSTTL compatible, Schmitt trigger input

## **Pin Configuration**


#### **Top View** 13.3 (1) V<sub>CC(L)</sub> (2) COM (21) $N_U$ 0 (3) IN<sub>(UL)</sub> (4) IN<sub>(VL)</sub> (22) $N_V$ (5) IN<sub>(WL)</sub> 19.1 (6) V<sub>FO</sub> $(23) N_W$ (7) C<sub>FOD</sub> (8) Csc (9) IN<sub>(UH)</sub> Case Temperature (Tc) (10) V<sub>CC(H)</sub> Detecting Point (11) $V_{B(U)} =$ (12) V<sub>S(U)</sub> = (13) IN<sub>(VH)</sub> (25) V (14) V<sub>CC(H)</sub> (15) V<sub>B(V)</sub> = (16) V<sub>S(V)</sub> -(26) W (17) IN(WH) Ceramic Substrate (18) V<sub>CC(H)</sub> (19) V<sub>B(W)</sub> (27) P (20) V<sub>S(W)</sub> 5

Figure 2.

# Pin Descriptions

Pin Number	Pin Name	Pin Description
1	V <sub>CC(L)</sub>	Low-side Common Bias Voltage for IC and IGBTs Driving
2	COM	Common Supply Ground
3	IN <sub>(UL)</sub>	Signal Input for Low-side U Phase
4	IN <sub>(VL)</sub>	Signal Input for Low-side V Phase
5	IN <sub>(WL)</sub>	Signal Input for Low-side W Phase
6	V <sub>FO</sub>	Fault Output
7	C <sub>FOD</sub>	Capacitor for Fault Output Duration Time Selection
8	C <sub>SC</sub>	Capacitor (Low-pass Filter) for Short-Current Detection Input
9	IN <sub>(UH)</sub>	Signal Input for High-side U Phase
10	V <sub>CC(H)</sub>	High-side Common Bias Voltage for IC and IGBTs Driving
11	V <sub>B(U)</sub>	High-side Bias Voltage for U Phase IGBT Driving
12	V <sub>S(U)</sub>	High-side Bias Voltage Ground for U Phase IGBT Driving
13	IN <sub>(VH)</sub>	Signal Input for High-side V Phase
14	V <sub>CC(H)</sub>	High-side Common Bias Voltage for IC and IGBTs Driving
15	V <sub>B(V)</sub>	High-side Bias Voltage for V Phase IGBT Driving
16	V <sub>S(V)</sub>	High-side Bias Voltage Ground for V Phase IGBT Driving
17	IN <sub>(WH)</sub>	Signal Input for High-side W Phase
18	V <sub>CC(H)</sub>	High-side Common Bias Voltage for IC and IGBTs Driving
19	V <sub>B(W)</sub>	High-side Bias Voltage for W Phase IGBT Driving
20	V <sub>S(W)</sub>	High-side Bias Voltage Ground for W Phase IGBT Driving
21	N <sub>U</sub>	Negative DC-Link Input for U Phase
22	N <sub>V</sub>	Negative DC–Link Input for V Phase
23	N <sub>W</sub>	Negative DC-Link Input for W Phase
24	U	Output for U Phase
25	V	Output for V Phase
26	W	Output for W Phase
27	Р	Positive DC-Link Input

# **Internal Equivalent Circuit and Input/Output Pins**



#### Note

- 1) Inverter low-side is composed of three IGBTs, freewheeling diodes for each IGBT and one control IC. It has gate drive and protection functions.
- 2) Inverter power side is composed of four inverter dc-link input terminals and three inverter output terminals.
- 3) Inverter high-side is composed of three IGBTs, freewheeling diodes and three drive ICs for each IGBT.

Figure 3.

# **Absolute Maximum Ratings** (T<sub>J</sub> = 25°C, Unless Otherwise Specified)

#### **Inverter Part**

Symbol	Parameter	Conditions	Rating	Units
V <sub>PN</sub>	Supply Voltage	Applied between P- N <sub>U</sub> , N <sub>V</sub> , N <sub>W</sub>	450	V
V <sub>PN(Surge)</sub>	Supply Voltage (Surge)	Applied between P- N <sub>U</sub> , N <sub>V</sub> , N <sub>W</sub>	500	V
V <sub>CES</sub>	Collector-emitter Voltage		600	V
± I <sub>C</sub>	Each IGBT Collector Current	T <sub>C</sub> = 25°C	15	Α
± I <sub>CP</sub>	Each IGBT Collector Current (Peak)	T <sub>C</sub> = 25°C, Under 1ms Pulse Width	30	Α
P <sub>C</sub>	Collector Dissipation	T <sub>C</sub> = 25°C per One Chip	25	W
T <sub>J</sub>	Operating Junction Temperature	(Note 1)	-40 ~ 150	°C

#### **Control Part**

Symbol	Parameter	Conditions	Rating	Units
V <sub>CC</sub>	Control Supply Voltage	Applied between V <sub>CC(H)</sub> , V <sub>CC(L)</sub> - COM	20	V
$V_{BS}$	High-side Control Bias Voltage	Applied between $V_{B(U)}$ - $V_{S(U)}$ , $V_{B(V)}$ - $V_{S(V)}$ , $V_{B(W)}$ - $V_{S(W)}$	20	V
V <sub>IN</sub>	Input Signal Voltage	Applied between $IN_{(UH)}$ , $IN_{(VH)}$ , $IN_{(WH)}$ , $IN_{(UL)}$ , $IN_{(VL)}$ , $IN_{(WL)}$ - COM	-0.3~17	V
V <sub>FO</sub>	Fault Output Supply Voltage	Applied between V <sub>FO</sub> - COM	-0.3~V <sub>CC</sub> +0.3	V
I <sub>FO</sub>	Fault Output Current	Sink Current at V <sub>FO</sub> Pin	5	mA
V <sub>SC</sub>	Current Sensing Input Voltage	Applied between C <sub>SC</sub> - COM	-0.3~V <sub>CC</sub> +0.3	V

## **Bootstrap Diode Part**

Symbol	Parameter	Conditions	Rating	Units
$V_{RRM}$	Maixmum Repetitive Reverse Voltage		600	V
I <sub>F</sub>	Forward Current	T <sub>C</sub> = 25°C	0.5	Α
I <sub>FP</sub>	Forward Current (Peak)	T <sub>C</sub> = 25°C, Under 1ms Pulse Width	2	Α
$T_J$	Operating Junction Temperature		-40 ~ 150	°C

## **Total System**

Symbol	Parameter	Conditions	Rating	Units
V <sub>PN(PROT)</sub>	Self Protection Supply Voltage Limit (Short Circuit Protection Capability)	$V_{CC}$ = $V_{BS}$ = 13.5 ~ 16.5V $T_J$ = 150°C, Non-repetitive, less than 2 $\mu$ s	400	V
T <sub>STG</sub>	Storage Temperature		-40 ~ 150	°C
V <sub>ISO</sub>	Isolation Voltage	60Hz, Sinusoidal, AC 1 minute, Connection Pins to ceramic substrate	2500	V <sub>rms</sub>

#### **Thermal Resistance**

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
R <sub>th(j-c)Q</sub>	Junction to Case Thermal	Inverter IGBT part (per 1/6 module)	-	-	4.9	°C/W
R <sub>th(j-c)F</sub>	Resistance	Inverter FWD part (per 1/6 module)	-	-	5.7	°C/W

#### Note:

<sup>1.</sup> The maximum junction temperature rating of the power chips integrated within the SPM is  $150^{\circ}$ C.

<sup>2.</sup> For the measurement point of case temperature( $T_{\mbox{\scriptsize C}}$ ), please refer to Figure 2.

# $\textbf{Electrical Characteristics} \ \, (\textbf{T}_{J} = 25^{\circ}\textbf{C}, \, \textbf{Unless Otherwise Specified})$

#### **Inverter Part**

S	ymbol	Parameter	Condi	tions	Min.	Тур.	Max.	Units
V	CE(SAT)	Collector-Emitter Saturation Voltage	$V_{CC} = V_{BS} = 15V$ $I_{C} = 15A, T_{J} = 25^{\circ}C$ $V_{IN} = 5V$		-	-	2.2	V
	V <sub>F</sub>	FWD Forward Voltage	V <sub>IN</sub> = 0V	I <sub>C</sub> = 15A, T <sub>J</sub> = 25°C	-	-	2.5	V
HS	t <sub>ON</sub>	Switching Times	V <sub>PN</sub> = 300V, V <sub>CC</sub> = V <sub>BS</sub>	<sub>S</sub> = 15V	-	0.85	-	μS
	t <sub>C(ON)</sub>		$I_C = 15A$	ve Load	-	0.15	-	μS
	t <sub>OFF</sub>		$V_{IN} = 0V \leftrightarrow 5V$ , Inductive Load (Note 3)		-	0.45	-	μS
	t <sub>C(OFF)</sub>				-	0.10	-	μS
	t <sub>rr</sub>				-	0.10	-	μS
LS	t <sub>ON</sub>		V <sub>PN</sub> = 300V, V <sub>CC</sub> = V <sub>BS</sub>	<sub>S</sub> = 15V	-	0.55	-	μS
	t <sub>C(ON)</sub>		$I_C = 15A$ $V_{IN} = 0V \leftrightarrow 5V$ , Inducti	ve I nad	-	0.25	-	μS
	t <sub>OFF</sub>		(Note 3)	ve Load	-	0.45	-	μS
	t <sub>C(OFF)</sub>				-	0.10	-	μS
	t <sub>rr</sub>				-	0.15	-	μS
	I <sub>CES</sub>	Collector-Emitter Leakage Current	V <sub>CE</sub> = V <sub>CES</sub>		-	-	1	mA

#### Note

#### **Control Part**

Symbol	Parameter	Co	nditions	Min.	Тур.	Max.	Units
I <sub>QCCL</sub>	Quiescent V <sub>CC</sub> Supply Current	V <sub>CC</sub> = 15V IN <sub>(UL, VL, WL)</sub> = 0V	V <sub>CC(L)</sub> - COM	-	-	23	mA
Ідссн		V <sub>CC</sub> = 15V IN <sub>(UH, VH, WH)</sub> = 0V	V <sub>CC(H)</sub> - COM	-	-	600	μΑ
I <sub>QBS</sub>	Quiescent V <sub>BS</sub> Supply Current	V <sub>BS</sub> = 15V IN <sub>(UH, VH, WH)</sub> = 0V	$V_{B(U)}$ - $V_{S(U)}$ , $V_{B(V)}$ - $V_{S(V)}$ , $V_{B(W)}$ - $V_{S(W)}$	-	-	500	μА
V <sub>FOH</sub>	Fault Output Voltage	V <sub>SC</sub> = 0V, V <sub>FO</sub> Circu	$V_{SC}$ = 0V, $V_{FO}$ Circuit: 4.7k $\Omega$ to 5V Pull-up		-	-	V
V <sub>FOL</sub>		V <sub>SC</sub> = 1V, V <sub>FO</sub> Circu	it: 4.7kΩ to 5V Pull-up	-	-	0.8	V
V <sub>SC(ref)</sub>	Short Circuit Trip Level	V <sub>CC</sub> = 15V (Note 4)		0.45	0.5	0.55	V
UV <sub>CCD</sub>	Supply Circuit Under-	Detection Level		10.7	11.9	13.0	V
UV <sub>CCR</sub>	Voltage Protection	Reset Level		11.2	12.4	13.4	V
UV <sub>BSD</sub>		Detection Level		10	11	12	V
UV <sub>BSR</sub>		Reset Level	Reset Level		11.5	12.5	V
t <sub>FOD</sub>	Fault-out Pulse Width	C <sub>FOD</sub> = 33nF (Note 5)		1.0	1.8	-	ms
V <sub>IN(ON)</sub>	ON Threshold Voltage	Applied between IN <sub>(UH)</sub> , IN <sub>(VH)</sub> , IN <sub>(WH)</sub> , IN <sub>(UL)</sub> ,		2.8	-	-	V
V <sub>IN(OFF)</sub>	OFF Threshold Voltage	IN <sub>(VL)</sub> , IN <sub>(WL)</sub> - COM		-	-	0.8	V

6

#### Note

<sup>3.</sup>  $t_{ON}$  and  $t_{OFF}$  include the propagation delay time of the internal drive IC.  $t_{C(ON)}$  and  $t_{C(OFF)}$  are the switching time of IGBT itself under the given gate driving condition internally. For the detailed information, please see Figure 4.

<sup>4.</sup> Short-circuit current protection is functioning only at the low-sides.

<sup>5.</sup> The fault-out pulse width  $t_{FOD}$  depends on the capacitance value of  $C_{FOD}$  according to the following approximate equation :  $C_{FOD} = 18.3 \times 10^{-6} \times t_{FOD}[F]$ 




Figure 4. Switching Time Definition

#### **Switching Loss (Typical)**





Figure 5. Switching Loss Characteristics

#### **Bootstrap Diode Part**

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
V <sub>F</sub>	Forward Voltage	I <sub>F</sub> = 0.1A, T <sub>C</sub> = 25°C	-	2.5	-	V
t <sub>rr</sub>	Reverse Recovery Time	I <sub>F</sub> = 0.1A, T <sub>C</sub> = 25°C	-	80	-	ns



#### Note:

6. Built in bootstrap diode includes around 15  $\!\Omega$  resistance characteristic.

Figure 6. Built in Bootstrap Diode Characteristics

# **Recommended Operating Conditions**

Symbol	Parameter	Conditions	Value			Units
Symbol	mbol Farameter Conditions		Min.	Тур.	Max.	Ullits
V <sub>PN</sub>	Supply Voltage	Applied between P - N <sub>U</sub> , N <sub>V</sub> , N <sub>W</sub>	-	300	400	V
V <sub>CC</sub>	Control Supply Voltage	Applied between V <sub>CC(H)</sub> , V <sub>CC(L)</sub> - COM	13.5	15	16.5	V
V <sub>BS</sub>	High-side Bias Voltage	Applied between $V_{B(U)}$ - $V_{S(U)}$ , $V_{B(V)}$ - $V_{S(V)}$ , $V_{B(W)}$ - $V_{S(W)}$	13.0	15	18.5	V
dV <sub>CC</sub> /dt, dV <sub>BS</sub> /dt	Control supply variation		-1	-	1	V/μs
t <sub>dead</sub>	Blanking Time for Preventing Arm-short	For Each Input Signal	1.5	-	-	μ\$
f <sub>PWM</sub>	PWM Input Signal	$-20^{\circ}C \le T_J \le 125^{\circ}C$	-	-	20	kHz
V <sub>SEN</sub>	Voltage for Current Sensing	Applied between $N_U$ , $N_V$ , $N_W$ - COM (Including surge voltage)	-4		4	V

8

# **Mechanical Characteristics and Ratings**

Parameter	Co		Units			
Parameter		Min.	Тур.	Max.	Ullits	
Mounting Torque	Mounting Screw: - M3	Recommended 0.62N•m	0.51	0.62	1.00	N•m
Device Flatness		Note Figure 5	0	-	+120	μm
Weight			-	15.4	-	g





Figure 7. Flatness Measurement Position

# **Package Marking and Ordering Information**


Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FSBF15CH60CT	FSBF15CH60CT	SPM27-JA		-	10

#### **Time Charts of SPMs Protective Function**



- a1 : Control supply voltage rises: After the voltage rises UV<sub>CCR</sub>, the circuits start to operate when next input is applied.
- a2: Normal operation: IGBT ON and carrying current.
- a3 : Under voltage detection (UV<sub>CCD</sub>).
- a4: IGBT OFF in spite of control input condition.
- a5 : Fault output operation starts.
- a6 : Under voltage reset (UV $_{CCR}$ ).
- a7: Normal operation: IGBT ON and carrying current.


Figure 8. Under-Voltage Protection (Low-side)



i duit Output Oigha

- $\verb|b1|: Control supply voltage rises: After the voltage reaches UV_{BSR}, the circuits start to operate when next input is applied.$
- b2: Normal operation: IGBT ON and carrying current.
- b3 : Under voltage detection (UV<sub>BSD</sub>).
- b4: IGBT OFF in spite of control input condition, but there is no fault output signal.
- b5 : Under voltage reset (UV<sub>BSR</sub>)
- b6: Normal operation: IGBT ON and carrying current


Figure 9. Under-Voltage Protection (High-side)



(with the external shunt resistance and CR connection)

- c1: Normal operation: IGBT ON and carrying current.
- c2 : Short circuit current detection (SC trigger).
- c3: Hard IGBT gate interrupt.
- c4: IGBT turns OFF.
- c5 : Fault output timer operation starts: The pulse width of the fault output signal is set by the external capacitor  $C_{FO}$ .
- c6: Input "L": IGBT OFF state.
- c7 : Input "H": IGBT ON state, but during the active period of fault output the IGBT doesn't turn ON.
- c8: IGBT OFF state


Figure 10. Short-Circuit Current Protection (Low-side Operation only)



#### Note:

- 1) RC coupling at each input (parts shown dotted) might change depending on the PWM control scheme used in the application and the wiring impedance of the application's printed circuit board. The SPM input signal section integrates 5kΩ (typ.) pull-down resistor. Therefore, when using an external filtering resistor, please pay attention to the signal voltage drop at input terminal.
- 2) The logic input is compatible with standard CMOS or LSTTL outputs.

Figure 11. Recommended CPU I/O Interface Circuit




These Values depend on PWM Control Algorithm

#### Note:

1) The ceramic capacitor placed between V<sub>CC</sub>-COM should be over 1uF and mounted as close to the pins of the SPM as possible.

Figure 12. Recommended Bootstrap Operation Circuit and Parameters




#### Note:

- 1) To avoid malfunction, the wiring of each input should be as short as possible. (less than 2-3cm)
- 2) By virtue of integrating an application specific type HVIC inside the SPM, direct coupling to CPU terminals without any opto-coupler or transformer isolation is possible.
- 3) V<sub>FO</sub> output is open collector type. This signal line should be pulled up to the positive side of the 5V power supply with approximately 4.7kΩ resistance. Please refer to Figure11.
- 4)  $C_{SP15}$  of around 7 times larger than bootstrap capacitor  $C_{BS}$  is recommended.
- 5)  $V_{FO}$  output pulse width should be determined by connecting an external capacitor( $C_{FOD}$ ) between  $C_{FOD}$ (pin7) and COM(pin2). (Example : if  $C_{FOD}$  = 33 nF, then  $t_{FO}$  = 1.8ms (typ.)) Please refer to the note 5 for calculation method.
- 6) Input signal is High-Active type. There is a  $5k\Omega$  resistor inside the IC to pull down each input signal line to GND. RC coupling circuits is recommended for the prevention of input signal oscillation.  $R_SC_{PS}$  time constant should be selected in the range 50~150ns.  $C_{PS}$  should not be less than 1nF. (Recommended  $R_S=100\,\Omega$ ,  $C_{PS}=1$ nF)
- 7) To prevent errors of the protection function, the wiring around  $\rm R_{F}$  and  $\rm C_{SC}$  should be as short as possible.
- 8) In the short-circuit protection circuit, please select the  $R_F C_{SC}$  time constant in the range 1.5~2 $\mu$ s.
- 9) Each capacitor should be mounted as close to the pins of the SPM as possible.
- 10) To prevent surge destruction, the wiring between the smoothing capacitor and the P&GND pins should be as short as possible. The use of a high frequency non-inductive capacitor of around 0.1~0.22µF between the P&GND pins is recommended.
- 11) Relays are used at almost every systems of electrical equipments of home appliances. In these cases, there should be sufficient distance between the CPU and the relays.
- 12)  $C_{SPC15}$  should be over  $1\mu F$  and mounted as close to the pins of the SPM as possible.


Figure 13. Typical Application Circuit


# **Detailed Package Outline Drawings**




Lead Pitch :  $\pm 0.30$ 


A: 1.778
B: 2.050
C: 2.531








# **Detailed Package Outline Drawings (Continued)**





Lead Forming Dimension




PKG Center to Lead Distance

# **Detailed Package Outline Drawings (Continued)**











#### **TRADEMARKS**

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

Build it Now™ CorePLUS™ CorePOWER™ CROSSVOLT™

CTL™

Current Transfer Logic™ EcoSPARK®

EfficentMax™ EZSWITCH™ \*

airchild®

FastvCore<sup>™</sup>

Fairchild Semiconductor® FACT Quiet Series™ FACT® FAST®

FlashWriter® \* FPS™ F-PFS™

FRFET® Global Power Resource<sup>SM</sup>

Green FPS™ Green FPS™ e-Series™

GTO™ IntelliMAX™ ISOPLANAR™ MegaBuck™ MICROCOUPLER™ MicroFET™ MicroPak™

MillerDrive™ MotionMax™ Motion-SPM™ OPTOLOGIC® OPTOPLANAR®

PDP SPM™ Power-SPM™ PowerTrench® PowerXS™

Programmable Active Droop™

QFĔT<sup>®</sup> QS™ Quiet Series™ RapidConfigure™

Saving our world, 1mW /W /kW at a time™

SmartMax™ SMART START™ SPM®

STEALTH™ SuperFET™ SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS™ SyncFET™

SYSTEM ® GENERAL

The Power Franchise®

bwer franchise TinyBoost™ TinyBuck™ TinyLogic<sup>®</sup>
TINYOPTO™ TinyPower™ TinyPWM™ TinyWire™ TriFault Detect™ μSerDes™

**UHC®** Ultra FRFET™

UniFET™ VCX™ VisualMax™ XSTN

\* EZSWITCH™ and FlashWriter® are trademarks of System General Corporation, used under license by Fairchild Semiconductor

#### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

EIFE SUPPORT FOLICES.
FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness

#### ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.Fairchildsemi.com, under Sales Support.

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufactures of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed application, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handing and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address and warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

#### PRODUCT STATUS DEFINITIONS **Definition of Terms**

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev. I38

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor and see no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and h

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative