ON Semiconductor

Is Now

Onsemi

To learn more about onsemi[™], please visit our website at <u>www.onsemi.com</u>

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product factures, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and asfety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or by customer's technical experts. onsemi products and actal performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiari



Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized applications, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an equif prese



Features

- Brownout Protection with Hysteresis
- Built-In 5ms Soft-Start Function
- Internal Avalanche-Rugged 700V SenseFET
- No Acoustic Noise During Light-Load Operation
- High-Voltage Startup

SEMICONDUCTOR

- Linearly Decreasing PWM Frequency to 18KHz
- Peak-Current-Mode Control
- Cycle-by-Cycle Current Limiting
- Leading-Edge Blanking (LEB)
- Synchronized Slope Compensation
- Internal Open-Loop Protection
- V_{DD} Under-Voltage Lockout (UVLO)
- V_{DD} Over-Voltage Protection (OVP)
- Internal Auto-Restart Circuit (OVP, OTP)
- Constant Power Limit (Full AC Input Range)
- Internal OTP Sensor with Hysteresis
- VIN Pin for Pull-HIGH Latch Function and Pull-LOW Auto-Recovery Protection

Applications

General-purpose switch-mode power supplies and flyback power converters, including:

- Auxiliary Power Supply for PC and Server
- SMPS for VCR, SVR, STB, DVD & DVCD Player, Printer, Facsimile, and Scanner
- Adapter for Camcorder

Description

The highly integrated FSBH-series consists of an integrated current-mode Pulse Width Modulator (PWM) and an avalanche-rugged 700V SenseFET. It is specifically designed for high-performance offline Switch Mode Power Supplies (SMPS) with minimal external components.

The integrated PWM controller features include a proprietary green-mode function that provides off-time modulation to linearly decrease the switching frequency at light-load conditions to minimize standby power consumption. To avoid acoustic-noise problems, the minimum PWM frequency is set above 18kHz. This green-mode function enables the power supply to meet international power conservation requirements. The PWM controller is manufactured using the BiCMOS process to further reduce power consumption. The FSBH-series turns off some internal circuits to improve power saving when V_{FB} is lower than 1.6V, which allows an operating current of only 2.5mA.

The FSBH-series has built-in synchronized slope compensation to achieve stable peak-current-mode control. The proprietary external line compensation ensures constant output power limit over a wide AC input voltage range, from $90V_{AC}$ to $264V_{AC}$.

The FSBH-series provides many protection functions. In addition to cycle-by-cycle current limiting, the internal open-loop protection circuit ensures safety when an open-loop or output short occurs. PWM output is disabled until V_{DD} drops below the V_{TH-OLP} , then the controller starts up again. As long as V_{DD} exceeds 28V, the internal OVP circuit is triggered.

Compared with a discrete MOSFET and controller or RCC switching converter solution, the FSBH-series reduces total component count, design size, and weight; while increasing efficiency, productivity, and system reliability. These devices provide a basic platform that is well suited for the design of costeffective flyback converters, such as in PC auxiliary power supplies.

Ordering Information									
Part Number Sense FET		Operating Temperature Range	VIN Pin (PIN #4)	Package	Packing Method				
FSBH0F70ANY	0.5A 700V	-40°C to +105°C							
FSBH0170ANY	1.0A 700V	-40°C to +105°C	Not Available						
FSBH0270ANY	2.0A 700V	-40°C to +105°C	-	8-Pin Dual In-Line	Tube				
FSBH0170NY	1.0A 700V	-40°C to +105°C		Package (DIP)	Tube				
FSBH0270NY	2.0A 700V	-40°C to +105°C	Enabled						
FSBH0370NY	3.0A 700V	-40°C to +105°C	-						

Application Diagram




Figure 1. Typical Flyback Application

Output Power Table⁽¹⁾

Product	230V _{AC}	± 15% ⁽²⁾	85-265V _{AC}		
	Adapter ⁽³⁾	Open Frame ⁽⁴⁾	Adapter ⁽³⁾	Open Frame ⁽⁴⁾	
FSBH0F70A	7W	10W	6W	8W	
FSBH0170/A	10W	15W	9W	13W	
FSBH0270/A	14W	20W	11W	16W	
FSBH0370	17.5W	25W	13W	19W	


Notes:


1. The maximum output power can be limited by junction temperature.


2. 230 $V_{AC}\, or\, 100/115\, V_{AC}$ with doublers.

3. Typical continuous power in a non-ventilated enclosed adapter with sufficient drain pattern as a heat sink at 50°C ambient.

4. Maximum practical continuous power in an open-frame design with sufficient drain pattern as a heat sink at 50°C ambient.







Pin Definitions

Pin #	Name	Description
1	GND	Ground. SenseFET source terminal on primary side and internal controller ground.
2	VDD	Power Supply . The internal protection circuit disables PWM output as long as V_{DD} exceeds the OVP trigger point.
3	FB	Feedback . The signal from the external compensation circuit is fed into this pin. The PWM duty cycle is determined in response to the signal on this pin and the internal current-sense signal.
4	VIN	Line-Voltage Detection . The line-voltage detection is used for brownout protection with hysteresis and constant output power limit over universal AC input range. This pin has additional protections that are pull-HIGH latch and pull-LOW auto recovery, depending on the application.
	NC	No Connection for FSBH0F70A, FSBH0170A and FSBH0270A.
5	ΗV	Startup. For startup, this pin is pulled HIGH to the line input or bulk capacitor via resistors.
6	Drain	SenseFET Drain. High-voltage power SenseFET drain connection.
7	Drain	SenseFET Drain. High-voltage power SenseFET drain connection.
8	Drain	SenseFET Drain. High-voltage power SenseFET drain connection.

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Paramete	er	Min.	Max.	Unit
V _{DRAIN}	Drain Pin Voltage ^(5,6)	FSBH0x70/A		700	V
		FSBH0F70A		1.5	
	Drain Current Pulsed ⁽⁷⁾	FSBH0170/A		4.0	A
I _{DM}		FSBH0270/A		8.0	A
		FSBH0370		12.0	
		FSBH0F70A		10	
E	Single Pulsed Avalanche Energy ⁽⁸⁾	FSBH0170/A		50	mJ
E _{AS}	Single Fulsed Avalanche Energy	FSBH0270/A		140	IIIJ
		FSBH0370		230	
V _{DD}	DC Supply Voltage		30	V	
V _{FB}	FB Pin Input Voltage	-0.3	7.0	V	
V _{IN}	VIN Pin Input Voltage	-0.3	7.0	V	
V _{HV}	HV Pin Input Voltage		700	V	
PD	Power Dissipation (T _A < 50°C)		1.5	W	
θ_{JA}	Junction-to-Air Thermal Resistance			80	°C/W
θ _{JC}	Junction-to-Case Thermal Resistance	e		20	°C/W
TJ	Operating Junction Temperature		Internally	limited ⁽⁹⁾	°C
T _{STG}	Storage Temperature Range		-55	+150	°C
ΤL	Lead Temperature (Wave Soldering		+260	°C	
ESD	Electrostatic Discharge Capability,	Human Body Model: JESD22-A114	3		kV
EOD	All pins except HV pin	Charged Device Model: JESD22-C101	1		ĸv

Notes:

5. All voltage values, except differential voltages, are given with respect to the network ground terminal.

6. Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device.

7. Non-repetitive rating: pulse width is limited by maximum junction temperature.

8. L = 51mH, starting $T_1 = 25^{\circ}C$.

9. Internally Limited of T_J refers to T_{OTP}

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

S	Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
	T _A	Operating Ambient Temperature		-40		+105	°C

Symbol	Parame	ter	Condition	Min.	Тур.	Max.	Unit	
SenseFET S	Section ⁽¹⁰⁾							
BV_{DSS}	Drain-Source Breakdown Voltage	FSBH0x70/A	V _{DS} = 700V, V _{GS} = 0V	700			V	
		Zero-Gate-Voltage	FOD 10-70/A	V_{DS} = 700V, V_{GS} = 0V			50	
I _{DSS}	Drain Current	FSBH0x70/A	V _{DS} = 560V, V _{GS} = 0V, T _C = 125°C			200	μA	
		FSBH0F70A			14.00	19.00		
Р	Drain-Source On-	FSBH0170/A			8.80	11.00		
R _{DS(ON)}	State Resistance ⁽¹¹⁾	FSBH0270/A	– V _{GS} = 10V, I _D = 0.5A		6.00	7.20	Ω	
		FSBH0370			4.00	4.75		
		FSBH0F70A			162	211		
0	Innut Consoitance	FSBH0170/A	V _{GS} = 0V, V _{DS} = 25V,		250	325	~~	
C _{ISS}	Input Capacitance	FSBH0270/A	f = 1MHz		550	715	pF	
		FSBH0370			315	410		
Coss	Output Capacitance	FSBH0F70A			18	24	- pF	
		FSBH0170/A	V _{GS} = 0V, V _{DS} = 25V, f = 1MHz		25	33		
		FSBH0270/A			38	50		
		FSBH0370			47	61		
		FSBH0F70A			3.8	5.7	pF	
0	Reverse Transfer	FSBH0170/A	V _{GS} = 0V, V _{DS} = 25V, f = 1MHz		10.0	15.0		
C_{RSS}	Capacitance	FSBH0270/A			17.0	26.0		
		FSBH0370			9.0	24.0		
		FSBH0F70A			9.5	29.0		
		FSBH0170/A			12.0	34.0	- ns	
t _{D(ON)}	Turn-On Delay Time	FSBH0270/A	– V _{DS} = 350V, I _D = 1.0A		20.0	50.0		
		FSBH0370			11.2	33.0		
		FSBH0F70A			19	48		
+	Diao Timo	FSBH0170/A			4	18	- ns	
t _R	Rise Time	FSBH0270/A	- V _{DS} = 350V, I _D = 1.0A		15	40		
		FSBH0370			34	78		
		FSBH0F70A			33.0	76.0		
+_		FSBH0170/A	1/2E01/1-40A		30.0	70.0		
t _{D(OFF)}	Turn-Off Delay Time	FSBH0270/A	V _{DS} = 350V, I _D = 1.0A		55.0	120.0	ns	
		FSBH0370			28.2	67.0		
		FSBH0F70A			42	94		
+		FSBH0170/A			10	30		
t⊨	Fall Time	FSBH0270/A	- V _{DS} = 350V, I _D = 1.0A		25	60	ns	
		FSBH0370	1		32	74	1	

Electrical Characteristics

Continued on the following page...

Symbol	Param	eter	Condition	Min.	Тур.	Max.	Unit
Control Sec	tion					1	
V _{DD} Section	1						
V _{DD-ON}	Start Threshold Voltag	je		11	12	13	V
V _{DD-OFF}	Minimum Operating V	oltage		7	8	9	V
las or S	Startun Current	FSBH0170 FSBH0270 FSBH0370	V _{DD-ON} – 0.16V			30	
I _{DD-ST}	Startup Current	FSBH0F70A FSBH0170A FSBH0270A	V _{DD-ON} – 0.16V	240	320	400	μA
I _{DD-OP}	Operating Supply Cur	rent	V _{DD} = 15V, V _{FB} = 3V	3.0	3.5	4.0	mA
I _{DD-ZDC}	Operating Current for	V _{FB} <v<sub>FB-ZDC</v<sub>	V_{DD} = 12V, V_{FB} = 1.6V	1.5	2.5	3.5	mA
I _{DD-OLP}	Internal Sink Current		V _{TH-OLP} +0.1V	30	70	90	μA
$V_{\text{TH-OLP}}$	I _{DD-OLP} Off Voltage			5	6	7	V
$V_{\text{DD-OVP}}$	V _{DD} Over-Voltage Pro	tection		27	28	29	V
t _{D-VDD-OVP}	V _{DD} Over-Voltage Protection Debounce Time			75	130	200	μs
HV Section							
I _{HV}	Maximum Current Drawn from HV Pin		HV 120V _{DC} , V _{DD} = 0V with 10 μ F	1.5	3.5	5.0	mA
I _{HV-LC}	Leakage Current after Startup		HV = 700V, V _{DD} = V _{DD-OFF} +1V		1	20	μA
Oscillator S	Section						
f _{OSC}	Frequency in Nominal	Mode	Center Frequency	94	100	106	kHz
fosc-g	Green-Mode Frequen	су		14	18	22	kHz
D _{MAX}	Maximum Duty Cycle				85		%
f_{DV}	Frequency Variation v		V _{DD} = 11V to 22V			5	%
f _{DT}	Frequency Variation v Deviation ⁽¹⁰⁾	s. Temperature	T _A = -25 to 85°C			5	%
V _{IN} Section	(FSBH0170, FSBH0270), FSBH0370)					
V _{IN-ON}	PWM Turn-On Thresh	old Voltage		1.08	1.13	1.18	V
$V_{\text{IN-OFF}}$	PWM Turn-Off Thresh	old Voltage		V _{IN-ON} – 0.48	V _{IN-ON} – 0.54	V _{IN-ON} – 0.60	V
$t_{\text{IN-OFF}}$	PWM Turn-Off Debou	nce Time			500		ms
$V_{\text{IN-H}}$	Pull-HIGH Latch Trigg			4.4	4.7	5.0	V
t _{IN-H}	Pull-HIGH Latch Debo				100		μs
V _{IN-L}	Pull-LOW Auto-Recovery Trigger Level			0.2	0.3	0.4	V
Feedback In	nput Section						
A _V	FB Voltage to Current Attenuation	-Sense		1/4.5	1/4.0	1/3.5	V/V
Z _{FB}	Input Impedance			4		7	kΩ

Continued on the following page...

7

Electrical Characteristics (Continued)

 V_{DD} =15V and T_A=25°C unless otherwise specified.

Symbol	Parameter		Condition	Min.	Тур.	Max.	Unit
V _{FB-OPEN}	Output High Voltage		FB Pin Open	5.5			V
$V_{\text{FB-N}}$	Green-Mode Entry FB Voltage			2.3	2.5	2.7	V
V_{FB-G}	Green-Mode Ending F	B Voltage		1.9	2.0	2.1	V
V _{FB-ZDC}	Zero Duty Cycle FB V	oltage			1.6		V
	FB Open-Loop	FSBH0F70A		5.2	5.4	5.6	V
V_{FB-OLP}	Trigger Level	FSBH0x70/A		4.4	4.6	4.8	V
t _{D-OLP}	FB Open-Loop Protec	tion Delay		50	56	59	ms
Current-Ser	nse Section ⁽¹⁴⁾						-
	Peak Current Limit	FSBH0F70A	V _{IN} Open	0.63	0.73	0.83	
		FSBH0170/A	V _{IN} = 1.2V / V _{IN} Open	0.70	0.80	0.90	A
I _{LIM}		FSBH0270/A	V _{IN} = 1.2V / V _{IN} Open	0.90	1.00	1.10	
		FSBH0370	V _{IN} = 1.2V	1.10	1.20	1.30	
t _{ss}	Period During Soft-Start Time ⁽¹⁰⁾			4.5	5.0	5.5	ms
Constant P	ower Limit (FSBH0170	, FSBH0270, FSB	H0370)				
V_{LMT1}	Threshold Voltage 1 f	or Current Limit	V _{IN} = 1.2V	0.73	0.80	0.87	V
V_{LMT2}	Threshold Voltage 2 f	or Current Limit	V _{IN} = 3.6V	0.56	0.63	0.70	V
Current Lim	nit (FSBH0F70A, FSBH	0170A, FSBH0270	DA)				
M		T		0.97	1.00	1.03	V
VLMT	V _{LMT} Threshold Voltage for 0		FSBH0170A/0270A	70A 0.77 0.80		0.83	V
Over-Temp	erature Protection Sec	tion (OTP)					
T _{OTP}	Protection Junction Te	Protection Junction Temperature ^(10, 12)		+135	+142	+150	°C
T _{RESTART}	Restart Junction Tem	perature ^(10, 13)			T _{OTP} -25		°C

Notes:


10. These parameters, although guaranteed, are not 100% tested in production.

11. Pulse test: pulse width \leq 300is, duty \leq 2%.


12. When activated, the output is disabled and the latch is turned off.


13. The threshold temperature for enabling the output again and resetting the latch after over-temperature protection has been activated.

14. These parameters, although guaranteed, are tested in wafer process.









FSBH0F70A, FSBH0170/A, FSBH0270/A, FSBH0370 — Green Mode Fairchild Power Switch (FPS™)




Figure 24. I_{DD-ZDC} vs. Temperature

Figure 25. t_{D-OLP} vs. Temperature

Functional Description

Startup Operation

The HV pin is connected to bulk voltage through an external resistor, R_{HV}, as shown in Figure 26. When AC voltage is applied to power system, an internal HV startup circuit provides a high current (around 3.5mA) to charge an external V_{DD} capacitor until V_{DD} voltage exceeds the turn-on threshold voltage (V_{DD-ON}). For better power consumption, the HV startup circuit shuts down during normal operation. The external V_{DD} capacitor and auxiliary winding maintain the V_{DD} voltage and provide operating current to controller.





Figure 26. Startup Circuit

Slope Compensation

The FSBH-series is designed for flyback power converters. The peak-current-mode control is used to optimize system performance. Slope compensation is added to reduce current loop gain and improve power system stability. The FSBH-series has a built-in, synchronized, positive slope for each switching cycle.

Soft-Start

The FSBH-series has an internal soft-start circuit that reduces the SenseFET switching current during power system startup. The characteristic curve of soft-start time versus V_{LMT} level is shown in Figure 27. The V_{LMT} level slopes up like a six-step staircase. In doing so, power system can smoothly build up the rated output voltage and effectively reduce voltage stress on the PWM switch and output diode.



Brown-In/Out Function

FSBH0x70 has a built-in internal brown-in/out protection comparator monitoring voltage of VIN pin. Figure 28 shows a resistive divider with low-pass filtering for linevoltage detection on the VIN pin.




Figure 28. Brown-In/Out Function on VIN Pin

Once the VIN pin voltage is lower than 0.6V and lasts for 500ms, the PWM gate is disabled to protect the system from over current. FSBH0x70 starts up as $V_{\rm IN}$ increases above 1.1V. Because the divider resistors of the VIN pin are connected behind the bridge, the ratio calculation for brownout in PFC and non-PFC system are different, as shown in Figure 29. The formulas are provided in the following equations:

Brownout with PFC:

$$\frac{R_{\rm C}}{R_{\rm A} + R_{\rm B} + R_{\rm C}} \cdot \sqrt{2} V_{\rm AC_OUT} \cdot \frac{2}{\pi} = 0.6 \tag{1}$$

Brownout with non-PFC:

$$\frac{R_C}{R_A + R_B + R_C} \cdot \sqrt{2} V_{AC_OUT} = 0.6 \tag{2}$$

Brown-in level is determined by:

$$V_{AC_{IN}} = \frac{1.1}{\sqrt{2}} \cdot \frac{R_A + R_B + R_C}{R_C}$$
(3)




Figure 29. VIN Level According to PFC Operation


Brown-In Function of FSBH0x70A

The VIN pin functions are disabled from FSBH0x70A, but FSBH0x70A has brown-in protection in the VDD pin. There is a discharge current internal from V_{DD} to ground during startup. The HV source current must be larger than I_{DD-ST} to charge the capacitor of V_{DD} . Therefore, the brown-in level can be determined by R_{HV} according to the equation:

$$R_{HV} = \frac{\sqrt{2}V_{AC} - 12}{I_{DD-ST}} \tag{4}$$


Green-Mode Operation

The FSBH-series uses feedback voltage (V_{FB}) as an indicator of the output load and modulates the PWM frequency, as shown in Figure 30, such that the switching frequency decreases as load decreases. In heavy load conditions, the switching frequency is 100kHz. Once V_{FB} decreases below V_{FB-N} (2.5V), the PWM frequency starts to linearly decrease from 100kHz to 18kHz for reducing switching losses. As V_{FB} decreases below V_{FB-G} (2.0V), the switching frequency is fixed at 18kHz and FSBH-series enters "deep" green mode to reduce the standby power consumption.





As V_{FB} decreases below V_{FB-ZDC} (1.6V), FSBH-series enters into burst-mode operation. When V_{FB} drops below V_{FB-ZDC} , FSBH-series stops switching and the output voltage starts to drop, which causes the feedback voltage to rise. Once V_{FB} rises above V_{FB-ZDC} , switching resumes. Burst mode alternately enables and disables switching, thereby reducing switching loss to improve power saving, as shown in Figure 31.



H/L Line Over-Power Compensation

To limit the output power of the converter constantly, high/low line over-power compensation is included. Sensing the converter input voltage through the VIN pin, the high/low line compensation function generates a relative peak-current-limit threshold voltage for constant power control, as shown in Figure 32.





Figure 32. Constant Power Control

Protections

The FSBH-series provides full protection functions to prevent the power supply and the load from being damaged. The protection features include:

Latch/Auto-Recovery Function

Besides the brownout protection and high/low line overpower compensation, the FSBH0170/0270/0370 has additional protections via the VIN pin, such as pull-HIGH latch and pull-LOW auto-recovery that depends on the application. As shown in Figure 33, V_{IN} level is higher than 4.7V, FSBH-series is latched until the V_{DD} is discharged. FSBH-series is auto-recovery when the V_{IN} level is lower than 0.3V.







Open-Loop / Overload Protection (OLP)

When the upper branch of the voltage divider for the shunt regulator (KA431 shown) is broken, as shown in Figure 34, or over current or output short occurs, there is no current flowing through the opto-coupler transistor, which pulls the feedback voltage up to 6V.

When feedback voltage is above 4.6V for longer than 56ms, OLP is triggered. This protection is also triggered when the SMPS output drops below the nominal value longer than 56ms due to the overload condition.






V_{DD} Over-Voltage Protection (OVP)

 V_{DD} over-voltage protection prevents IC damage caused by over voltage on the VDD pin. The OVP is triggered when V_{DD} voltage reaches 28V. Debounce time (typically 130µs) prevents false trigger by switching noise.

Over-Temperature Protection (OTP)

The SenseFET and the control IC are integrated, making it easier to detect the temperature of the SenseFET. When the temperature exceeds approximately 142°C, thermal shutdown is activated.



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative