



Product Overview

KAI-16050: Interline Transfer CCD Image Sensor, 16 MP

[For complete documentation, see the data sheet](#)

Product Description

The KAI-16050 Image Sensor is a 16-megapixel CCD in an APS-H optical (32.36 mm diagonal) optical format. Based on the TRUESENSE 5.5 micron Interline Transfer CCD Platform, the sensor features broad dynamic range, excellent imaging performance, and a flexible readout architecture that enables use of 1, 2, or 4 outputs for full resolution readout up to 8 frames per second. A vertical overflow drain structure suppresses image blooming and enables electronic shuttering for precise exposure control. The sensor is available with the TRUESENSE Sparse Color Filter Pattern, a technology which provides a 2x improvement in light sensitivity compared to a standard color Bayer part. The sensor shares common PGA pin-out and electrical configurations with other devices based on the TRUESENSE 5.5 micron Interline Transfer CCD Platform, allowing a single camera design to be leveraged to support multiple members of this sensor family.

Features

- Bayer Color Pattern, TRUESENSE Sparse Color Filter Pattern, and Monochrome configurations
- Progressive scan readout
- Flexible readout architecture
- High frame rate
- High sensitivity
- Low noise architecture
- Excellent smear performance
- Package pin reserved for device identification

Applications

- Digitization
- Intelligent Transportation Systems
- Machine Vision
- Mapping / Aerial
- Photography

Part Electrical Specifications

Product	Compliance	Status	Type	Megapixels	Frame Rate (fps)	Optical Format	Shutter Type	Pixel Size (μm)	Color	Package Type
KAI-16050-AXA-JD-AE	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Mono	CPGA-71
KAI-16050-AXA-JD-B1	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Mono	CPGA-71
KAI-16050-AXA-JD-B2	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Mono	CPGA-71
KAI-16050-CXA-JD-AE	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Bayer Color	CPGA-71
KAI-16050-FXA-JD-AE	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Bayer Color	CPGA-71
KAI-16050-FXA-JD-B1	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Bayer Color	CPGA-71
KAI-16050-FXA-JD-B2	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Bayer Color	CPGA-71
KAI-16050-PXA-JD-AE	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Sparse CFA	CPGA-71
KAI-16050-QXA-JD-AE	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Sparse CFA	CPGA-71
KAI-16050-QXA-JD-B1	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Sparse CFA	CPGA-71
KAI-16050-QXA-JD-B2	Pb-free Halide free	Active	Interline CCD	16	8	APS-H	Electronic	5.5 x 5.5	Sparse CFA	CPGA-71

For more information please contact your local sales support at www.onsemi.com

Created on: 7/11/2015