

MOSFET – Power, Single, N-Channel

60 V, 4.0 mΩ, 100 A

NTMYS4D1N06CL

Features

- Small Footprint (5x6 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- LFPAK4 Package, Industry Standard
- These Devices are Pb-Free and are RoHS Compliant

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V_{DSS}	60	V
Gate-to-Source Voltage	9		V _{GS}	±20	V
Continuous Drain	Steady State	T _C = 25°C	I _D	100	Α
Current R _{θJC} (Notes 1, 2, 3)	State	T _C = 100°C	1	71	
Power Dissipation		T _C = 25°C	P_{D}	79	W
R _{θJC} (Notes 1, 2)		T _C = 100°C		40	
Continuous Drain Current R _{0.IA}	Steady State	T _A = 25°C	I _D	22	Α
(Notes 1, 2, 3)	State	T _A = 100°C		15	
Power Dissipation		T _A = 25°C	P_{D}	3.7	W
R _{θJA} (Notes 1, 2)		T _A = 100°C	1	1.8	
Pulsed Drain Current $T_A = 25^{\circ}C$, $t_p = 10 \mu s$			I _{DM}	820	Α
Operating Junction and Storage Temperature Range			T _J , T _{stg}	-55 to +175	°C
Source Current (Body Diode)			Is	100	Α
Single Pulse Drain-to-Source Avalanche Energy ($T_J = 25$ °C, $I_{L(pk)} = 5$ A)			E _{AS}	185	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State	$R_{\theta JC}$	1.9	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	39	

- The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
- 2. Surface-mounted on FR4 board using a 650 mm², 2 oz. Cu pad.
- Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX	
60 V	4.0 mΩ @ 10 V	100 4	
00 V	5.7 mΩ @ 4.5 V	100 A	




N-CHANNEL MOSFET



LFPAK4 CASE 760AB

MARKING DIAGRAM



4D1N06CL = Specific Device Code A = Assembly Location

WL =Wafer Lot Y = Year W = Work Week

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS					•		
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA		60			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J	·			28		mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	V _{GS} = 0 V.	T _J = 25°C			10	
		$V_{GS} = 0 V$, $V_{DS} = 48 V$	T _J = 125°C			250	μΑ
Gate-to-Source Leakage Current	I _{GSS}	$V_{DS} = 0 V, V_{GS}$	= 20 V			100	nA
ON CHARACTERISTICS (Note 4)					-		
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D$	= 80 μΑ	1.2		2.0	V
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J				-5.4		mV/°C
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 50 A		3.3	4.0	
		V _{GS} = 4.5 V	I _D = 50 A		4.6	5.7	mΩ
Forward Transconductance	9FS	V _{DS} = 15 V, I _D	= 50 A		105		S
CHARGES, CAPACITANCES & GATE RESIS	STANCE				-		
Input Capacitance	C _{ISS}				2200		
Output Capacitance	C _{OSS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 25 V			900		pF
Reverse Transfer Capacitance	C _{RSS}				17		
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = 4.5 \text{ V}, V_{DS} = 30 \text{ V}; I_D = 50 \text{ A}$ $V_{GS} = 10 \text{ V}, V_{DS} = 30 \text{ V}; I_D = 50 \text{ A}$			16		
Total Gate Charge	Q _{G(TOT)}				34		
Threshold Gate Charge	Q _{G(TH)}				1.5		nC
Gate-to-Source Charge	Q_{GS}	$V_{GS} = 4.5 \text{ V}, V_{DS} = 30 \text{ V}; I_D = 50 \text{ A}$			5.6		
Gate-to-Drain Charge	Q_{GD}				5.1		
Plateau Voltage	V_{GP}				2.8		V
SWITCHING CHARACTERISTICS (Note 5)					-		
Turn-On Delay Time	t _{d(ON)}				10		
Rise Time	t _r	V _{GS} = 4.5 V, V _{DS}	s = 30 V,		15		1
Turn-Off Delay Time	t _{d(OFF)}	$I_D = 50 \text{ A}, R_G = 2.5 \Omega$			24		ns
Fall Time	t _f				5.0		
DRAIN-SOURCE DIODE CHARACTERISTIC	s				-		
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V,	T _J = 25°C		0.88	1.2	
		$I_{S} = 50 \text{ A}$ $T_{J} = 125^{\circ}\text{C}$			0.78		V
Reverse Recovery Time	t _{RR}	$V_{GS} = 0$ V, dIS/dt = 100 A/ μ s, $I_{S} = 50$ A			41		
Charge Time	t _a				21		ns
Discharge Time	t _b				20		
Reverse Recovery Charge	Q _{RR}				32		nC
	•				•		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width $\leq 300~\mu s$, duty cycle $\leq 2\%$.

5. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics

Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On–Resistance Variation with Temperature






Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS (continued)



vs. Gate Resistance

1000



 $T_C = 25^{\circ}C$ 0.01 ms $V_{GS}^{-} \le 10 \text{ V}$ 100 l_{DS} (A) 10 ms 10 R_{DS(on)} Limit Thermal Limit Package Limit 10 100

V_{DS} (V) Figure 11. Safe Operating Area

Figure 12. I_{PEAK} vs. Time in Avalanche

TYPICAL CHARACTERISTICS (continued)




Figure 13. Thermal Response




Figure 14. Thermal Response

DEVICE ORDERING INFORMATION

	Device	Marking	Package	Shipping [†]
NTMYS4D	1N06CLTWG	4D1N06CL	LFPAK4 (Pb-Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.





LFPAK4 4.90x4.15x1.15MM, 1.27P CASE 760AB

ISSUE D

1.30


DATE 22 MAY 2024





NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
- CONTROLLING DIMENSION: MILLIMETERS.
- 3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR BURRS. MOLD FLASH PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.150mm PER SIDE.
- 4. DIMENSIONS D AND E ARE DETERMINED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.



D4

(D8)

-	1.61
1	0.70
	↑
,	1.15
	0.70 - - 1.27 -
	RECOMMENDED LAND PATTERN
	*FOR ADDITIONAL INFORMATION ON OUR
	PB-FREE STRATEGY AND SOLDERING
	I B THEE OH WILLIAM GOLDLINIA

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

GENERIC MARKING DIAGRAM*

BOTTOM VIEW

D5

D6 (D7)

XXXXXX XXXXXX AWLYW XXXXXX = Specific Device Code A = Assembly Location

WL = Wafer Lot Y = Year W = Work Week

*This information is generic. Please refer to device data sheet for actual part marking. Some products may not follow the Generic Marking.

DIM MIN NOM MAX A 1.10 1.20 1.30 A1 0.00 0.08 0.15 A2 1.10 1.15 1.20 A3 0.25 BSC 0.50 b 0.40 0.45 0.50 b2 3.80 4.10 4.40 b4 0.45 0.55 0.65 c 0.19 0.22 0.25 c2 0.19 0.22 0.25 D 4.15 BSC 0.20 0.25 D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 <td< th=""><th colspan="6">MILLIMETER</th></td<>	MILLIMETER							
A1 0.00 0.08 0.15 A2 1.10 1.15 1.20 A3 0.25 BSC b 0.40 0.45 0.50 b2 3.80 4.10 4.40 b4 0.45 0.55 0.65 c 0.19 0.22 0.25 c2 0.19 0.22 0.25 D 4.15 BSC D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2<	DIM	DIM MIN NOM MAX						
A2 1.10 1.15 1.20 A3 0.25 BSC b 0.40 0.45 0.50 b2 3.80 4.10 4.40 b4 0.45 0.55 0.65 c 0.19 0.22 0.25 c2 0.19 0.22 0.25 D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00	Α	1.10	1.20	1.30				
A3	A1	0.00	0.08	0.15				
b 0.40 0.45 0.50 b2 3.80 4.10 4.40 b4 0.45 0.55 0.65 c 0.19 0.22 0.25 c2 0.19 0.22 0.25 D 4.15 BSC D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF B8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF	A2	1.10	1.15	1.20				
b2 3.80 4.10 4.40 b4 0.45 0.55 0.65 c 0.19 0.22 0.25 c2 0.19 0.22 0.25 D 4.15 BSC D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0	Α3	().25 BSC					
b4 0.45 0.55 0.65 c 0.19 0.22 0.25 c2 0.19 0.22 0.25 D 4.15 BSC D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90	b	0.40	0.45	0.50				
C 0.19 0.22 0.25 c2 0.19 0.22 0.25 D 4.15 BSC D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00	b2	3.80	4.10	4.40				
C2 0.19 0.22 0.25 D 4.15 BSC D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF 1.10 REF	b4		0.55					
D 4.15 BSC D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	C	0.19		0.25				
D1 3.80 4.00 4.20 D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF								
D2 3.00 3.10 3.20 D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF		4	4.15 BS	2				
D3 0.30 0.40 0.50 D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	D1	3.80	4.00	4.20				
D4 0.90 1.00 1.10 D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	D2	3.00	3.10	3.20				
D5 0.70 0.80 0.90 D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	D3	0.30	0.40	0.50				
D6 0.55 0.65 0.75 D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	D4	0.90	1.00	1.10				
D7 0.31 REF D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	D5	0.70	0.80	0.90				
D8 0.40 REF E 4.90 BSC E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	D6	0.55	0.65	0.75				
E	D7		0.31 REI	F				
E1 4.85 4.95 5.05 E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	D8		0.40 REI	F				
E2 3.10 3.20 3.30 E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF		4	4.90 BS0	0				
E3 0.00 0.10 0.20 E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF		4.85	4.95	5.05				
E4 2.00 2.10 2.20 e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	E2	3.10	3.20	3.30				
e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	E3	0.00						
e 1.27 BSC e/2 0.635 BSC e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	E4			2.20				
e1 0.40 REF H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	е	1.27 BSC						
H 6.00 6.15 6.30 L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF	e/2	0.635 BSC						
L 0.50 0.70 0.90 L1 0.80 0.90 1.00 L2 1.10 REF		0.40 REF						
L1 0.80 0.90 1.00 L2 1.10 REF								
L2 1.10 REF	L							
L2 1.10 REF Θ 0° 4° 8°	L1							
Θ 0° 4° 8°		1.10 REF						
	θ	0°	4°	8°				

DOCUMENT NUMBER: 98AON82777G Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. DESCRIPTION: LFPAK4 4.90x4.15x1.15MM, 1.27P PAGE 1 OF 1

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales